

Product information

BOTTOM TRACK SEAL CFS-BTS

Product description

• Preformed firestop solution for bottom-of-wall drywall joints — helps increase productivity on the job site and eliminate the need for slower, messier sealants

Applications for use

- Firestop, smoke, and sound seal for the bottom of the wall joints between bottom track and drywall to flat and metal deck concrete slabs
- Tested and UL classified with standard 1-hour and 2-hour partition walls, resilient channel walls and shaft walls (5/8" and 1-1/4" available)

Advantages

- Easier to install under real job site conditions compressible firestop joint seal suitable for installation in temperatures as low as 14°F (-10°C)
- Higher productivity the preformed firestop replaces 5/8" drywall shims and works with kick-lifts to help save time and improve quality control of drywall install
- · Zero waste controlled material cost / easier to bid
- Sound and Leakage-rated joint seal CFS-BTS firestop can provide STC ratings for fire/sound walls, and has been tested in accordance with L-rating compliance in smoke barrier walls (IBC)
- Compliance with LEED green building regulations provides industry-leading low VOC, LEED 4.1, and Red List (LBC) compliance
- No skilled labor required and may not be subjective to destructive testing

Installation instructions

• See Hilti literature or third-party listings for application and installation details

Technical Data Chemical basis XLPE foam Color White / Red 14° to 122°F (-10° to 50°C) **Recommended Application temperature** 14° to 122°F (-10° to 50°C) Storage and transportation temperature range Temperature resistance range 14° to 122°F (-10° to 50°C) Surface burning characteristics (ASTM E84-96) Flame Spread: 0 Smoke Development: 0 Surface burning characteristics Flame Spread: 0 (CAN/ULC-S102) Smoke Development: 5 Mold and mildew performance Class 0 (ASTM G21-96) Tested In accordance with UL 2079 (5th Edition), CAN/ULC S115, ASTM D3575 Suffix L (modified) LEEDv4.1 CDPH Standard Method v1.2-2017 Compliant LEED VOC 1 g/L Length 72 in (6ft) Acoustics performance 63 (relates to specific construction) ASTM E90 Shelf Life Unlimited

1/4" - 3/4"



Order Information

Designation	Sales pack quantity	ltem number
Bottom track seal CFS-BTS (5/8") ①	70	2331840
Bottom track seal CFS-BTS (1-1/4") ②	70	2331841



FILL, VOID OR CAVITY MATERIAL FOR USE IN JOINT SYSTEMS SEE UL FIRE RESISTANCE DIRECTORY



Joint Width