## UL/cUL SYSTEM NO. FF-D-1026


## FIRE-RATED JOINT THROUGH CONCRETE FLOOR ASSEMBLY

**ASSEMBLY RATING = 3-HR.** 

**CLASS II MOVEMENT CAPABILITIES - 25% COMPRESSION OR EXTENSION** 

**TOP VIEW** 

**SECTION A-A** 



- 1. CONCRETE FLOOR ASSEMBLY (MINIMUM 5" THICK) (3-HR. FIRE-RATING).
- 2. MINIMUM 4-3/4" THICKNESS MINERAL WOOL (MIN. 4 PCF DENSITY) COMPRESSED MINIMUM 50%.
- 3. MINIMUM 1/4" (WET) THICKNESS HILTI CFS-SP WB FIRESTOP JOINT SPRAY OR HILTI CP 672 SPEED SPRAY APPLIED WITHIN THE JOINT. FLUSH WITH TOP SURFACE OF FLOOR AND LAPPING MINIMUM 3/4" ONTO THE TOP SURFACE OF THE FLOOR ON BOTH SIDES OF JOINT.

NOTE: MAXIMUM WIDTH OF JOINT = 3".



HILTI, Inc. Tulsa, Oklahoma USA (800) 879-8000

Sheet	1 of 1
Scale	1/4" = 1"
Date	June 29, 2010

Drawing No. **FFD** 1026c

Saving Lives through Innovation and Education