
## UL/cUL SYSTEM NO. FF-D-1087

## FIRE-RATED JOINT THROUGH CONCRETE FLOOR ASSEMBLY

ASSEMBLY RATING = 2-HR.

CLASS II MOVEMENT CAPABILITIES - 17% COMPRESSION OR EXTENSION
L-RATING AT AMBIENT = LESS THAN 1 CFM/LIN. FT.
L-RATING AT 400°F = LESS THAN 1 CFM/LIN. FT.

## **CROSS-SECTIONAL VIEW**



- 1. LIGHTWEIGHT OR NORMAL WEIGHT CONCRETE FLOOR (MINIMUM 4-1/2" THICK) (2-HR. FIRE-RATING).
- 2. MINIMUM 4" THICKNESS MINERAL WOOL (MIN. 4 PCF DENSITY) COMPRESSED 40%.
- 3. MINIMUM 1/4" DEPTH HILTI CP 606 FLEXIBLE FIRESTOP SEALANT.

NOTE: MAXIMUM WIDTH OF JOINT = 3".



HILTI, Inc. Tulsa, Oklahoma USA (800) 879-8000

Sheet	1 of 1
Scale	3/8" = 1"
Date	Sep. 28, 2009

FFD 1087a

Saving Lives through Innovation and Education

FD10879 002800