## **UL/cUL SYSTEM NO. C-AJ-8148**

## HVAC LINE SET THROUGH CONCRETE FLOOR/WALL OR BLOCK WALL ASSEMBLY

F-RATING = 2-HR. T-RATING = 0-HR.

- 1. CONCRETE FLOOR OR WALL ASSEMBLY (2-HR. FIRE-RATING) :
  - A. LIGHTWEIGHT OR NORMAL WEIGHT CONCRETE FLOOR OR WALL (MINIMUM 4-1/2" THICK).
  - B. PRECAST (HOLLOW-CORE) CONCRETE FLOOR (MINIMUM 6" THICK).
- 2. [OPTIONAL] MAXIMUM 4" NOMINAL DIAMETER STEEL PIPE SLEEVE (SCHEDULE 10 OR HEAVIER).
- 3. MAXIMUM 1" NOMINAL DIAMETER COPPER PIPE.
- 4. MAXIMUM 1/2" NOMINAL DIAMETER COPPER PIPE.
- 5. NOMINAL 3/4" THICK AB/PVC PIPE INSULATION INSTALLED ON ONE COPPER PIPE.
- 6. MAXIMUM 4-PAIR NO. 18 AWG THERMOSTAT CABLE WITH PVC JACKET.
- 7. MINIMUM 4" THICKNESS MINERAL WOOL (MIN. 4 PCF DENSITY) TIGHTLY PACKED AND RECESSED TO ACCOMMODATE FIRESTOP SEALANT.
- 8. MINIMUM 1/4" DEPTH HILTI FS-ONE MAX OR FS-ONE INTUMESCENT FIRESTOP SEALANT.
- 9. MINIMUM 1/4" BEAD HILTI FS-ONE MAX OR FS-ONE INTUMESCENT FIRESTOP SEALANT APPLIED AT POINT OF CONTACT.

ANNULAR SPACE	MINIMUM	MAXIMUM
BETWEEN PIPES AND PERIPHERY OF OPENING	1/4"	1-1/2"
BETWEEN PENETRANTS	0"	1"
BETWEEN INSULATED PIPE AND PERIPHERY OF OPENING	0"	1-1/2"
BETWEEN CABLE AND PERIPHERY OF OPENING	1/2"	1"

NOTES: 1. MAXIMUM DIAMETER OF OPENING = 4".

- 2. WHEN PRECAST (HOLLOW-CORE) FLOORS ARE USED, MINERAL WOOL SHOULD BE INSTALLED FLUSH WITH BOTTOM SURFACE OF FLOOR.
- 3. HILTI FS-ONE MAX OR FS-ONE INTUMESCENT FIRESTOP SEALANT TO BE APPLIED INTO INTERSTICES OF BUNDLE TO MAXIMUM EXTENT POSSIBLE.
- 4. MINIMUM 1/4" DEPTH HILTI FS-ONE MAX OR FS-ONE INTUMESCENT FIRESTOP SEALANT IS REQUIRED ON EACH SIDE OF A WALL ASSEMBLY.



HILTI, Inc. Tulsa, Oklahoma USA (800) 879-8000

Sheet	1 of 1
Scale	5/32" = 1"
Date	Jan .15, 2015

CAJ 8148c