### **UL/cUL SYSTEM NO. W-J-3060**


# CABLE BUNDLE THROUGH CONCRETE WALL OR BLOCK WALL ASSEMBLY


F-RATING = 1-HR. OR 2-HR.


T-RATING = 0-HR.


L-RATING AT AMBIENT = 15 CFM / SQ FT

L-RATING AT 400° F = 8 CFM / SQ FT











HILTI, Inc. Plano, Texas USA (800) 879-8000

Sheet	1 of 3
Scale	3/32" = 1"
Date	Sep. 06, 2022

WJ 3060p

WJ3060p.090622

#### UL/cUL SYSTEM NO. W-J-3060

### CABLE BUNDLE THROUGH CONCRETE WALL OR BLOCK WALL ASSEMBLY

F-RATING = 1-HR. OR 2-HR.

T-RATING = 0-HR.

L-RATING AT AMBIENT = 15 CFM / SQ FT

L-RATING AT 400° F = 8 CFM / SQ FT

WJ3060p.090622

- 1. CONCRETE WALL ASSEMBLY (1-HR. OR 2-HR. FIRE-RATING):
  - A. LIGHTWEIGHT OR NORMAL WEIGHT CONCRETE WALL (MIN. 4-3/4" THICK, FOR A 1-HR. FIRE-RATING).
  - B. LIGHTWEIGHT OR NORMAL WEIGHT CONCRETE WALL (MIN. 6" THICK, FOR A 2-HR. FIRE-RATING).
  - C. ANY UL/cUL CLASSIFIED CONCRETE BLOCK WALL ASSEMBLY.
- 2. [OPTIONAL] MAXIMUM 4" NOMINAL DIAMETER EMT, STEEL PIPE (SCHEDULE 5 OR HEAVIER) OR 28 GA. GALVANIZED STEEL SLEEVE, FRICTION FIT OR CAST INTO WALL FLUSH WITH WALL SURFACES (SEE NOTE NO. 5 BELOW).
- 3. CABLE BUNDLE TO CONSIST OF ANY COMBINATION OF THE FOLLOWING:
  - A. MAXIMUM 7/C NO. 12 AWG POWER CABLE WITH PVC INSULATION AND OUTER JACKET.
  - B. MAXIMUM 25 PAIR NO. 24 AWG TELEPHONE CABLE WITH PVC INSULATION AND OUTER JACKET.
  - C. MAXIMUM RG 59 (OR SMALLER) COAXIAL CABLE WITH POLYETHYLENE INSULATION AND PVC JACKET.
  - D. MAXIMUM RG 6/U COAXIAL CABLE WITH FLUORINATED ETHYLENE INSULATION AND JACKETING.
  - E. MULTIPLE 24 FIBER OPTIC COMMUNICATION CABLE WITH PVC JACKET, HAVE A MAX OUTSIDE DIAM OF 5/8" (16 mm).
  - F. MAXIMUM FOUR PAIR NO. 22 AWG CAT 5 OR CAT 6 COMPUTER CABLES.
  - G. THROUGH PENETRATING PRODUCT MAX THREE COPPER CONNECTOR NO. 8 AWG METAL-CLAD CABLE (AFC CABLE SYSTEMS INC.).
  - H. ANY CABLES, METAL-CLAD OR ARMORED CABLE, CURRENTLY CLASSIFIED CLASSIFIED UNDER THE THROUGH PENETRANTS PRODUCTS CATEGORY.
- 4. MINIMUM 5/8" DEPTH HILTI FS-ONE MAX INTUMESCENT FIRESTOP SEALANT, HILTI CP 606 FLEXIBLE FIRESTOP SEALANT, HILTI CFS-S SIL GG FIRESTOP SILICONE SEALANT, OR HILTI CP 618 FIRESTOP PUTTY STICK.
- 5. MINIMUM 1/2" BEAD HILTI FS-ONE MAX INTUMESCENT FIRESTOP SEALANT, HILTI CP 606 FLEXIBLE FIRESTOP SEALANT, HILTI CFS-S SIL GG FIRESTOP SILICONE SEALANT, OR HILTI CP 618 FIRESTOP PUTTY STICK APPLIED AT WALL/SLEEVE INTERFACE WHEN STEEL SLEEVE EXTENDS BEYOND ONE OR BOTH SIDES OF WALL.



HILTI, Inc. Plano, Texas USA (800) 879-8000

Sheet	2 of 3
Scale	-
Date	Sep. 06, 2022

WJ 3060p

#### UL/cUL SYSTEM NO. W-J-3060

## CABLE BUNDLE THROUGH CONCRETE WALL OR BLOCK WALL ASSEMBLY

F-RATING = 1-HR. OR 2-HR.

T-RATING = 0-HR.

L-RATING AT AMBIENT = 15 CFM / SQ FT

L-RATING AT 400° F = 8 CFM / SQ FT

VJ3060p.09062;

NOTES: 1. MAXIMUM DIAMETER OF OPENING WITH SLEEVE = 5-1/2".

- 2. MAXIMUM DIAMETER OF OPENING WITHOUT SLEEVE = 4".
- 3. ANNULAR SPACE = MINIMUM 0", MAXIMUM 1".
- 4. CABLES TO FILL MAXIMUM 45% OF CROSS-SECTIONAL AREA OF OPENING.
- 5. WHEN SCHEDULE 5 STEEL PIPE OR EMT IS USED, SLEEVE MAY EXTEND UP TO 18" BEYOND WALL SURFACES. AS AN OPTION, SLEEVE MAY BE CONTINUOUS ON ONE SIDE OF WALL ASSEMBLY.
- 6. WHEN SLEEVE IS CONTINUOUS ON ONE SIDE OF WALL, THE CABLE FILL MAY BE 0% TO 45% AND THE MAXIMUM ANNULAR SPACE IS NOT LIMITED.
- 7. [OPTIONAL NOT SHOWN] MINERAL WOOL (MIN. 4 PCF DENSITY) TIGHTLY PACKED AND RECESSED TO ACCOMMODATE FIRESTOP SEALANT OR PUTTY MAY BE USED AS BACKING MATERIAL.



HILTI, Inc. Plano, Texas USA (800) 879-8000

Sheet	3 of 3
Scale	•
Date	Sep. 06, 2022

WJ 3060p

Saving Lives through Innovation and Education