
UL/cUL SYSTEM NO. WW-D-0064

FIRE-RATED JOINT THROUGH CONCRETE WALL ASSEMBLY

ASSEMBLY RATING = 3-HR.

CLASS II MOVEMENT CAPABILITIES - 6% COMPRESSION OR EXTENSION
L-RATING AT AMBIENT = LESS THAN 1 CFM / LIN FT
L-RATING AT 400°F = LESS THAN 1 CFM / LIN FT

TOP VIEW



- 1. CONCRETE WALL ASSEMBLY (3-HR. FIRE-RATING) :
 - A. LIGHTWEIGHT OR NORMAL WEIGHT CONCRETE WALL (MINIMUM 6" THICK).
 - B. ANY UL/cUL CLASSIFIED CONCRETE BLOCK WALL.
- 2. MINIMUM 5" THICKNESS MINERAL WOOL SAFING (MIN. 4 PCF DENSITY) COMPRESSED 50%.
- 3. MINIMUM 1/2" DEPTH HILTI CP 606 FLEXIBLE FIRESTOP SEALANT FLUSH WITH BOTH SIDES OF WALL.

NOTE: MAXIMUM WIDTH OF JOINT = 2".



HILTI, Inc. Plano, Texas USA (800) 879-8000

Sheet	1 of 1
Scale	5/16" = 1"
Date	Aug. 02, 2019

WWD 0064b

Saving Lives through Innovation and Education