


Classified by Underwriters Laboratories, Inc. to UL 1479 and CAN/ULC-S115

System No. F-C-3044

ANSI/UL1479 (ASTM E814)	CAN/ULC S115
F Rating — 1 Hr	F Rating — 1 Hr
T Rating — 1 Hr	FT Rating — 1 Hr
	FH Rating — 1 Hr
	FTH Rating — 1 Hr



- 1. Floor-Ceiling Assembly The 1 hr fire-rated solid or trussed lumber joist floor-ceiling assembly shall be constructed of the materials and in the manner specified in the individual L500 Series Floor-Ceiling Designs in the UL Fire Resistance Directory. The general construction features of the floor-ceiling assembly are summarized below:
 - A. Flooring System Lumber or plywood subfloor with finish floor of lumber, plywood or Floor Topping Mixture* as specified in the individual Floor-Ceiling Design. Max diam of opening shall be 3 in. (76 mm).
 - B. Wood Joists* Nom 10 in. (254 mm) deep (or deeper) lumber, steel or combination lumber and steel joists, trusses or Structural Wood Members* with bridging as required and with ends firestopped.
 - C. Gypsum Board* Nom 4 ft (1.2 m) wide by 5/8 in. (16 mm) thick as specified in the individual Floor-Ceiling Design. Max diam of opening shall be 3 in. (76 mm).
- 1.1 Chase Wall (Not Shown, Optional)—The through penetrants (Item 2) may be routed through a 1 hr fire-rated single, double or staggered wood stud/gypsum wallboard chase wall having a fire rating consistent with that of the floor-ceiling assembly. The chase wall shall be constructed of the materials and in the manner specified in the individual U300 Series Wall and Partition Designs in the UL Fire Resistance Directory and shall include the following construction features:
 - A. Studs Nom 2 by 4 in. (51 by 102 mm) lumber studs.
 - B. Sole Plate Nom 2 by 4 in. (51 by 102 mm) lumber plates. Max diam of opening shall be 3 in. (76 mm).
 - C. Top Plate The double top plate shall consist of two nom 2 by 4 in. (51 by 102 mm) lumber plates. Max diam of opening shall be 3 in. (76 mm).
 - D. Gypsum Board* Thickness, type, number of layers and fasteners shall be as specified in individual Wall and Partition Design.



System No. F-C-3044

- 2. Cables Aggregate cross-sectional area of cables in opening to be max 25 percent of the cross-sectional area of the opening. The annular space within the firestop system shall be 3/4 in. Cables to be rigidly supported on both sides of floor assembly. Any combination of the following types and sizes of cables may be used:
 - A. RG 59 coaxial cable with single copper conductor, cellular polyethylene cellular foam insulation and polyvinyl chloride (PVC) jacket.
 - B. Max 25 pair No. 24 AWG telephone cable with polyvinyl chloride (PVC) jacketing.
 - C. Max 3/C No. 10 AWG cable (Type NM).
 - D. Max 3/C with ground No. 2/0 AWG aluminum or copper Type SER cable with polyvinyl chloride (PVC) insulation.
 - E. Max 24 fiber optic cable.
 - F. Through Penetrating Products* Three conductor No. 10 AWG Metal-Clad Cable. AFC CABLE SYSTEMS INC
- 3. Fill, Void or Cavity Materials*-Sealant Min 3/4 in. (19 mm) thickness of sealant applied within the annular space, flush with top surface of floor or sole plate. Min 5/8 in. (16 mm) thickness of sealant applied within annular space, flush with bottom surface of the gypsum wallboard or lower top plate. Sealant forced into the interstices of the cables on both sides of the wall.
- HILTI CONSTRUCTION CHEMICALS, DIV OF HILTI INC FS-ONE Sealant or FS-ONE MAX Intumescent Sealant
- * Indicates such products shall bear the UL or cUL Certification Mark for jurisdictions employing the UL or cUL Certification (such as Canada), respectively.
- +Bearing the UL Listing Mark

