

# FIRESTOP SILICONE JOINT SPRAY CFS-SP SIL

## **Product description**

- The fast curing properties of the new Hilti Firestop silicone joint spray CFS-SP SIL allow contractors to reduce delays caused by weather, while improving their productivity and reducing the risk of water damage.
- This low slump formulation combines superior sprayability and coverage characteristics which also limits runs in vertical surface applications.

### **Product features**

- A fast curing spray coating with a short tack-free time
- Tested in accordance with ASTM D6904 provides rain and wash out resistance within a few hours
- Both sprayable and brushable
- Quicker and easier installation with Graco Ultra Max II 595 and 695 Sprayers can help save you time and money
- Contains no halogens, solvents or asbestos
- One 5 gal bucket will yield approx. 245 lin.ft (@4" gap)
- Mold and mildew resistance rating 1 (ASTM G21)

## Areas of application

Sealing building perimeter gaps between floor slabs and exterior curtain wall facades

#### For use with

· Concrete floors and façade assemblies

#### **Examples**

 Where a concrete floor assembly meets with non-rated exterior wall (concrete, glass, etc.)

## Installation instructions

See Hilti literature or third-party listings for complete application and installation details


## **Technical data**

Teominear data			
Density	Approx. 11 lb/gal		
Color	Off-white		
Application temperature	35° to 104° ( 1.5°C to 40)*		
Temperature resistance	-30°F to 248°F (-35°C to 120°C)		
Storage temperature	35°F to 77°F (1.5°C to 25°C)		
Consistency	Sprayable liquid		
Chemical basis	Neutral cross-linking silicone		
Paintable	No		
Mold and mildew	Class 1 (ASTM G21-96)		
Movement	+/-12.5%		
Packaging	5gal Pail (19 Liters)		
Volume per unit	1,153.3 in <sup>3</sup>		
Rain resistance (ASTM D6904)	Passed (2 hour rain resisitance after 160 min. cure t		
Tack free time (ASTM C679)	55 min at 73°F, 50% humidity		
Curing time	Approx. 5 hours at 73°F, 50% humidity for 2 mm depth		
Surface burning characteristics (ASTM E84)	Flame spread: 0, Smoke development: 50		
Sound transmission classification (ASTM E90)	61 (per tested construction type)		
Elongation at break	>200%		
VOC	72 a/l		

12 months from date of manufacture

ASTM E2307, ASTM E 84, ASTM E90,

CAN/ULC-S115





## **Order Information**

Designation	Legend	Qty per package	Item number
Firestop silicone joint spray CFS-SP SIL	1	1	2095007
Graco Ultra Max II 595 Sprayer	2	1	3509241
Graco Ultra Max II 695 Sprayer	3	1	3509242
Firestop silicone joint spray CFS-SP SIL (Pallet — 18 pails)	1	18	3517095
CFS-SP SIL w/ Graco Ultra Max II 595 Sprayer (Pallet)	① & ②	18	3517096
CFS-SP SIL w/ Graco Ultra Max II 695 Sprayer (Pallet)	1 & 3	18	3517097



FILL, VOID OR CAVITY MATERIAL FOR USE IN THROUGH-PENETRATION FIRESTOP SYSTEMS, JOINT SYSTEMS AND PERIMETER FIRE CONTAINMENT SYSTEMS
SEE UL FIRE RESISTANCE DIRECTORY 5BP5



- Definition = For ambient and surface temperatures between 10°F (12°C) and 35°F (1.5°C), the following conditions must apply:
   Substrate surfaces are clean and dry (e.g. free of dust, rust, grease, oil, dew, frost, ice, moisture, etc):
- Product maintained above 50°F (10°C) for a minimum of 24 hours
- prior to application;
   Product will not cure at ambient temperatures below 32°F / 0°C













Tested in accordance with

Shelf life