




Classified by  
Underwriters Laboratories, Inc.  
to UL 1479 and CAN/ULC-S115

## System No. W-J-1215

WJ 1215

ANSI/UL1479 (ASTM E814)	CAN/ULC S115
F Rating — 2 Hr	F Rating — 2 Hr
T Ratings — 0 and 3/4 Hr (See Item 3)	FT Ratings — 0 and 3/4 Hr (See Item 3)
	FH Rating — 2 Hr
	FTH Ratings — 0 and 3/4 Hr (See Item 3)



1. Wall Assembly — Min 5-5/8 in. (143 mm) reinforced lightweight or normal weight (100-150 pcf or 1600-2400 kg/m<sup>3</sup>) concrete. Wall may also be constructed of any UL Classified Concrete Blocks\*. Opening in wall to be 2-1/2 in. (64 mm) diam for nominal 2 in. (51 mm) firestop device and 4 1/2 in. (114 mm) diam for nominal 4 in. (102 mm) firestop device.

See Concrete Blocks (CAZT) category in the Fire Resistance Directory for names of manufacturers.

2. Through Penetrant — One metallic pipe, conduit or tubing to be installed concentrically within the firestop system. Pipe, conduit or tubing to be rigidly supported on both sides of the wall assembly. The following types and sizes of metallic pipes, conduits and tubes may be used:

A. Steel Pipe — Nom 3 in. (76 mm) diam (or smaller) Schedule 5 (or heavier) steel pipe.

B. Iron Pipe — Nom 3 in. (76 mm) diam (or smaller) cast or ductile iron pipe.

C. Conduit — Nom 3 in. (76 mm) diam (or smaller) rigid steel conduit or steel electrical metallic tubing (EMT).

3. Firestop Device\* — Firestop device consists of a corrugated steel tube with an inner plastic housing, intumescent material rings, tightly twisted inner fabric smoke seal, flanges and gasketing material (not shown). As an option, the inner fabric seal may remain open. The T, FT and FTH Ratings of the firestop system are 0 hr when the inner fabric seal remains open. Firestop device to be installed in accordance with the accompanying installation instructions. Device slid into wall such that ends project an equal distance from the approximate centerline of the wall assembly. The annular space between the device and the periphery of the opening shall be min 0 in. (point contact). Device provided with flanges that are spun clockwise onto device threads, over gasketing material butting tightly to both sides of wall. As an alternate to gasket material, sealant (Item 4) may be used.

HILTI CONSTRUCTION CHEMICALS, DIV OF HILTI INC — CP 653 and CP 653 BA 2" Speed Sleeve, CP 653 and CP 653 BA 4" Speed Sleeve, CFS-SL GA L Speed Sleeves, CP 653 4" BA ILS and CFS-SL GA L ILS Speed Sleeve

The CFS-SL GA L and CFS-SL GA L ILS Speed Sleeves shall only be used in wall thickness of 8 in. (203 mm) or greater.

4. Fill, Void or Cavity Material\* - Sealant — As an alternate to gasket material (see Item 3), min 1/2 in. (13 mm) thickness of fill material applied within the annulus between firestop device and wall, flush with both surfaces of wall. An additional 1/4 in. (6 mm) bead shall be applied around periphery of device on each side of wall prior to securing device flanges.

HILTI CONSTRUCTION CHEMICALS, DIV OF HILTI INC — CP 606 or FS-ONE MAX Intumescent Sealant

\* Indicates such products shall bear the UL or cUL Certification Mark for jurisdictions employing the UL or cUL Certification (such as Canada), respectively.



Reproduced by HILTI, Inc. Courtesy of  
Underwriters Laboratories, Inc.  
July 02, 2018