


Classified by Underwriters Laboratories, Inc. to UL 1479 and CAN/ULC-S115

System No. W-J-7110

ANSI/UL1479 (ASTM E814)	CAN/ULC S115
F Rating — 2 Hr	F Rating — 2 Hr
T Rating — 0 Hr	FT Rating — 0 Hr
L Rating At Ambient — Less Than 1 CFM/sq ft	FH Rating — 2 Hr
L Rating At 400 F — Less Than 1 CFM/sq ft	FTH Rating — 0 Hr
	L Rating At Ambient — Less Than 1 CFM/sq ft
	L Rating At 400 F — Less Than 1 CFM/sq ft



- Wall Assembly Min 6 in. (152 mm) thick reinforced lightweight or normal weight (100-150 pcf or 1600-2400 kg/m3) concrete. Wall may also be constructed of any UL Classified Concrete Blocks*. Max area of opening is 324 sq in. (0.21 m2) with max dim of 18 in. (457 mm).
 See Concrete Blocks (CAZT) category in Fire Resistance Directory for names of manufacturers.
- 2. Through Penetrant One W14X90 (or smaller) steel beam service support to be installed within the firestop system. An annular space of min 1/2 in. (13 mm) to max 3 in. (76 mm) is required between the steel beam and the periphery of the opening. Steel beam service support to be rigidly supported on both sides of wall assembly.
- 3. Firestop System The firestop system shall consist of the following items:
 - A. Packing Material Mineral wool batt insulation, nom 4 pcf (64 kg/m3), tightly-packed into opening to full depth of wall except for min 5/8 in. (16 mm) recess on each side of wall as required to accommodate fill material (Item 3B).
 - B. Fill, Void or Cavity Material* Sealant Min 1/2 in. (13 mm) thickness of fill material applied to fill annular space around steel beam flush with each surface of wall.
 - HILTI CONSTRUCTION CHEMICALS, DIV OF HILTI INC FS-ONE Sealant or FS-ONE MAX Intumescent Sealant
- * Indicates such products shall bear the UL or cUL Certification Mark for jurisdictions employing the UL or cUL Certification (such as Canada), respectively.

