


System No. W-J-1221

ANSI/UL1479 (ASTM E814)	CAN/ULC S115
F Rating — 2 Hr	F Rating — 2 Hr
T Rating — 1-1/2 Hr	FT Rating — 1-1/2 Hr
	FH Rating — 2 Hr
	FTH Rating — 1-1/2 Hr



SECTION A-A

- 1. Wall Assembly Min 6 in. (152 mm) thick reinforced lightweight or normal weight (100-150 pcf or 1600-2400 kg/m3) concrete. Wall may also be constructed of any UL Classified Concrete Blocks*. Max diam of opening is 5-1/2 in. (140 mm).
 - See Concrete Blocks (CAZT) category in the Fire Resistance Directory for names of manufacturers.
- 2. Through Penetrants Max six nom 1 in. (25 mm) diam (or smaller) flexible steel conduits to be installed either concentrically or eccentrically within the firestop system. The annular space between the conduits and the periphery of the opening shall be min 0 in. (point contact) to max 3 in. (76 mm). Conduits to be rigidly supported on both sides of wall.
- 3. Fill, Void or Cavity Material* Sealant Min 5/8 in. (16 mm) thickness of sealant applied within annulus, flush with both surfaces of wall. A min 1/2 in. diam bead of sealant to be applied at the conduit/wall interface at the point contact location.
 - HILTI CONSTRUCTION CHEMICALS, DIV OF HILTI INC FS-ONE Sealant or FS-ONE MAX Intumescent Sealant.
- * Indicates such products shall bear the UL or cUL Certification Mark for jurisdictions employing the UL or cUL Certification (such as Canada), respectively.

