## UL/cUL SYSTEM NO. F-B-2061

## PLASTIC PIPE THROUGH CONCRETE FLOOR ASSEMBLY

F-RATING = 2-HR.


T-RATING = 1-1/2-HR. OR 2-HR.

L-RATING AT AMBIENT = 1.47 CFM PER DEVICE L-RATING AT 400°F = LESS THAN 1 CFM PER DEVICE

W-RATING = CLASS I (SEE NOTE NO. 2 BELOW)

TOP VIEW

**SECTION A-A** 



SYSTEM TESTED WITH A PRESSURE DIFFERENTIAL OF 2.5 Pa BETWEEN THE EXPOSED AND THE UNEXPOSED SURFACES WITH THE HIGHER PRESSURE ON THE EXPOSED SIDE.

- 1. LIGHTWEIGHT OR NORMAL WEIGHT CONCRETE FLOOR ASSEMBLY (MINIMUM 6" THICK) (2-HR. FIRE-RATING).
- 2. PENETRATING ITEM TO BE ONE OF THE FOLLOWING:
  - A. NOMINAL 8" OR 10" DIAMETER PVC PLASTIC PIPE (CELLULAR OR SOLID CORE).
  - B. NOMINAL 8" OR 10" DIAMETER CPVC PLASTIC PIPE (CLOSED PIPING SYSTEM).
- 3. HILTI CFS-CID P [8" OR 10"] FIRESTOP CAST-IN DEVICE CAST OR GROUTED INTO CONCRETE FLOOR.
- NOTES: 1. CLOSED OR VENTED PIPING SYSTEM (PVC = SCHEDULE 40; CPVC = SDR 13.5).
  - 2. [OPTIONAL] FOR W-RATING ONLY, THE FOLLOWING MATERIALS MUST BE INSTALLED
    - A. MINIMUM 1" THICKNESS MINERAL WOOL (MIN. 4 PCF DENSITY) TIGHTLY PACKED AND RECESSED TO ACCOMMODATE SEALANT MINERAL WOOL SHALL NOT EXTEND INTO THE WRAP STRIP LAYERS.
    - B. MINIMUM 1/2" DEPTH HILTI CFS-S SIL GG FIRESTOP SILICONE SEALANT OR HILTI CFS-S SIL SL FIRESTOP SILICONE SEALANT FLUSH WITH TOP SURFACE OF FLOOR.



HILTI, Inc. Plano, Texas USA (800) 879-8000

Sheet	1 of 1
Scale	1/8" = 1"
Date	July 19, 2017

FB 2061c

Saving Lives through Innovation and Education