



## System No. W-J-5194

<del></del>	
ANSI/UL1479 (ASTM E814)	CAN/ULC S115
F Rating — 2 Hr	F Rating — 2 Hr
T Rating — 1/2 Hr	FT Rating — 1/2 Hr
	FH Rating — 2 Hr
	FTH Rating — 1/2 Hr





- 1. Wall Assembly Min 6 in. (152 mm) thick reinforced lightweight or normal weight (100-150 pcf or 1600-2400 kg/m3) concrete. Wall may also be constructed of any UL Classified Concrete Blocks\*. Max diam of opening is 5-1/2 in. (140 mm).
  - See Concrete Blocks (CAZT) in the Fire Resistance Directory for names of manufacturers.
- 2. Through Penetrants (Refrigerant Tubing)+ Maximum four nom 7/8 in. (22 mm) diam (or smaller) Streamline® ACR-Type L (or heavier) copper tubes preassembled with nom 1/2 in. (13 mm) thick Streamline Duraguard TM polyethylene tubing insulation to be installed within the firestop system. Penetrants to be rigidly supported on both sides of wall assembly. The annular space between the insulated tubing and periphery of the opening shall be min 0 in. (point contact) to max 1-3/4 in. (44 mm).
- 3. Firestop System The details of the firestop system shall be as follows:
  - A. Fill, Void or Cavity Material\* Sealant Min 5/8 in. (16 mm) thickness of fill material applied within annulus, flush with both surfaces of wall assembly. Fill material forced into grouped penetrant interstices to max extent possible within opening.
    - HILTI CONSTRUCTION CHEMICALS, DIV OF HILTI INC FS-ONE MAX Intumescent Sealant
  - B. Fill, Void or Cavity Material\* Wrap Strip Nom 3/16 in. (5 mm) thick by 1-3/4 in. (44 mm) wide intumescent wrap strip. Wrap strip is continuously wrapped around the outer circumference of bundled penetrants two times with ends butted and held in place with tape. Wrap strip installed flush with both surfaces of wall assembly.
    - HILTI CONSTRUCTION CHEMICALS, DIV OF HILTI INC CP648-E- W45/1-3/4" Wrap Strip
  - C. Steel Collar Steel collar fabricated from coils of precut min 0.016 in. (0.41 mm) thick (No. 28 gauge) galv steel available from fill material manufacturer. Collar shall be min 1-3/4 in. (44 mm) deep with 1 in. (25 mm) wide by 2 in. (51 mm) long anchor tabs on 1-3/4 in. (44 mm) centers for securement to both surfaces of wall. In addition, collars contain preformed retainer tabs 1/2 in. (13 mm) wide by 3/16 in. (5 mm) long, located opposite the anchor tabs. Collar shall be tightly wrapped over the wrap strip, overlapping min 1 in. (25 mm) at seam and compressed with a min 1/2 in. (13 mm) wide by 0.028 in. (0.71 mm) thick stainless steel band at collar mid-height. Every other anchor tab of collar secured to surface of wall with min 1-1/2 in. (38 mm) long drywall or laminate screws with min 3/4 in. (19 mm) steel washers
- \* Indicates such products shall bear the UL or cUL Certification Mark for jurisdictions employing the UL or cUL Certification (such as Canada), respectively.
- # Bearing the UL Recognized Component Marking

