



1 (Projects/2012)12 122 YBT Details/CAD\12 122 05f dwg 8/15/2012 2:38

STRUT FASTEN TO BOTTOM FLANGE (OVERHEAD)




DETAILS FOR ELECTRICAL ENGINEERS

STRUT FASTENED WITH S-BT TO BOTTOM/TOP FLANGE



HILTI X-BTW10-24-6 SN12R POWDER-ACTUATED THREADED STUD WITH STAINLESS STEEL FLAT WASHER (ASTM A240 TYPE 316), HELICAL SPRING LOCK WASHER AND HEX NUT (ASTM F594)

U.V. RESISTANT SEALING WASHER WITH STAINLESS STEEL COVER



- SPACE POWDER-ACTUATED STUDS ACCORDINGLY TO ACCOMMODATE DESIGN LOADS. MINIMUM OF TWO STUDS PER STRUT SECTION.
- POWDER-ACTUATED STUDS SHALL BE INSTALLED PER HILTI INSTALLATION INSTRUCTIONS.
- POWDER-ACTUATED STUDS SHALL BE INSTALLED AT CENTERLINE OF OPEN FULL SLOT.
- CONTACT HILTI ENGEERING FOR THINNER BASE MATERIAL




Information and loads are recommendations for static application, and based on the published data in the Hilti Technical Guide (including allowable load values, factors of safety, methods of calculation and limiting factors). The responsible project engineer must verify suitability for any specific application. Modification to design may alter performance and should be evaluated by engineer of record.

HAM/JGB RPB 25 JUN 12

DETAILS FOR ELECTRICAL ENGINEERS


STRUT FASTENED TO **BOTTOM/TOP FLANGE** 12-122-04

STRUT FASTEN TO TOP FLANGE




FRONT ELEVATION


No.	Unit Qty	Unit	Description	Box Qty	# Boxes Needed	Item No.
1	AS REQ'D	EA	X-BTW10-24-6 SN12-R	100	AS REQ'D	377076
2	AS REQ'D	EA	WASHER 3/8" SS316	200	AS REQ'D	411780
3	AS REQ'D	EA	HEX NUT STANDARD 3/8" SS316	100	AS REQ'D	411775
4	AS REQ'D	EA	HELICAL SPRING LOCK WASHER 3/8" SS 316	-	AS REQ'D	-
5a	AS REQ'D	EA	STRUT HS-158-12/HDG 10'	1	AS REQ'D	407570
5b	AS REQ'D	EA	STRUT MS-158-12/ SS316TI 9'-10" (3M)	1	AS REQ'D	3424527
6	AS REQ'D	EA	CABLE TRAY CLIP ASSEMBLY (BY OTHERS)	-	AS REQ'D	-







EXPANSION GUIDE CLIP



NOTE:

- 1. SPACE POWDER-ACTUATED STUDS ACCORDINGLY TO ACCOMMODATE DESIGN LOADS. MINIMUM OF TWO STUDS PER STRUT SECTION.
- 2. POWDER-ACTUATED STUDS SHALL BE INSTALLED PER HILTI INSTALLATION INSTRUCTIONS.




Information and loads are recommendations for static application, and based on the published data in the Hilli Technical Gulde (Including allowable load values, factors of safety, methods of calculation and limiting factors). The responsible project engineer must verify suitability for any specific application. Modification to design may alter performance and should be evaluated by engineer of record.

25 JUN 12

Drawn Develop
HAM/JGB RPB

DETAILS FOR ELECTRICAL STRUT TO STEEL WITH X-BT FOR CABLE TRAY


TH X-BT | Total No. | 12-122-02 | Total No. | 12-122-02 | Total No. | Total No



FRONT ELEVATION

No.	Unit Qty	Unit	Description	Box Qty	# Boxes Needed	Item No.
1	AS REQ'D	EA	S-BT-MR W10/15 SN6 STUD	100	AS REQ'D	2140741
2	AS REQ'D	EA	HILTI SERRATED FLANGE NUT	100	AS REQ'D	*
3a	AS REQ'D	EA	STRUT HS-158-12/HDG 10'	1	AS REQ'D	407570
3b	AS REQ'D	EA	STRUT MS-158-12/ SS316TI 9'-10" (3M)	1	AS REQ'D	3424527
4	AS REQ'D	EA	CABLE TRAY CLIP ASSEMBLY (BY OTHERS)	-	AS REQ'D	-

^{*} S-BT-MR W10/15 SN6 PACKAGE INCLUDES SERRATED FLANGE NUTS




NOTE:

- 1. SPACE HILTI S-BT STUDS ACCORDINGLY TO ACCOMMODATE DESIGN LOADS. MINIMUM OF TWO STUDS PER STRUT SECTION.
- 2. HILTI S-BT STUDS SHALL BE INSTALLED PER HILTI INSTALLATION INSTRUCTIONS.




HILTI S-BT STRUT MOUNTING ASSEMBLY FOR HIGHLY CORROSIVE ENVIRONMENTS



HILTI S-BT-MR W10/15 SN6 STUD.
 HILTI SERRATED FLANGE NUT *


* S-BT-MR W10/15 SN6 STUD PACKAGE INCLUDES SERRATED FLANGES NUTS

HILTI X—BT STRUT MOUNTING ASSEMBLY FOR HIGHLY CORROSIVE ENVIRONMENTS



- 1. HILTI X-BT W10-24-6 SN12-R.
- 2. HEX JAM NUT 3/8-16, ALLOY GROUP 2 (316SS) ACCORDING TO ASTM F 594
- 3. TYPE A PLAIN WASHER ACCORDING TO ANSI B18.22.1, MATERIAL ACCORDING TO ASTM A240 TYPE 316.

HILTI X-BT-MF STRUT MOUNTING ASSEMBLY FOR MILDLY CORROSIVE ENVIRONMENTS



- 1. HILTI X-BT-MF W10/10 SN4.
- 2. W10 FLANGE NUT (INCL. WITH X-BT-MF PACKAGE).