

MULTI-THREAD CAST-IN ANCHOR SOLUTION FOR WOOD FORMS AND PAN JOIST DECKS

Cast-In Anchor KCM-WF and KCM-PD Technical Supplement







KCM-WF



Listings/Approvals

ICC-ES (International Code Council) ESR-4145

City of Los Angeles, 2018 LABC Supplement (within ESR-4145)

Florida Building Code, 2017 FBC with HVHZ Supplement (within ESR-4145)

FM (Factory Mutual)

Pipe Hanger Components for Automatic Sprinkler Systems 3/8 through 3/4 (see Table 11)

UL LLC

UL 203 Pipe Hanger Equipment for Fire Protection Services 3/8 through 3/4 (see Table 11)









PRODUCT DESCRIPTION

KCM-WF/PD cast-in anchors are internally threaded cast-in anchors suitable for use with either wood (WF) or metal pan joist deck (PD) form work. The internal thread designs for the KCM-WF/PD anchors include multiple thread sizes within each anchor to allow for the installation of different diameters of anchor rods. The KCM-WF and KCM-PD are ideally suited for a variety of rod hanging applications and offer time savings over traditional post-installed anchor solutions.

Product features

- Application-relevant multi-thread configurations
- KCM-WF/PD have color coded perforated foam inserts to prevent concrete intrusion
- KCM-WF have notched nails that snap off easily at the concrete surface after the wood forms are stripped.
- KCM-WF nails above the head lock the metal head to the plastic body preventing head popping off due to rebar hits
- KCM-WF nail and anchor design profile help reduce the risk of anchor knock over due to accidental rebar hit
- KCM-PD has a design without nails for fastening to pan joist deck
- Wider base of the KCM-PD allows for easy fastening to pan joist deck.

MATERIAL SPECIFICATIONS

KCM-WF and KCM-PD anchors have an insert body made from carbon steel with an engineered plastic flange. The insert body is zinc plated per ASTM B633 Fe/Zn 5 Type III.

2 July 2023

INSTALLATION PARAMETERS

Table 1 - Hilit KCM-WF and KCM-PD specification table

		- 1						
Design Information	Symbol	Units	1/4"-3/8"	1/4"-3/8"- 1/2 ["]	3/8"-1/2"	3/8"-1/2"- 5/8"	3/8"-1/2"- 5/8"-3/4"	5/8"-3/4"
Insert type	-	-	WF and PD	WF	WF	WF and PD	WF and PD	WF
Plastic housing color	-	-	Green	Black	Orange	Red	Grey	Grey
Effective embedment	h _{ef}	in. (mm)	1.12 (28)	1.63 (41)	1.63 (41)	2.04 (52)	3.0 (76)	2.5 (64)
Nominal embedment	h _{nom}	in. (mm)	1.27 (32)	1.78 (45)	1.78 (45)	2.19 (56)	3.2 (81)	2.7 (69)
Minimum member thickness	h _{min}	in. (mm)	2 1/2 (64)	2 1/2 (64)	2 1/2 (64)	3 (76)	4 (102)	3 1/2 (89)
Outside diameter of anchor steel body	d _a	in. (mm)	0.51 (13)	0.67 (17)	0.67 (17)	0.87 (22)	1.02 (26)	1 (25)
Bearing area	A_{brg}	in.² (mm²)	0.91 (590)	0.96 (619)	0.96 (619)	1.23 (792)	2.25 (1,451)	1.23 (792)
Minimum anchor spacing ¹	S _{min}	in. (mm)	2.0 (51)	2.6 (66)	2.6 (66)	3.5 (89)	4.1 (104)	4 (102)





Table 2 - Thread engagement measurements for various thread diameters

Anchor	Plastic Housing Color	Threaded Rod Diameter (in)	Thread Engagement Length (Ith) (in)
1/4"-3/8" WF/PD	Green	1/4	1.1
1/4 -3/6 WF/FD	Green	3/8	0.7
		1/4	1.4
1/4"-3/8"-1/2" WF	Black	3/8	1.2
		1/2	0.7
2/01/ 1/01/ WE/DD	Orongo	3/8	1.5
3/8"-1/2" WF/PD	Orange	1/2	0.9
		3/8	1.9
3/8"-1/2"-5/8" WF/PD	Red	1/2	1.5
		5/8	0.9
		3/8	2.8
0/01/ 4/01/ 5/01/ 0/41/ 14/5/00		1/2	2.3
3/8"-1/2"-5/8"-3/4" WF/PD	Grey	5/8	1.7
		3/4	0.9
E/QII Q/AII IME	Cross	5/8	1.4
5/8"-3/4" WF	Grey	3/4	0.9



INSTALLATION INSTRUCTIONS

Installation Instructions For Use (IFU) are included with each product package. They can also be viewed or downloaded online at www.hilti.com (US), or www.hilti.ca (Canada). Because of the possibility of changes, always verify that downloaded IFU are current when used. Proper installation is critical to achieve full performance. Training is available on request. Contact Hilti Technical Services for applications and conditions not addressed in the IFU.

Figure 2—KCM-PD Anchor

¹ Minimum anchor spacing values correspond to 4d_a for an un-torqued anchor as specified by ACI 318-19 17.9.2



DESIGN DATA IN CONCRETE PER ACI 318

ACI 318-14 Chapter 17 Design

The technical data contained in this section are Hilti Simplified Design Tables. The load values were developed using the Strength Design parameters and variables of ESR-4145 and the equations within ACI 318-19 Chapter17. For a detailed explanation of the Hilti Simplified Design Tables, refer to section 3.1.8 of Volume 2: Anchor Fastening Technical Guide Ed. 22 (PTG Ed. 22) Data tables from ESR-4145 are not contained in this section, but can be found at www.icc-es.org or at www.hilti.com.

Table 3 - Design strength for steel failure of KCM-WF and KCM-PD inserts^{1,2,3}

DESIGN INFORMATION	1/4"	-3/8"	1/4	1"-3/8"-	1/2"	3/8"	-1/2"	3/	/8"-1/2"-	5/8"	;	3/8"-1/2	"-5/8"-3	/4"	5/8"	3/4"
Insert type	WF	PD		WF/PD		W	/F		WF/PD			W	F/PD		W	/F
Nominal rod diameter (in)	1/4	3/8	1/4	3/8	1/2	3/8	1/2	3/8	1/2	5/8	3/8	1/2 4	5/8 4	3/4	5/8	3/4
Design steel strength of insert in tension, $\Phi N_{\text{sa,insert}}$ lb (kN)		315 3.6)		8,035 (35.7))35 5.7)		10,920 (48.6)				7,795 79.2)		14,6 (65	
Design seismic steel strength of insert in tension, $\Phi N_{\text{sa,insert,eq}}$ lb (kN)	-	5,315 (23.6)	-	8,035 (35.7)	8,035 (35.7)	8,035 (35.7)	8,035 (35.7)	-	10,920 (48.6)	10,920 (48.6)	-	17,795 (79.2)	17,795 (79.2)	17,795 (79.2)	14,625 (65.1)	14,625 (65.1)
Design steel strength of insert in shear, $\Phi V_{\text{sa,insert}}$ lb (kN)	-	1,775 (7.9)	-	2,080 (9.3)	3,490 (15.5)	2,000 (8.9)	3,490 (15.5)	-	3,650 (16.2)	5,785 (25.7)	-	4,955 (22.0)	8,245 (36.7)	11,140 (49.6)	6,230 (27.7)	6,635 (29.5)
Design seismic steel strength of insert in shear, $\Phi V_{\text{sa,insert,eq}} \mid b \; (kN)$	-	1,775 (7.9)	-	1,250 (5.6)	1,775 (7.9)	1,200 (5.3)	3,490 (15.5)	-	2,555 (11.4)	5,785 (25.7)	-	4,955 (22.0)	8,245 (36.7)	11,140 (49.6)	3,740 (16.6)	6,635 (29.5)

¹ See Hilti Product Technical Guide, Edition 22 (PTG ED.22) Section 3.1.8.6 to convert design strength value to ASD value.

Table 4 - Hilti KCM-WF and KCM-PD cast-in insert design strength with concrete/pullout failure in uncracked concrete 1,2,3,4,5,6

				Tensio	n - φN _n			Shear	r - φV _n	
Nominal anchor internal diameter	Plastic Housing Color	Effective embedment depth in. (mm)	f' _c = 2,500 psi (17.2 MPa) Ib (kN)	f' _c = 3,000 psi (20.7 MPa) Ib (kN)	f' _c = 4,000 psi (27.6 MPa) Ib (kN)	f' _c = 6,000 psi (41.1 MPa) Ib (kN)	f' _c = 2,500 psi (17.2 MPa) Ib (kN)	f' _c = 3,000 psi (20.7 MPa) Ib (kN)	f' _c = 4,000 psi (27.6 MPa) Ib (kN)	f' _c = 6,000 psi (41.1 MPa) Ib (kN)
1/4"-3/8"	Green	1.12 (28)	1,240 (5.5)	1,355 (6.0)	1,570 (7.0)	1,920 (8.5)	1,240 (5.5)	1,355 (6.0)	1,570 (7.0)	1,920 (8.5)
1/4'-3/8'-1/2'	Black	1.63 (41)	2,180 (9.7)	2,390 (10.6)	2,760 (12.3)	3,380 (15.0)	2,180 (9.7)	2,390 (10.6)	2,760 (12.3)	3,380 (15.0)
3/8"-1/2"	Orange	1.63 (41)	2,180 (9.7)	2,390 (10.6)	2,760 (12.3)	3,380 (15.0)	2,180 (9.7)	2,390 (10.6)	2,760 (12.3)	3,380 (15.0)
3/8"-1/2"-5/8"	Red	2.04 (52)	3,055 (13.6)	3,345 (14.9)	3,865 (17.2)	4,735 (21.1)	3,055 (13.6)	3,345 (14.9)	3,865 (17.2)	4,735 (21.1)
3/8"-1/2"-5/8"-3/4"	Grey	3.00 (76)	5,455 (24.3)	5,975 (26.6)	6,900 (30.7)	8,450 (37.6)	10,910 (48.5)	11,950 (53.2)	13,800 (61.4)	16,900 (75.2)
5/8"-3/4"	Grey	2.50 (76)	4,150 (18.5)	4,545 (20.2)	5,250 (23.4)	6,425 (28.6)	8,300 (36.9)	9,090 (40.4)	10,500 (46.7)	12,855 (57.2)

¹ See Hilti Product Technical Guide, Edition 22 (PTG ED.22) Section 3.1.8.6 to convert design strength value to ASD value.

July 2023

² Hilti KCM-WF/PD Inserts are considered as brittle steel elements

³ Values are for the insert only. The capacity of the threaded rod must be also be determined from Table 6. The design strength of concrete must be in accordance with ACI 318-19 Chapter 17 and Tables 4 to 5 as necessary. Compare the values (threaded rod, inserts, and concrete). The lesser of the values is to be used for the design.

⁴ Only threaded rods ASTM A193 Grade B7, ASTM A325, or ASTM F1554 Grade 105 are allowed to be used with the insert

² Linear interpolation between concrete compressive strengths is not permitted.

³ Tabular values are for single anchors located at edge distance (c) and spacing (s) greater than 3h_{ef}. For anchors with edge distance or spacing less than 3h_{ef} use ACI 318 to calculate load reduction factor. Compare the calculated value to the steel values (threaded rod and inserts) in Tables 3 And 6. The lesser of the values is to be used for the design.

⁴ Tabular values are for normal weight concrete only. For lightweight concrete multiply design strength by $λ_a$ as follows: For sand-lightweight, $λ_a$ = 0.85. For all-lightweight, $λ_a$ = 0.75.

⁵ Tabular values are for static loads only. Seismic design is not permitted for uncracked concrete. For seismic tension loads, multiply cracked concrete tabular values in tension by α_{N,seis} = 0.75. No reduction needed for seismic shear.

⁶ Compare tabular value to the insert steel strength values in Table 3 and threaded rod steel strength values in Table 6. The lesser of the values is to be used for the design.

Table 5 - Hilti KCM-WF and KCM-PD cast-in insert design strength with concrete / pullout failure in cracked concrete 1,2,3,4,5,6

				Tensio	n - φN _n			Shear	r - φ V _n	
Nominal anchor internal diameter	Plastic Housing Color	Effective embedment depth in. (mm)	f' _c = 2,500 psi (17.2 MPa) Ib (kN)	f' _c = 3,000 psi (20.7 MPa) Ib (kN)	f' _c = 4,000 psi (27.6 MPa) lb (kN)	f' _c = 6,000 psi (41.1 MPa) lb (kN)	f' _c = 2,500 psi (17.2 MPa) Ib (kN)	f' _c = 3,000 psi (20.7 MPa) Ib (kN)	f' _c = 4,000 psi (27.6 MPa) Ib (kN)	f' _c = 6,000 psi (41.1 MPa) Ib (kN)
1/4"-3/8"	Green	1.12 (28)	990 (4.4)	1,085 (4.8)	1,255 (5.6)	1,535 (6.8)	990 (4.4)	1,085 (4.8)	1,255 (5.6)	1,535 (6.8)
1/4"-3/8"-1/2"	Black	1.63 (41)	1,745 (7.8)	1,910 (8.5)	2,210 (9.8)	2,705 (12.0)	1,745 (7.8)	1,910 (8.5)	2,210 (9.8)	2,705 (12.0)
3/8"-1/2"	Orange	1.63 (41)	1,745 (7.8)	1,910 (8.5)	2,210 (9.8)	2,705 (12.0)	1,745 (7.8)	1,910 (8.5)	2,210 (9.8)	2,705 (12.0)
3/8"-1/2"-5/8"	Red	2.04 (52)	2,445 (10.9)	2,675 (11.9)	3,090 (13.7)	3,785 (16.8)	2,445 (10.9)	2,675 (11.9)	3,090 (13.7)	3,785 (16.8)
3/8"-1/2"-5/8"-3/4"	Grey	3.00 (76)	4,360 (19.4)	4,780 (21.3)	5,520 (24.6)	6,760 (30.1)	8,725 (38.8)	9,560 (42.5)	11,040 (49.1)	13,520 (60.1)
5/8"-3/4"	Grey	2.50 (76)	3,320 (14.8)	3,635 (16.2)	5,250 (23.4)	6,425 (28.6)	6,640 (29.5)	7,270 (32.3)	10,500 (46.7)	12,855 (57.2)

¹ See Hilti Product Technical Guide, Edition 22 (PTG ED.22) Section 3.1.8.6 to convert design strength value to ASD value.

Table 6 - Design strength for steel failure of common threaded rods^{1,5}

	Grad	le A36 threade	d rod	ASTM A 193	B7 or ASTM F threaded rod	1554 Gr. 105	ASTM A 3	07, Grade A th	readed rod
Nominal rod diameter in.	Tensile ² φN _{sa,rod} or φN _{sa,eq,rod} lb (kN)	Shear³ φV _{sa,rod} Ib (kN)	Seismic Shear ⁴ φV _{sa,eq,rod} Ib (kN)	Tensile ² φN _{sa,rod} or φN _{sa,eq,rod} lb (kN)	Shear³ φV _{sa,rod} Ib (kN)	Seismic Shear ⁴ φV _{sa,eq,rod} Ib (kN)	Tensile ² φN _{sa,rod} or φN _{sa,eq,rod} lb (kN)	Shear³ $\phi V_{sa,rod}$ Ib (kN)	Seismic Shear ⁴ φV _{sa,eq,rod} Ib (kN)
1/4	1,390	720	505	3,000	1,550	1,085	1,425	740	518
	(6.2)	(3.2)	(2.2)	(13.3)	(6.9)	(4.8)	(6.3)	(3.3)	(2.3)
3/8	3,395	1,750	1,225	7,315	3,780	2,646	3,490	1,815	1,271
	(15.1)	(7.8)	(5.4)	(32.5)	(16.8)	(11.8)	(15.5)	(8.1)	(5.7)
1/2	6,175	3,210	2,245	13,315	6,915	4,841	6,375	3,315	2,321
	(27.5)	(14.3)	(10.0)	(59.2)	(30.8)	(21.5)	(28.4)	(14.7)	(10.3)
5/8	9,835	5,110	3,575	21,190	11,020	7,714	10,165	5,285	3,700
	(43.7)	(22.7)	(15.9)	(94.3)	(49.0)	(34.3)	(45.2)	(23.5)	(16.5)
3/4	14,550	7,565	5,295	31,405	16,305	11,414	15,040	7,820	5,474
	(64.7)	(33.7)	(23.6)	(139.7)	(72.5)	(50.8)	(66.9)	(34.8)	(24.3)

¹ See Hilti Product Technical Guide, (PTG ED 22, Section 3.1.8.7 for additional information on seismic applications.

² Linear interpolation between concrete compressive strengths is not permitted.

³ Tabular values are for single anchors located at edge distance (c) and spacing (s) greater than 3h_{et}. For anchors with edge distance or spacing less than 3h_{et} use ACI 318 to calculate load reduction factor. Compare the calculated value to the steel values (threaded rod and inserts) in Tables 3 and 6. The lesser of the values is to be used for the design.

⁴ Tabular values are for normal weight concrete only. For lightweight concrete multiply design strength by λ_a as follows: For sand-lightweight, λ_a = 0.85.

For all-lightweight, $\lambda_a = 0.75$.

⁵ Tabular values are for static loads only. Seismic design is not permitted for uncracked concrete. For seismic tension loads, multiply cracked concrete tabular values in tension by $\alpha_{\text{N,seis}}$ = 0.75. No reduction needed for seismic shear.

⁶ Compare tabular value to the insert steel strength values in Table 3 and threaded rod steel strength values in Table 6. The lesser of the values is to be used for the design.

Tensile values determined by static tension tests with $\phi N_{sa} = \phi A_{se,N} f_{uta}$ as noted in ACI 318-19 Chapter 17.

Shear values determined by static shear tests with $\phi V_{sa} = \phi 0.60 A_{se,V} f_{uta}$ as noted in ACI 318-19 Chapter 17.

Seismic shear values determined by seismic shear tests with $\phi V_{sa} = \phi 0.60 A_{se,V} f_{uta}$ as noted in ACI 318-19, Chapter 17.

Values are for the threaded rod only. The capacity of the insert must be also be determined from Table 3. The design strength of concrete must be in accordance with ACI 318-19 Chapter 17 and Tables 4 to 5 as necessary. Compare the values (threaded rod, inserts, and concrete). The lesser of the values is to be used for the design.



DESIGN DATA IN CONCRETE PER CSA A23.3



CSA A23.3-14 Annex D design

Limit State Design of anchors is described in the provisions of CSA A23.3-14 Annex D for post-installed and cast in anchors tested and assessed in accordance with ACI 355.2 for mechanical anchors and ACI 355.4 for adhesive anchors. This section contains the Limit State Design tables with unfactored characteristic loads that are based on the published loads in ICC Evaluation Services ESR-4145. These tables are followed by factored resistance tables. The factored resistance tables have characteristic design loads that are prefactored by the applicable reduction factors for a single anchor with no anchor-to-anchor spacing or edge distance adjustments for the convenience of the user of this document. All the figures in the previous ACI 318-19 Chapter 17 design section are applicable to Limit State Design and the tables will reference these figures.

For a detailed explanation of the tables developed in accordance with CSA A23.3-14 Annex D, refer to Section 3.1.8 of Volume 2: Anchor Fastening Technical Guide Ed. 22. Technical assistance is available by contacting Hilti Canada at (800) 363-4458 or at www.hilti.ca.

Table 7 - Hilti KCM-WF/PD insert design information in accordance with CSA A23.3-14 (R2014) Annex D 1

									Nom	inal an	chor d	liamet	er						Ref
Design parameter	Symbol	Units	1/4"-	3/8"	1/4"	'-3/8"-	1/2"	3/8"	-1/2"	3/8"	-1/2"-	5/8"	3/8	3"-1/2"	-5/8"-3,	/4"	5/8"	-3/4"	A23.3-14
Plastic Housing Color	-	-	Gre	en		Black		Ora	nge		Red			G	rey		Gı	rey	
Nominal rod diameter	d _a	in.	1/4	3/8	1/4	3/8	1/2	3/8	1/2	3/8	1/2	5/8	3/8	1/2 4	5/8 4	3/4	5/8	3/4	
Effective embedment	h _{ef}	in. (mm)	1.1			1.63 (41)			63 ·1)		2.04 (52)				3 76)			.5 '6)	
Steel embed. material resistance factor for reinforcement	Φ _s	-								().85								8.4.3
Resistance modification factor for tension, steel failure modes ²	R	-								().70								D.5.3
Resistance modification factor for shear, steel failure modes ²	R	-								().65								D.5.3
Factored steel resistance in tension	N _{sar}	lb (kN)	4,864 (21.6)	4,864 (21.6)	7,357 (32.7)	7,357 (32.7)	7,357 (32.7)	7,357 (32.7)							16,291 (72.4)		13,388 (59.5)		
Factored steel resistance in tension	N _{sar,eq}	lb (kN)		4,864 (21.6)			7,357 (32.7)	7,357 (32.7)				9,996 (44.4)		16,291 (72.4)	16,291 (72.4)	16,291 (72.4)	13,388 (59.5)	13,388 (59.5)	D.6.1.2
Factored steel resistance in shear	V _{sar}	lb (kN)	-	1,633 (7.3)	-	1,917 (8.5)	3,216 (14.3)	1,843 (8.2)	3,216 (14.3)	-	3,362 (14.9)	5,326 (23.7)	-	4,564 (20.3)	7,595 (33.8)	10,260 (45.6)	5,738 (25.5)	6,108 (27.1)	D.7.1.2
Factored steel resistance in shear, seismic	V _{sar,eq}	lb (kN)		1,633 (7.3)			3,216 (14.3)		3,216 (14.3)			5,326 (23.7)		4,564 (20.3)	7,594 (33.7)		3,442 (15.3)	6,108 (27.1)	D.7.1.2
Coeff. for factored conc. breakout resistance, uncracked concrete	k _{c,uncr}	-									10								D.6.2.2
Coeff. for factored conc. breakout resistance, cracked concrete	k _{c,cr}	-									10								D.6.2.2
Modification factor for anchor resistance, tension, uncracked conc.	$\psi_{\text{c,N}}$	-								1	.25								D.6.2.6
Modification factor for anchor resistance, tension, cracked conc.	Ψ _{c,N}	-									1.0								D.6.2.6
Anchor category	-	-								Ca	st-in								D.5.3 (c)
Concrete material resistance factor	Фс	-								().65								8.4.2
Resistance modification factor for tension and shear, concrete failure modes, Condition B ³	R	-						1.00						D.5.3 (c)					

¹ Design information in this table is taken from ICC-ES ESR-4145, and converted for use with CSA A23.3-14 (R2014) Annex D.

² The carbon steel KCM-WF/PD is considered a brittle steel element as defined by CSA A23.3-14 (R2014) Annex D section D.2.

³ For use with the load combinations of CSA A23.3-14 (R2014) chapter 8. Condition B applies where supplementary reinforcement in conformance with CSA A23.3-14 (R2014) section D.5.3 is not provided, or where pullout or pryout strength governs. For cases where the presence of supplementary reinforcement can be verified, the resistance modification factors associated with Condition A may be used.

³ Values are for the insert only. The capacity of the threaded rod must be also be determined from Table 10. The design strength of concrete must be in accordance with CSA A23.3-14 (R2014) and Tables 8 to 9 as necessary. Compare the values (threaded rod, inserts, and concrete). The lesser of the values is to be used for the design.

⁴ Only threaded rods ASTM A193 Grade B7, ASTM A325, or ASTM F1554 Grade 105 are allowed to be used with the insert



Table 8 - Hilti KCM-WF/PD cast-in insert design strength with concrete / pullout failure in uncracked concrete 1,2,3,4,5

				Tensi	on - N _r			Shea	ar - V _r	
Nominal anchor diameter in. (mm)	Plastic Housing Color	Effective embed. in. (mm)	f' = 20 MPa (2,900 psi) Ib (kN)	f' = 25 MPa (3,625 psi) Ib (kN)	f' = 30 MPa (4,350 psi) Ib (kN)	f' = 40 MPa (5,800 psi) Ib (kN)	f' = 20 MPa (2,900 psi) Ib (kN)	f' = 25 MPa (3,625 psi) Ib (kN)	f' = 30 MPa (4,350 psi) Ib (kN)	f' = 40 MPa (5,800 psi) Ib (kN)
1/4"-3/8"	Green	1.12 (28)	1,235 (5.5)	1,380 (6.1)	1,515 (6.7)	1,750 (7.8)	1,235 (5.5)	1,380 (6.1)	1,515 (6.7)	1,750 (7.8)
1/4"-3/8"-1/2"	Black	1.63 (41)	2,175 (9.7)	2,435 (10.8)	2,665 (11.9)	3,075 (13.7)	2,175 (9.7)	2,435 (10.8)	2,665 (11.9)	3,075 (13.7)
3/8"-1/2"	Orange	1.63 (41)	2,175 (9.7)	2,435 (10.8)	2,665 (11.9)	3,075 (13.7)	2,175 (9.7)	2,435 (10.8)	2,665 (11.9)	3,075 (13.7)
3/8"-1/2"-5/8"	Red	2.04 (52)	3,045 (13.6)	3,405 (15.2)	3,730 (16.6)	4,305 (19.2)	3,045 (13.6)	3,405 (15.2)	3,730 (16.6)	4,305 (19.2)
3/8"-1/2"-5/8"-3/4"	Grey	3.00 (76)	5,435 (24.2)	6,075 (27.0)	6,655 (29.6)	7,685 (34.2)	10,865 (48.3)	12,150 (54.1)	13,310 (59.2)	15,370 (68.4)
5/8"-3/4"	Grey	2.50 (64)	4,135 (18.4)	4,620 (20.6)	5,060 (22.5)	5,845 (26.0)	4,135 (18.4)	4,620 (20.6)	5,060 (22.5)	5,845 (26.0)

Table 9 - Hilti KCS-WF/PD cast-in insert design strength with concrete / pullout failure in cracked concrete 1.2.3.4.5

				Tensio	on - N _r			Shea	ır - V _r	
Nominal anchor diameter in. (mm)	Plastic Housing Color	Effective embed. in. (mm)	f' = 20 MPa (2,900 psi) Ib (kN)	f' = 25 MPa (3,625 psi) Ib (kN)	f' = 30 MPa (4,350 psi) Ib (kN)	f' = 40 MPa (5,800 psi) Ib (kN)	f' = 20 MPa (2,900 psi) Ib (kN)	f' = 25 MPa (3,625 psi) Ib (kN)	f' = 30 MPa (4,350 psi) Ib (kN)	f' = 40 MPa (5,800 psi) Ib (kN)
1/4"-3/8"	Green	1.12 (28)	990 (4.4)	1,105 (4.9)	1,210 (5.4)	1,400 (6.2)	990 (4.4)	1,105 (4.9)	1,210 (5.4)	1,400 (6.2)
1/4"-3/8"-1/2"	Black	1.63 (41)	1,740 (7.7)	1,945 (8.7)	2,130 (9.5)	2,460 (10.9)	1,740 (7.7)	1,945 (8.7)	2,130 (9.5)	2,460 (10.9)
3/8"-1/2"	Orange	1.63 (41)	1,740 (7.7)	1,945 (8.7)	2,130 (9.5)	2,460 (10.9)	1,740 (7.7)	1,945 (8.7)	2,130 (9.5)	2,460 (10.9)
3/8"-1/2"-5/8"	Red	2.04 (52)	2,435 (10.8)	2,725 (12.1)	2,985 (13.3)	3,445 (15.3)	2,435 (10.8)	2,725 (12.1)	2,985 (13.3)	3,445 (15.3)
3/8"-1/2"-5/8"-3/4"	Grey	3.00 (76)	4,345 (19.3)	4,860 (21.6)	5,325 (23.7)	6,145 (27.3)	8,695 (38.7)	9,720 (43.3)	10,650 (47.4)	12,295 (54.7)
5/8"-3/4"	Grey	2.50 (64)	3,305 (14.7)	3,695 (16.4)	4,050 (18.0)	4,675 (20.8)	3,305 (14.7)	3,695 (16.4)	4,050 (18.0)	4,675 (20.8)

¹ See Hilti Product Technical Guide, Edition 22 (PTG ED.22) Section 3.1.8.6 to convert design strength value to ASD value.

² Linear interpolation between concrete compressive strengths is not permitted.

 ³ Tabular values are for single anchor located at edge distance (c) and spacing (s) greated than 24". For anchors with edge distance or spacing less than 24" use CSA A23.3 to calculate load reduction factors. Compare the value to the steel values in Tables 7 and 10. The lesser of the values is to be used for the design.
 4 Tablular values are for normal weight concrete only. For lightweight concrete multiply design strength by λ_a as follows: For sand-lightweight, λ_a = 0.85; for all-lightweight, λ_a = 0.75.

⁵ Tabular values are for static loads only. Seismic design is not permitted for uncracked concrete. For seismic loads, multiply cracked concrete tabular values by $\alpha_{N.seis} = 0.75$.



Table 10 - Design strength for steel failure of common threaded rods used with KCM-WF/PD cast-in inserts 1.2.3



	Grad	le A36 threade	d rod	ASTM A 193	B B7 or ASTM F threaded rod	1554 Gr. 105	ASTM A 3	07, Grade A th	readed rod
Nominal rod diameter in.	Tensile ⁴ φN _{sa,rod} or φN _{sa,eq,rod} lb (kN)	Shear ⁵ φV _{sa,rod} lb (kN)	Seismic Shear ⁶ φV _{sa,eq,rod} Ib (kN)	Tensile ⁴ φN _{sa,rod} or φN _{sa,eq,rod} lb (kN)	Shear ^s φV _{sa,rod} lb (kN)	Seismic Shear ⁶ φV _{sa,eq,rod} Ib (kN)	Tensile ⁴ φN _{sa,rod} or φN _{sa,eq,rod} lb (kN)	Shear⁵ φV _{sa,rod} lb (kN)	Seismic Shear ⁶ φV _{sa,eq,rod} Ib (kN)
1/4	1,260	705	495	2,720	1,520	1,064	1,290	725	508
	(5.6)	(3.1)	(2.2)	(12.1)	(6.8)	(4.7)	(5.7)	(3.2)	(2.3)
3/8	3,075	1,720	1,205	6,630	3,705	2,594	3,160	1,780	1,246
	(13.7)	(7.7)	(5.4)	(29.5)	(16.5)	(11.5)	(14.1)	(7.9)	(5.5)
1/2	5,600	3,150	2,205	12,070	6,785	4,750	5,780	3,250	2,275
	(24.9)	(14.0)	(9.8)	(53.7)	(30.2)	(21.1)	(25.7)	(14.5)	(10.1)
5/8	8,915	5,010	3,505	19,210	10,805	7,564	9,215	5,185	3,630
	(39.7)	(22.3)	(15.6)	(85.4)	(48.1)	(33.6)	(41.0)	(23.1)	(16.1)
3/4	13,190	7,420	5,195	28,475	15,990	11,193	13,635	7,670	5,369
	(58.7)	(33.0)	(23.1)	(126.7)	(71.1)	(49.8)	(60.7)	(34.1)	(23.9)

¹ See section 3.1.8.6 of Product Technical Guide Volume 2 Edition 22 (PTG ED 22) to convert design strength value to ASD value.

Table 11 - UL LLC and FM approvals^{1,2}

Design information	١	1/4"-3/8 WF and		1/	4"-3/8"- Only W	<u> </u>		3/8"-1/2 Only W		-	/8"-1/2" WF and		,	·1/2"-5/8 VF and I			5/8"-3/4 Only Wi	
Nominal rod diameter	UL max pipe size (in.)	UL test load (lb)	FM max pipe size (in.)															
3/8	4	1,500	4	4	1,500	4	4	1,500	4	4	1,500	4	4	1,500	4	-	-	-
1/2	-	-	-	8	4,050	8	8	4,050	8	8	4,050	8	8	4,050	8	-	-	-
5/8	-	-	-	-	-	-	-	-	-	8	4,050	8	12	7,900	12	12	7,900	12
3/4	-	-	-	-	-	-	-	-	-	-	-	-	12	7,900	12	12	7,900	12

¹ UL LLC Listing based on successful completion of testing in accordance with UL 203

8 July 2023

Hilti KCM-WF/PD anchors are to be considered brittle steel elements
 See Section 3.1.8.7 of Product Technical Guide Volume 2 Edition 22 (PTG ED 22) for additional information on seismic applications.

⁴ Tensile $N_{sar} = \varphi_s A_{sa} R f_{tut}$ as noted in CSA A23.3-14 Annex D.
⁵ Shear values determined by static shear tests with $V_{sar} < \varphi_s 0.60 A_{se,v} f_{tut} R$. as noted in CSA A23.3-14 Annex D.
⁶ Seismic shear values determined by seismic shear tests with $V_{sar,eq} < \varphi_s 0.60 A_{se,v} f_{tut} R$. as noted in CSA A23.3-14 Annex D.

² FM Approval based on succesful completion of testing in accordance with FM 1952

ORDERING INFORMATION¹

KCM - WF cast-in anchor for use in wood forms

Description	Sleeve color	Qty / box
KCM-WF 1/4"-3/8"	Green	250
KCM-WF 1/4"-3/8"-1/2"	Black	150
KCM-WF 3/8"-1/2"	Orange	150
KCM-WF 3/8"-1/2"-5/8"	Red	100
KCM-WF 3/8"-1/2"-5/8"-3/4"	Grey	25
KCM-WF 5/8"-3/4"	Grey	75

KCM - PD cast-in anchor for use in pan joist deck

Description	Sleeve color	Qty / box
KCM-PD 1/4"-3/8"	Green	250
KCM-PD 3/8"-1/2"-5/8"	Red	100
KCM-PD 3/8"-1/2"-5/8"-3/4"	Grey	25

¹ All dimensions in inches



Hilti, Inc. (U.S.) Legacy Tower, Suite 1000 7250 Dallas Parkway | Plano, TX 75024 www.facebook.com/HiltiNorthAmerica www.hilti.com Customer Service: 1-800-879-8000 Hilti (Canada) Corporation 2360 Meadowpine Blvd. Mississauga, Ontario, L5N 6S2 www.facebook.com/HiltiNorthAmerica www.hilti.ca Customer Service: 1-800-363-4458