

Klübersynth GH 6-460 (H)

Version	Revision Date:	Date of last issue: -	Print Date:
1.0	05/26/2021	Date of first issue: 05/26/2021	02/15/2022

SECTION 1. IDENTIFICATION

Product name : Klübersynth GH 6-460 (H)

Article-No. : 012402

Manufacturer or supplier's details

Company name of supplier : Klüber Lubrication NA LP
9010 CR 2120
Tyler, Texas 75707
Phone: (903) 534-8021
Fax: (903) 581-4376

32 Industrial Drive
Londonderry, NH 03053
Phone: (603) 647-4104
Fax: (603) 647-4106

E-mail address of person : mcm@us.kluber.com
responsible for the SDS Material Compliance Management

Emergency telephone num- : +1-517-545-7070 NCEC
ber

Recommended use of the chemical and restrictions on use

Recommended use : Lubricating oil

Restrictions on use : Restricted to professional users.

SECTION 2. HAZARDS IDENTIFICATION

GHS classification in accordance with the OSHA Hazard Communication Standard (29 CFR 1910.1200)

Not a hazardous substance or mixture.

GHS label elements

This chemical is not considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200).

Other hazards

None known.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance / Mixture : Mixture

Chemical nature : polyalkylene glycol oil

Klübersynth GH 6-460 (H)

Version 1.0	Revision Date: 05/26/2021	Date of last issue: - Date of first issue: 05/26/2021	Print Date: 02/15/2022
----------------	------------------------------	--	---------------------------

Components

No hazardous ingredients

SECTION 4. FIRST AID MEASURES

- | | |
|---|--|
| If inhaled | : Remove person to fresh air. If signs/symptoms continue, get medical attention.
Keep patient warm and at rest.
If unconscious, place in recovery position and seek medical advice.
Keep respiratory tract clear.
If breathing is irregular or stopped, administer artificial respiration. |
| In case of skin contact | : Remove contaminated clothing. If irritation develops, get medical attention.
In case of contact, immediately flush skin with plenty of water.
Wash clothing before reuse.
Thoroughly clean shoes before reuse. |
| In case of eye contact | : Rinse immediately with plenty of water, also under the eyelids, for at least 10 minutes.
If eye irritation persists, consult a specialist. |
| If swallowed | : Move the victim to fresh air.
If unconscious, place in recovery position and seek medical advice.
Keep respiratory tract clear.
Do NOT induce vomiting.
Rinse mouth with water.
Never give anything by mouth to an unconscious person. |
| Most important symptoms and effects, both acute and delayed | : No information available.
None known. |
| Notes to physician | : No information available. |

SECTION 5. FIREFIGHTING MEASURES

- | | |
|--------------------------------|--|
| Suitable extinguishing media | : Use water spray, alcohol-resistant foam, dry chemical or carbon dioxide. |
| Unsuitable extinguishing media | : High volume water jet |
| Hazardous combustion prod- | : Carbon oxides |

Klübersynth GH 6-460 (H)

Version 1.0	Revision Date: 05/26/2021	Date of last issue: - Date of first issue: 05/26/2021	Print Date: 02/15/2022
----------------	------------------------------	--	---------------------------

ucts	Nitrogen oxides (NO _x)
Further information	: Standard procedure for chemical fires. Collect contaminated fire extinguishing water separately. This must not be discharged into drains.
Special protective equipment for firefighters	: In the event of fire, wear self-contained breathing apparatus. Use personal protective equipment. Exposure to decomposition products may be a hazard to health.

SECTION 6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures	: Evacuate personnel to safe areas. Use personal protective equipment. Ensure adequate ventilation. Refer to protective measures listed in sections 7 and 8.
Environmental precautions	: Do not allow contact with soil, surface or ground water. Prevent further leakage or spillage if safe to do so. If the product contaminates rivers and lakes or drains inform respective authorities.
Methods and materials for containment and cleaning up	: Contain spillage, and then collect with non-combustible absorbent material, (e.g. sand, earth, diatomaceous earth, vermiculite) and place in container for disposal according to local / national regulations (see section 13).

SECTION 7. HANDLING AND STORAGE

Advice on safe handling	: Avoid inhalation of vapour or mist. Avoid contact with skin and eyes. For personal protection see section 8. Smoking, eating and drinking should be prohibited in the application area. Wash hands and face before breaks and immediately after handling the product. Do not ingest. Do not repack. Do not re-use empty containers. These safety instructions also apply to empty packaging which may still contain product residues. Keep container closed when not in use.
Conditions for safe storage	: Store in original container. Keep container closed when not in use. Keep in a dry, cool and well-ventilated place. Containers which are opened must be carefully resealed and kept upright to prevent leakage.

Klübersynth GH 6-460 (H)

Version	Revision Date:	Date of last issue: -	Print Date:
1.0	05/26/2021	Date of first issue: 05/26/2021	02/15/2022

Store in accordance with the particular national regulations.
Keep in properly labelled containers.

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Components with workplace control parameters

Contains no substances with occupational exposure limit values.

Engineering measures : none

Personal protective equipment

Respiratory protection : Not required; except in case of aerosol formation.

Filter type : Filter type A-P

Hand protection

Material : Nitrile rubber

Break through time : > 10 min

Protective index : Class 1

Remarks : For prolonged or repeated contact use protective gloves. The break through time depends amongst other things on the material, the thickness and the type of glove and therefore has to be measured for each case.

Eye protection : Safety glasses with side-shields

Protective measures : The type of protective equipment must be selected according to the concentration and amount of the dangerous substance at the specific workplace.
Choose body protection in relation to its type, to the concentration and amount of dangerous substances, and to the specific work-place.

Hygiene measures : Wash face, hands and any exposed skin thoroughly after handling.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance : liquid

Colour : yellow

Odour : characteristic

Odour Threshold : No data available

Klübersynth GH 6-460 (H)

Version 1.0	Revision Date: 05/26/2021	Date of last issue: - Date of first issue: 05/26/2021	Print Date: 02/15/2022
----------------	------------------------------	--	---------------------------

pH	:	No data available
Melting point/range	:	No data available
Boiling point/boiling range	:	No data available
Flash point	:	> 482 °F / 250 °C
		Method: open cup
Evaporation rate	:	No data available
Flammability (solid, gas)	:	Not applicable
Self-ignition	:	No data available
Upper explosion limit / Upper flammability limit	:	No data available
Lower explosion limit / Lower flammability limit	:	No data available
Vapour pressure	:	< 0.001 hPa (68 °F / 20 °C)
Relative vapour density	:	No data available
Relative density	:	1.07 (68 °F / 20 °C) Reference substance: Water The value is calculated
Bulk density	:	No data available
Solubility(ies)		
Water solubility	:	soluble
Solubility in other solvents	:	No data available
Partition coefficient: n-octanol/water	:	No data available
Auto-ignition temperature	:	No data available
Decomposition temperature	:	No data available
Viscosity		
Viscosity, dynamic	:	No data available
Viscosity, kinematic	:	460 mm ² /s (104 °F / 40 °C)
Explosive properties	:	Not explosive

Klübersynth GH 6-460 (H)

Version 1.0	Revision Date: 05/26/2021	Date of last issue: - Date of first issue: 05/26/2021	Print Date: 02/15/2022
----------------	------------------------------	--	---------------------------

Oxidizing properties : No data available

Sublimation point : No data available

SECTION 10. STABILITY AND REACTIVITY

Reactivity : No hazards to be specially mentioned.

Chemical stability : Stable under normal conditions.

Possibility of hazardous reactions : No dangerous reaction known under conditions of normal use.

Conditions to avoid : No conditions to be specially mentioned.

Incompatible materials : No materials to be especially mentioned.

Hazardous decomposition products : No decomposition if stored and applied as directed.

SECTION 11. TOXICOLOGICAL INFORMATION

Acute toxicity

Product:

Acute oral toxicity : Remarks: This information is not available.

Acute inhalation toxicity : Remarks: This information is not available.

Acute dermal toxicity : Remarks: This information is not available.

Skin corrosion/irritation

Product:

Remarks : This information is not available.

Serious eye damage/eye irritation

Product:

Remarks : This information is not available.

Respiratory or skin sensitisation

Product:

Remarks : This information is not available.

Klübersynth GH 6-460 (H)

Version 1.0	Revision Date: 05/26/2021	Date of last issue: - Date of first issue: 05/26/2021	Print Date: 02/15/2022
----------------	------------------------------	--	---------------------------

Germ cell mutagenicity

Product:

Genotoxicity in vitro : Remarks: No data available

Genotoxicity in vivo : Remarks: No data available

Carcinogenicity

Product:

Remarks : No data available

IARC No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

**IARC
OSHA** No component of this product present at levels greater than or equal to 0.1% is on OSHA's list of regulated carcinogens.

NTP No component of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.

Reproductive toxicity

Product:

Effects on fertility : Remarks: No data available

Effects on foetal development : Remarks: No data available

Repeated dose toxicity

Product:

Remarks : This information is not available.

Aspiration toxicity

Product:

This information is not available.

Further information

Product:

Remarks : Information given is based on data on the components and the toxicology of similar products.

Klübersynth GH 6-460 (H)

Version 1.0	Revision Date: 05/26/2021	Date of last issue: - Date of first issue: 05/26/2021	Print Date: 02/15/2022
----------------	------------------------------	--	---------------------------

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity

Product:

Toxicity to fish : Remarks: Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Toxicity to daphnia and other aquatic invertebrates : Remarks: No data available

Toxicity to algae/aquatic plants : Remarks: No data available

Toxicity to microorganisms : Remarks: No data available

Persistence and degradability

Product:

Biodegradability : Remarks: No data available

Physico-chemical removability : Remarks: No data available

Bioaccumulative potential

Product:

Bioaccumulation : Remarks: This mixture contains no substance considered to be persistent, bioaccumulating and toxic (PBT). This mixture contains no substance considered to be very persistent and very bioaccumulating (vPvB).

Mobility in soil

Product:

Mobility : Remarks: No data available

Distribution among environmental compartments : Remarks: No data available

Other adverse effects

Product:

Ozone-Depletion Potential : Regulation: 40 CFR Protection of Environment; Part 82 Protection of Stratospheric Ozone - CAA Section 602 Class I Substances
Remarks: This product neither contains, nor was manufactured with a Class I or Class II ODS as defined by the U.S. Clean Air Act Section 602 (40 CFR 82, Subpt. A, App.A + B).

Klübersynth GH 6-460 (H)

Version	Revision Date:	Date of last issue: -	Print Date:
1.0	05/26/2021	Date of first issue: 05/26/2021	02/15/2022

Additional ecological information : Harmful to aquatic life with long lasting effects.

SECTION 13. DISPOSAL CONSIDERATIONS

Disposal methods

Waste from residues : The product should not be allowed to enter drains, water courses or the soil.
Do not dispose of with domestic refuse.
Dispose of as hazardous waste in compliance with local and national regulations.

Contaminated packaging : Packaging that is not properly emptied must be disposed of as the unused product.
Dispose of waste product or used containers according to local regulations.

SECTION 14. TRANSPORT INFORMATION

International Regulations

UNRTDG

Not regulated as a dangerous good

IATA-DGR

Not regulated as a dangerous good

IMDG-Code

Not regulated as a dangerous good

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not applicable for product as supplied.

National Regulations

49 CFR

Not regulated as a dangerous good

SECTION 15. REGULATORY INFORMATION

EPCRA - Emergency Planning and Community Right-to-Know Act

CERCLA Reportable Quantity

This material does not contain any components with a CERCLA RQ.

SARA 304 Extremely Hazardous Substances Reportable Quantity

This material does not contain any components with a section 304 EHS RQ.

Klübersynth GH 6-460 (H)

Version	Revision Date:	Date of last issue: -	Print Date:
1.0	05/26/2021	Date of first issue: 05/26/2021	02/15/2022

SARA 302 Extremely Hazardous Substances Threshold Planning Quantity

This material does not contain any components with a section 302 EHS TPQ.

SARA 311/312 Hazards : No SARA Hazards

SARA 313 : This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

Clean Air Act

This product neither contains, nor was manufactured with a Class I or Class II ODS as defined by the U.S. Clean Air Act Section 602 (40 CFR 82, Subpt. A, App.A + B).

This product does not contain any hazardous air pollutants (HAP), as defined by the U.S. Clean Air Act Section 112 (40 CFR 61).

This product does not contain any chemicals listed under the U.S. Clean Air Act Section 112(r) for Accidental Release Prevention (40 CFR 68.130, Subpart F).

This product does not contain any chemicals listed under the U.S. Clean Air Act Section 111 SOCM Intermediate or Final VOC's (40 CFR 60.489).

Clean Water Act

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311, Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311, Table 117.3.

This product does not contain any toxic pollutants listed under the U.S. Clean Water Act Section 307

This product does not contain any priority pollutants related to the U.S. Clean Water Act

US State Regulations

Massachusetts Right To Know

No components are subject to the Massachusetts Right to Know Act.

Pennsylvania Right To Know

Glycols, polyethylene-polypropylene, RC 102 9003-11-6

Maine Chemicals of High Concern

Product does not contain any listed chemicals

Vermont Chemicals of High Concern

Product does not contain any listed chemicals

Washington Chemicals of High Concern

Triphenyl phosphate 115-86-6
tris(methylphenyl) phosphate 1330-78-5

TSCA list

No substances are subject to a Significant New Use Rule.

No substances are subject to TSCA 12(b) export notification requirements.

Klübersynth GH 6-460 (H)

Version	Revision Date:	Date of last issue: -	Print Date:
1.0	05/26/2021	Date of first issue: 05/26/2021	02/15/2022

SECTION 16. OTHER INFORMATION**Further information****Full text of other abbreviations**

AIIC - Australian Inventory of Industrial Chemicals; ASTM - American Society for the Testing of Materials; bw - Body weight; CERCLA - Comprehensive Environmental Response, Compensation, and Liability Act; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DOT - Department of Transportation; DSL - Domestic Substances List (Canada); ECx - Concentration associated with x% response; EHS - Extremely Hazardous Substance; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; ERG - Emergency Response Guide; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; HMIS - Hazardous Materials Identification System; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisation for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; MSHA - Mine Safety and Health Administration; n.o.s. - Not Otherwise Specified; NFPA - National Fire Protection Association; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NTP - National Toxicology Program; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; RCRA - Resource Conservation and Recovery Act; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; RQ - Reportable Quantity; SADT - Self-Accelerating Decomposition Temperature; SARA - Superfund Amendments and Reauthorization Act; SDS - Safety Data Sheet; TCSI - Taiwan Chemical Substance Inventory; TSCA - Toxic Substances Control Act (United States); UN - United Nations; UNRTDG - United Nations Recommendations on the Transport of Dangerous Goods; vPvB - Very Persistent and Very Bioaccumulative

Revision Date : 05/26/2021

This safety data sheet applies only to products as originally packed and labelled. The information contained therein may not be reproduced or modified without our express written permission. Any forwarding of this document is only permitted to the extent required by law. Any further, in particular public, dissemination of the safety data sheet (e.g. as a document for download from the Internet) is not permitted without our express written consent. We provide our customers with amended safety data sheets as prescribed by law. The customer is responsible for passing on safety data sheets and any amendments contained therein to its own customers, employees and other users of the product. We provide no guarantee that safety data sheets received by users

Klübersynth GH 6-460 (H)

Version	Revision Date:	Date of last issue: -	Print Date:
1.0	05/26/2021	Date of first issue: 05/26/2021	02/15/2022

from third parties are up-to-date. All information and instructions in this safety data sheet have been compiled to the best of our knowledge and are based on the information available to us on the day of publication. The information provided is intended to describe the product in relation to the required safety measures; it is neither an assurance of characteristics nor a guarantee of the product's suitability for particular applications and does not justify any contractual legal relationship. The existence of a safety data sheet for a particular jurisdiction does not necessarily mean that import or use within that jurisdiction is legally permitted. If you have any questions, please contact your responsible sales contact or authorized trading partner.