

# CP 506 / CS-ADH ACR 310

## Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

Revision date: 10/24/2025

Issue date: 10/24/2025

Supersedes: 6/20/2024

Version: 5.0

### SECTION 1: Identification

#### 1.1. Identification

Product form	Mixture
Product name	CP 506 / CS-ADH ACR 310
Product code	BU Fire Protection

#### 1.2. Other means of identification

No additional information available

#### 1.3. Recommended use of the chemical and restrictions on use

Use of the substance/mixture	: sealant
Recommended use	: Adhesives, sealants

#### 1.4. Supplier's details

##### Supplier

Hilti, Inc.  
Legacy Tower, Suite 1000  
7250 Dallas Parkway  
US TX 75024 Plano  
USA  
T +1 9724035800  
1-800-879-8000 toll free, F +1 918 254 0522  
[us-sales@hilti.com](mailto:us-sales@hilti.com)

##### Department issuing data specification sheet

Hilti AG  
Feldkircher Strasse  
FL 9494 Schaan  
Liechtenstein  
T +423 234 2111  
[product.compliance-fire.protection@hilti.com](mailto:product.compliance-fire.protection@hilti.com)

#### 1.5. Emergency phone number

Emergency number	Emergency CONTACT (24-Hour-Number) GBK/Infotrac ID 101022 (USA domestic) 1 800 535 5053 or international (001) 352 323 3500
------------------	--

### SECTION 2: Hazard(s) identification

#### 2.1. Classification of the substance or mixture

##### GHS-US classification

Not classified

#### 2.2. GHS Label elements, including precautionary statements

##### GHS US labelling

No labelling applicable

#### 2.3. Hazards associated with known or reasonably anticipated uses

No additional information available

#### 2.4. Hazards not otherwise classified

No additional information available

#### 2.5. Unknown acute toxicity (GHS US)

Not applicable

# CP 506 / CS-ADH ACR 310

## Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

### SECTION 3: Composition/information on ingredients

#### 3.1. Substances

Not applicable

#### 3.2. Mixtures

Name	Product identifier	%	GHS-US classification
Calcium carbonate	CAS-No.: 1317-65-3	40 – 60	Not classified
glycerol	CAS-No.: 56-81-5	1 – 2.5	Not classified

Full text of hazard classes and H-statements : see section 16

### SECTION 4: First-aid measures

#### 4.1. Description of first aid measures

First-aid measures general	Never give anything by mouth to an unconscious person. If you feel unwell, seek medical advice (show the label where possible).
First-aid measures after inhalation	Remove person to fresh air and keep comfortable for breathing. Allow affected person to breathe fresh air. Allow the victim to rest.
First-aid measures after skin contact	Remove affected clothing and wash all exposed skin area with mild soap and water, followed by warm water rinse. Wash skin with plenty of water.
First-aid measures after eye contact	Rinse eyes with water as a precaution.
First-aid measures after ingestion	Rinse mouth. Do NOT induce vomiting. Obtain emergency medical attention. Call a poison center or a doctor if you feel unwell.

#### 4.2. Most important symptoms and effects (acute and delayed)

Potential adverse human health effects and symptoms	Based on available data, the classification criteria are not met.
Symptoms/effects	Not expected to present a significant hazard under anticipated conditions of normal use.
Symptoms/effects after inhalation	None under normal conditions.
Symptoms/effects after skin contact	None under normal conditions.
Symptoms/effects after eye contact	None under normal conditions.
Symptoms/effects after ingestion	None under normal conditions.

#### 4.3. Immediate medical attention and special treatment, if necessary

Treat symptomatically.

### SECTION 5: Fire-fighting measures

#### 5.1. Suitable (and unsuitable) extinguishing media

Suitable extinguishing media	Foam. Dry powder. Carbon dioxide. Water spray. Sand.
Unsuitable extinguishing media	Do not use a heavy water stream.

#### 5.2. Specific hazards arising from the chemical

Fire hazard	No fire hazard.
Explosion hazard	No direct explosion hazard.
Hazardous decomposition products in case of fire	Carbon dioxide. Carbon monoxide.

#### 5.3. Special protective equipment and precautions for fire-fighters

Firefighting instructions	Use water spray or fog for cooling exposed containers. Exercise caution when fighting any chemical fire. Prevent fire fighting water from entering the environment. Do not enter fire area without proper protective equipment, including respiratory protection.
---------------------------	---

# CP 506 / CS-ADH ACR 310

## Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

Protection during firefighting

Do not enter fire area without proper protective equipment, including respiratory protection. Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

General measures : Stop leak if safe to do so. Notify authorities if product enters sewers or public waters. Absorb spillage to prevent material damage.

#### For non-emergency personnel

Protective equipment : Wear recommended personal protective equipment.  
Emergency procedures : Ventilate spillage area. Evacuate unnecessary personnel.

#### For emergency responders

Protective equipment : Do not attempt to take action without suitable protective equipment. Equip cleanup crew with proper protection. For further information refer to section 8: "Exposure controls/personal protection".  
Emergency procedures : Ventilate area. Evacuate unnecessary personnel. Stop leak if safe to do so.

Environmental precautions : Avoid release to the environment. Prevent entry to sewers and public waters. Notify authorities if liquid enters sewers or public waters.

### 6.2. Methods and materials for containment and cleaning up

For containment : Absorb spilled material with sand or earth. Contain any spills with dikes or absorbents to prevent migration and entry into sewers or streams. Stop leak without risks if possible.  
Methods for cleaning up : Take up liquid spill into absorbent material. Soak up spills with inert solids, such as clay or diatomaceous earth as soon as possible. Collect spillage. Store away from other materials.  
Other information : Dispose of materials or solid residues at an authorized site.

See Section 8, Exposure controls and personal protection, For further information refer to section 13

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Additional hazards when processed : Not expected to present a significant hazard under anticipated conditions of normal use.  
Precautions for safe handling : Ensure good ventilation of the work station. Wear personal protective equipment. Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work. Provide good ventilation in process area to prevent formation of vapour.  
Hygiene measures : Do not eat, drink or smoke when using this product. Always wash hands after handling the product.

### 7.2. Conditions for safe storage, including any incompatibilities

Technical measures : Keep in a cool, well-ventilated place away from heat.  
Storage conditions : Keep only in the original container in a cool, well ventilated place away from : Keep container closed when not in use.  
Incompatible products : Strong bases. Strong acids.  
Incompatible materials : Sources of ignition. Direct sunlight.  
Storage temperature : 41 – 77 °F  
Packaging materials : Store always product in container of same material as original container.

# CP 506 / CS-ADH ACR 310

## Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

### SECTION 8: Exposure controls/personal protection

#### 8.1. Control parameters

CP 506 / CS-ADH ACR 310	
No additional information available	
Calcium carbonate (1317-65-3)	
No additional information available	
USA - OSHA - Occupational Exposure Limits	
Local name	Calcium Carbonate (Limestone; Marble)
OSHA PEL TWA	15 mg/m <sup>3</sup> (Total dust) 5 mg/m <sup>3</sup> (Respirable fraction)
Regulatory reference (US-OSHA)	OSHA Annotated Table Z-1
glycerol (56-81-5)	
No additional information available	
USA - ACGIH - Occupational Exposure Limits	
Local name	Glycerin mist
Remark (ACGIH®)	URT irr
USA - OSHA - Occupational Exposure Limits	
Local name	Glycerin (mist)
OSHA PEL TWA	15 mg/m <sup>3</sup> (Total dust) 5 mg/m <sup>3</sup> (Respirable fraction)
Regulatory reference (US-OSHA)	OSHA Annotated Table Z-1

Additional information : The product has a pasty consistency. Exposure limit values for respirable dusts are not relevant for this product.

#### 8.2. Appropriate engineering controls

Appropriate engineering controls Ensure good ventilation of the work station.  
Environmental exposure controls Avoid release to the environment.

#### 8.3. Individual protection measures/Personal protective equipment

##### Personal protective equipment:

Avoid all unnecessary exposure. Protective goggles. Gloves. Protective clothing.

Hand protection:				
Wear protective gloves. Suitable for short-term work or as a splash guard: Nitrile rubber gloves (> 0.1 mm). In case of permanent product contact:				
Type	Material	Permeation	Thickness (mm)	Penetration
Disposable gloves	Nitrile rubber (NBR)	3 (> 60 minutes)	>0,4	
Eye protection:				
Chemical goggles or safety glasses. Use eye protection according to EN 166.				

# CP 506 / CS-ADH ACR 310

## Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

<b>Skin and body protection:</b>
Wear suitable protective clothing
<b>Respiratory protection:</b>
No respiratory protection needed under normal use conditions

### Personal protective equipment symbol(s):



### Other information:

Do not eat, drink or smoke during use.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

Physical state	Liquid
Appearance	Pasty.
Colour	Colourless
Odour	characteristic
Odour threshold	Not determined
pH	Not determined
Melting point	Not applicable
Freezing point	No data available
Boiling point	> 100 °C
Flash point	> 100 °C
Relative evaporation rate (butylacetate=1)	No data available
Flammability (solid, gas)	Non flammable.
Vapour pressure	23 hPa
Relative vapour density at 20°C	No data available
Relative density	No data available
Density	1.5 – 1.6 g/cm <sup>3</sup>
Molecular mass	Not determined
Solubility	No data available
Partition coefficient n-octanol/water (Log Pow)	No data available
Auto-ignition temperature	No data available
Decomposition temperature	No data available
Viscosity, kinematic	No data available
Viscosity, dynamic	No data available
Explosive limits	No data available
Explosive properties	No data available
Oxidising properties	No data available

### 9.2. Other information

VOC content	43.21 g/l ASTM D 2369 – 20, SCAQMD 1168 / All Other Architectural Sealants (limit 50g/L)
-------------	--

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

# CP 506 / CS-ADH ACR 310

## Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

### 10.2. Chemical stability

Not established.

### 10.3. Possibility of hazardous reactions

Not established.

### 10.4. Conditions to avoid

Direct sunlight. Extremely high or low temperatures.

### 10.5. Incompatible materials

Strong acids. Strong bases.

### 10.6. Hazardous decomposition products

fume. Carbon monoxide. Carbon dioxide.

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

Acute toxicity (oral)	Not classified
Acute toxicity (dermal)	Not classified
Acute toxicity (inhalation)	Not classified

Calcium carbonate (1317-65-3)	
LD50 oral rat	> 5000 mg/kg
glycerol (56-81-5)	
LD50 oral rat	27200 mg/kg (OECD 401: Acute Oral Toxicity, Rat, Female, Experimental value, Oral, 10 day(s))
LD50 dermal	56750 mg/kg (4 day(s), Guinea pig, Male / female, Experimental value, Dermal, 14 day(s))
LC50 Inhalation - Rat	> 5.85 mg/l (Equivalent or similar to OECD 412, 4 h, Rat, Male / female, Experimental value, Inhalation (aerosol), 14 day(s))

Skin corrosion/irritation	Not classified pH: Not determined
Serious eye damage/irritation	Not classified pH: Not determined
Respiratory or skin sensitisation	Not classified
Germ cell mutagenicity	Not classified
Carcinogenicity	Not classified
Reproductive toxicity	Not classified
STOT-single exposure	Not classified
STOT-repeated exposure	Not classified
Aspiration hazard	Not classified
Viscosity, kinematic	No data available
Potential adverse human health effects and symptoms	Based on available data, the classification criteria are not met.
Symptoms/effects	Not expected to present a significant hazard under anticipated conditions of normal use.
Symptoms/effects after inhalation	None under normal conditions.
Symptoms/effects after skin contact	None under normal conditions.
Symptoms/effects after eye contact	None under normal conditions.
Symptoms/effects after ingestion	None under normal conditions.

# CP 506 / CS-ADH ACR 310

## Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

### SECTION 12: Ecological information

#### 12.1. Toxicity

Ecology - general

The product is not considered harmful to aquatic organisms nor to cause long-term adverse effects in the environment.

Calcium carbonate (1317-65-3)	
LC50 - Fish [1]	> 10000 mg/l (Oncorhynchus mykiss (rainbow trout))
EC50 - Crustacea [1]	> 1000 mg/l (Daphnia magna (Water flea))
EC50 72h - Algae [1]	289 mg/l Desmodesmus subspicatus (green algae)
NOEC chronic algae	75 mg/l
glycerol (56-81-5)	
LC50 - Fish [1]	54000 mg/l (96 h, Oncorhynchus mykiss, Static system, Fresh water, Experimental value, Lethal)
EC50 - Crustacea [1]	> 10000 mg/l (24 h, Daphnia magna, Static system, Fresh water, Experimental value, Locomotor effect)

#### 12.2. Persistence and degradability

CP 506 / CS-ADH ACR 310	
Persistence and degradability	Not established.
glycerol (56-81-5)	
Not rapidly degradable	
Persistence and degradability	Readily biodegradable in water.

#### 12.3. Bioaccumulative potential

CP 506 / CS-ADH ACR 310	
Bioaccumulative potential	Not established.
glycerol (56-81-5)	
Partition coefficient n-octanol/water (Log Pow)	-1.75 (Experimental value, Equivalent or similar to OECD 107, 25 °C)
Bioaccumulative potential	Not bioaccumulative.

#### 12.4. Mobility in soil

glycerol (56-81-5)	
Surface tension	63 mN/m (20 °C, 1000 g/l)
Organic Carbon Normalized Adsorption Coefficient (Log Koc)	0 (log Koc, SRC PCKOCWIN v2.0, Calculated value)
Ecology - soil	Highly mobile in soil.

#### 12.5. Other adverse effects

Other information

Avoid release to the environment.

# CP 506 / CS-ADH ACR 310

## Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

### SECTION 13: Disposal considerations

#### 13.1. Disposal methods

Regional waste regulation	Disposal must be done according to official regulations.
Waste treatment methods	Dispose in a safe manner in accordance with local/national regulations. Dispose of contents/container in accordance with licensed collector's sorting instructions.
Sewage disposal recommendations	Disposal must be done according to official regulations.
Product/Packaging disposal recommendations	Recycle the material as far as possible. Dispose in a safe manner in accordance with local/national regulations. Disposal must be done according to official regulations.
Additional information	Do not re-use empty containers.
Ecological waste information	Avoid release to the environment.

### SECTION 14: Transport information

In accordance with DOT / TDG / IMDG / IATA

DOT	TDG	IMDG	IATA
<b>14.1. UN number</b>			
Not regulated for transport			
<b>14.2. Proper Shipping Name</b>			
Not applicable	Not applicable	Not applicable	Not applicable
<b>14.3. Transport hazard class(es)</b>			
Not applicable	Not applicable	Not applicable	Not applicable
<b>14.4. Packing group</b>			
Not applicable	Not applicable	Not applicable	Not applicable
<b>14.5. Environmental hazards</b>			
Dangerous for the environment: No	Dangerous for the environment: No	Dangerous for the environment: No Marine pollutant: No	Dangerous for the environment: No
No supplementary information available			

#### 14.6. Special precautions for user

**DOT**  
No data available

**TDG**  
No data available

**IMDG**  
No data available

**IATA**  
No data available

#### 14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable

# CP 506 / CS-ADH ACR 310

## Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

### SECTION 15: Regulatory information

#### 15.1. US Federal regulations

All components of this product are present and listed as Active on the United States Environmental Protection Agency Toxic Substances Control Act (TSCA) inventory

#### 15.2. International regulations

No additional information available

#### 15.3. US State regulations

California Proposition 65 - This product does not contain any substances known to the state of California to cause cancer, developmental and/or reproductive harm

### SECTION 16: Other information

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

Revision date

10/24/2025

Data sources

REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006.

Other information

None.

Abbreviations and acronyms	
ACGIH	American Conference of Government Industrial Hygienists
ADN	European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways
ADR	European Agreement concerning the International Carriage of Dangerous Goods by Road
ATE	Acute Toxicity Estimate
BCF	Bioconcentration factor
BLV	Biological limit value
BOD	Biochemical oxygen demand (BOD)
CAS-No.	Chemical Abstract Service number
CLP	Classification Labelling Packaging Regulation; Regulation (EC) No 1272/2008
COD	Chemical oxygen demand (COD)
CSA	Chemical safety assessment
DMEL	Derived Minimal Effect level
DNEL	Derived-No Effect Level
EC-No.	European Community number
EC50	Median effective concentration
ED	Endocrine disruptor
EN	European Standard
EWG	European waste catalogue

# CP 506 / CS-ADH ACR 310

## Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

Abbreviations and acronyms	
IARC	International Agency for Research on Cancer
IATA	International Air Transport Association
IMDG	International Maritime Dangerous Goods
LC50	Median lethal concentration
LD50	Median lethal dose
LOAEL	Lowest Observed Adverse Effect Level
Log Kow	Partition coefficient n-octanol/water (Log Kow)
Log Pow	Partition coefficient n-octanol/water (Log Pow)
MAK	maximum workplace concentration
NOAEC	No-Observed Adverse Effect Concentration
NOAEL	No-Observed Adverse Effect Level
NOEC	No-Observed Effect Concentration
N.O.S.	Not Otherwise Specified
OECD	Organisation for Economic Co-operation and Development
OEL	Occupational Exposure Limit
OSHA	Occupational Safety Health Administration
PBT	Persistent Bioaccumulative Toxic
PNEC	Predicted No-Effect Concentration
PPE	Personal protection equipment
RID	Regulations concerning the International Carriage of Dangerous Goods by Rail
SDS	Safety Data Sheet
STP	Sewage treatment plant
TF	Technical function
ThOD	Theoretical oxygen demand (ThOD)
TLM	Median Tolerance Limit
TWA	Time Weighted Average
VOC	Volatile Organic Compounds
vPvB	Very Persistent and Very Bioaccumulative
UFI	Unique Formula Identifier

NFPA health hazard

1 - Materials that, under emergency conditions, can cause significant irritation.

NFPA fire hazard

1 - Materials that must be preheated before ignition can occur.

# CP 506 / CS-ADH ACR 310

## Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

NFPA reactivity

Hazard Rating

Health

Flammability

Physical

Personal protection


0 - Material that in themselves are normally stable, even under fire conditions.

1 Slight Hazard - Irritation or minor reversible injury possible

1 Slight Hazard - Materials that must be preheated before ignition will occur. Includes liquids, solids and semi solids having a flash point above 200 F. (Class IIIB)

0 Minimal Hazard - Materials that are normally stable, even under fire conditions, and will NOT react with water, polymerize, decompose, condense, or self-react. Non-Explosives.

B - Safety glasses, Gloves



Indication of changes:			
Section	Changed item	Change	Comments
			29 CFR § 1910.1200, Hazard Communication Standard (HCS)

SDS\_US\_Hilti

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.