

CP 572

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

Revision date: 10/27/2025

Issue date: 10/27/2025

Supersedes: 9/11/2023

Version: 3.0

SECTION 1: Identification

1.1. Identification

Product form	Mixture
Product name	CP 572
Product code	BU Fire Protection



1.2. Other means of identification

No additional information available

1.3. Recommended use of the chemical and restrictions on use

Recommended use	: Adhesives, sealants
Restrictions on use	: For professional use only

1.4. Supplier's details

Supplier

Hilti, Inc.
Legacy Tower, Suite 1000
7250 Dallas Parkway
US TX 75024 Plano
USA
T +1 9724035800
1-800-879-8000 toll free, F +1 918 254 0522
us-sales@hilti.com

Department issuing data specification sheet

Hilti AG
Feldkircher Strasse
FL 9494 Schaan
Liechtenstein
T +423 234 2111
product.compliance-fire.protection@hilti.com

1.5. Emergency phone number

Emergency number	Emergency CONTACT (24-Hour-Number) GBK/Infotrac ID 101022 (USA domestic) 1 800 535 5053 or international (001) 352 323 3500
------------------	--

SECTION 2: Hazard(s) identification

2.1. Classification of the substance or mixture

GHS-US classification

Not classified

CP 572

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

2.2. GHS Label elements, including precautionary statements

GHS US labelling

No labelling applicable

2.3. Hazards associated with known or reasonably anticipated uses

No additional information available

2.4. Hazards not otherwise classified

No additional information available

2.5. Unknown acute toxicity (GHS US)

Not applicable

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	GHS-US classification
Calcium carbonate	CAS-No.: 1317-65-3	40 – 60	Not classified

Full text of hazard classes and H-statements : see section 16

SECTION 4: First-aid measures

4.1. Description of first aid measures

First-aid measures general	Never give anything by mouth to an unconscious person. If you feel unwell, seek medical advice (show the label where possible).
First-aid measures after inhalation	Remove person to fresh air and keep comfortable for breathing. Allow affected person to breathe fresh air. Allow the victim to rest. Get medical advice/attention if you feel unwell.
First-aid measures after skin contact	Remove affected clothing and wash all exposed skin area with mild soap and water, followed by warm water rinse. Wash skin with plenty of water. Take off contaminated clothing. If skin irritation or rash occurs: Get medical advice/attention.
First-aid measures after eye contact	Rinse immediately with plenty of water. Rinse eyes with water as a precaution.
First-aid measures after ingestion	Get medical advice/attention if you feel unwell. Rinse mouth. Do NOT induce vomiting. Call a poison center or a doctor if you feel unwell.

4.2. Most important symptoms and effects (acute and delayed)

Potential adverse human health effects and symptoms	Based on available data, the classification criteria are not met.
Symptoms/effects	Not expected to present a significant hazard under anticipated conditions of normal use.
Symptoms/effects after inhalation	None under normal conditions. Dust of the product, if present, may cause respiratory irritation after excessive inhalation exposure.
Symptoms/effects after skin contact	May cause an allergic skin reaction.
Symptoms/effects after eye contact	None under normal conditions. Dust from this product may cause eye irritation.
Symptoms/effects after ingestion	None under normal conditions.

4.3. Immediate medical attention and special treatment, if necessary

Treat symptomatically.

CP 572

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

SECTION 5: Fire-fighting measures

5.1. Suitable (and unsuitable) extinguishing media

Suitable extinguishing media	Water spray. Dry powder. Foam. Carbon dioxide. Sand.
Unsuitable extinguishing media	Do not use a heavy water stream.

5.2. Specific hazards arising from the chemical

Fire hazard	No fire hazard.
Explosion hazard	No direct explosion hazard.
Hazardous decomposition products in case of fire	Carbon dioxide. Carbon monoxide.

5.3. Special protective equipment and precautions for fire-fighters

Firefighting instructions	Use water spray or fog for cooling exposed containers. Exercise caution when fighting any chemical fire. Prevent fire fighting water from entering the environment. Do not enter fire area without proper protective equipment, including respiratory protection.
Protection during firefighting	Do not enter fire area without proper protective equipment, including respiratory protection. Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

General measures	: Notify authorities if product enters sewers or public waters. Absorb spillage to prevent material damage.
------------------	---

For non-emergency personnel

Protective equipment	: Wear recommended personal protective equipment.
Emergency procedures	: Ventilate spillage area. Evacuate unnecessary personnel. Avoid contact with skin and eyes. Avoid breathing dust/fume/gas/mist/vapours/spray.

For emergency responders

Protective equipment	: Do not attempt to take action without suitable protective equipment. Equip cleanup crew with proper protection. For further information refer to section 8: "Exposure controls/personal protection".
Emergency procedures	: Ventilate area. Evacuate unnecessary personnel.
Environmental precautions	: Avoid release to the environment. Prevent entry to sewers and public waters. Notify authorities if liquid enters sewers or public waters.

6.2. Methods and materials for containment and cleaning up

For containment	: Using a clean shovel, put the material in a dry container and cover without compressing it.
Methods for cleaning up	: Mechanically recover the product. Soak up spills with inert solids, such as clay or diatomaceous earth as soon as possible. Collect spillage. Store away from other materials.
Other information	: Dispose of materials or solid residues at an authorized site.

See Section 8, Exposure controls and personal protection, For further information refer to section 13

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Additional hazards when processed	Not expected to present a significant hazard under anticipated conditions of normal use.
-----------------------------------	--

CP 572

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

Precautions for safe handling

Ensure good ventilation of the work station. Wear personal protective equipment. Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work. Provide good ventilation in process area to prevent formation of vapour. Avoid contact with skin and eyes. Avoid breathing dust/fume/gas/mist/vapours/spray.

Hygiene measures

Wash contaminated clothing before reuse. Do not eat, drink or smoke when using this product. Always wash hands after handling the product. Contaminated work clothing should not be allowed out of the workplace.

7.2. Conditions for safe storage, including any incompatibilities

Technical measures

Keep in a cool, well-ventilated place away from heat.

Storage conditions

Keep cool. Store in a dry place. Keep container closed when not in use.

Incompatible products

Strong bases. Strong acids.

Incompatible materials

Sources of ignition. Direct sunlight.

Storage temperature

41 – 77 °F

Packaging materials

Store always product in container of same material as original container.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

CP 572	
No additional information available	
Calcium carbonate (1317-65-3)	
No additional information available	
USA - OSHA - Occupational Exposure Limits	
Local name	Calcium Carbonate (Limestone; Marble)
OSHA PEL TWA	15 mg/m ³ (Total dust) 5 mg/m ³ (Respirable fraction)
Regulatory reference (US-OSHA)	OSHA Annotated Table Z-1

Additional information : The product has a pasty consistency. Exposure limit values for respirable dusts are not relevant for this product.

8.2. Appropriate engineering controls

Appropriate engineering controls

Ensure good ventilation of the work station.

Environmental exposure controls

Avoid release to the environment.

8.3. Individual protection measures/Personal protective equipment

Personal protective equipment:

Protective clothing. Safety glasses. Gloves.

Hand protection:				
Wear protective gloves. Suitable for short-term work or as a splash guard: Nitrile rubber gloves (> 0.2 mm). In case of permanent product contact:				
Type	Material	Permeation	Thickness (mm)	Penetration
Disposable gloves	Nitrile rubber (NBR)	3 (> 60 minutes)	>0,4	
Eye protection:				
Chemical goggles or safety glasses. Use eye protection according to EN 166.				

CP 572

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

Skin and body protection:
Wear suitable protective clothing
Respiratory protection:
No respiratory protection needed under normal use conditions

Personal protective equipment symbol(s):



SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	Solid
Appearance	Pasty.
Colour	Various colours
Odour	slight
Odour threshold	Not determined
pH	Not applicable
Melting point	No data available
Freezing point	Not applicable
Boiling point	> 100 °C
Flash point	> 100 °C Not applicable
Relative evaporation rate (butylacetate=1)	No data available
Flammability (solid, gas)	Non flammable.
Vapour pressure	23 hPa(a)
Relative vapour density at 20°C	No data available
Relative density	No data available
Density	1.42 g/cm ³
Molecular mass	Not determined
Solubility	No data available
Partition coefficient n-octanol/water (Log Pow)	No data available
Auto-ignition temperature	Not applicable
Decomposition temperature	No data available
Viscosity, kinematic	Not applicable
Viscosity, dynamic	No data available
Explosive limits	Not applicable
Explosive properties	No data available
Oxidising properties	No data available

9.2. Other information

VOC content	< 20 mg/l
-------------	-----------

SECTION 10: Stability and reactivity

10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

10.2. Chemical stability

Not established.

CP 572

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

10.3. Possibility of hazardous reactions

Not established.

10.4. Conditions to avoid

Direct sunlight. Extremely high or low temperatures.

10.5. Incompatible materials

Strong acids. Strong bases.

10.6. Hazardous decomposition products

fume. Carbon monoxide. Carbon dioxide.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity (oral)	Not classified
Acute toxicity (dermal)	Not classified
Acute toxicity (inhalation)	Not classified

Calcium carbonate (1317-65-3)	
LD50 oral rat	> 5000 mg/kg
Skin corrosion/irritation	Not classified pH: Not applicable
Serious eye damage/irritation	Not classified pH: Not applicable
Respiratory or skin sensitisation	Not classified
Germ cell mutagenicity	Not classified
Carcinogenicity	Not classified
Reproductive toxicity	Not classified
STOT-single exposure	Not classified
STOT-repeated exposure	Not classified
Aspiration hazard	Not classified
Viscosity, kinematic	Not applicable
Potential adverse human health effects and symptoms	Based on available data, the classification criteria are not met.
Symptoms/effects	Not expected to present a significant hazard under anticipated conditions of normal use.
Symptoms/effects after inhalation	None under normal conditions. Dust of the product, if present, may cause respiratory irritation after excessive inhalation exposure.
Symptoms/effects after skin contact	May cause an allergic skin reaction.
Symptoms/effects after eye contact	None under normal conditions. Dust from this product may cause eye irritation.
Symptoms/effects after ingestion	None under normal conditions.

SECTION 12: Ecological information

12.1. Toxicity

Ecology - general	The product is not considered harmful to aquatic organisms nor to cause long-term adverse effects in the environment.
-------------------	---

Calcium carbonate (1317-65-3)	
LC50 - Fish [1]	> 10000 mg/l (Oncorhynchus mykiss (rainbow trout))
EC50 - Crustacea [1]	> 1000 mg/l (Daphnia magna (Water flea))

CP 572

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

Calcium carbonate (1317-65-3)	
EC50 72h - Algae [1]	289 mg/l Desmodesmus subspicatus (green algae)
NOEC chronic algae	75 mg/l

12.2. Persistence and degradability

CP 572	
Persistence and degradability	Not established.

12.3. Bioaccumulative potential

CP 572	
Bioaccumulative potential	Not established.

12.4. Mobility in soil

No additional information available

12.5. Other adverse effects

Other information Avoid release to the environment.

SECTION 13: Disposal considerations

13.1. Disposal methods

Regional waste regulation	Disposal must be done according to official regulations.
Waste treatment methods	Dispose in a safe manner in accordance with local/national regulations. Dispose of contents/container in accordance with licensed collector's sorting instructions.
Sewage disposal recommendations	Disposal must be done according to official regulations.
Product/Packaging disposal recommendations	Dispose in a safe manner in accordance with local/national regulations. Disposal must be done according to official regulations.
Additional information	Do not re-use empty containers.
Ecological waste information	Avoid release to the environment.

SECTION 14: Transport information

In accordance with DOT / TDG / IMDG / IATA

DOT	TDG	IMDG	IATA
14.1. UN number			
Not regulated for transport			
14.2. Proper Shipping Name			
Not applicable	Not applicable	Not applicable	Not applicable
14.3. Transport hazard class(es)			
Not applicable	Not applicable	Not applicable	Not applicable
14.4. Packing group			
Not applicable	Not applicable	Not applicable	Not applicable

CP 572

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

DOT	TDG	IMDG	IATA
14.5. Environmental hazards			
Dangerous for the environment: No	Dangerous for the environment: No	Dangerous for the environment: No Marine pollutant: No	Dangerous for the environment: No
No supplementary information available			

14.6. Special precautions for user

DOT

No data available

TDG

No data available

IMDG

No data available

IATA

No data available

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. US Federal regulations

All components of this product are present and listed as Active on the United States Environmental Protection Agency Toxic Substances Control Act (TSCA) inventory

15.2. International regulations

No additional information available

15.3. US State regulations

CP 572	
U.S. - California - Proposition 65 - Other information	ethanediol; ethylene glycol

WARNING:

This product can expose you to ethanediol; ethylene glycol, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

SECTION 16: Other information

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

Revision date

10/27/2025

Data sources

REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006.

Other information

None.

CP 572

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

Abbreviations and acronyms	
ACGIH	American Conference of Government Industrial Hygienists
ADN	European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways
ADR	European Agreement concerning the International Carriage of Dangerous Goods by Road
ATE	Acute Toxicity Estimate
BCF	Bioconcentration factor
BLV	Biological limit value
BOD	Biochemical oxygen demand (BOD)
CAS-No.	Chemical Abstract Service number
CLP	Classification Labelling Packaging Regulation; Regulation (EC) No 1272/2008
COD	Chemical oxygen demand (COD)
CSA	Chemical safety assessment
DMEL	Derived Minimal Effect level
DNEL	Derived-No Effect Level
EC-No.	European Community number
EC50	Median effective concentration
ED	Endocrine disruptor
EN	European Standard
EWC	European waste catalogue
IARC	International Agency for Research on Cancer
IATA	International Air Transport Association
IMDG	International Maritime Dangerous Goods
LC50	Median lethal concentration
LD50	Median lethal dose
LOAEL	Lowest Observed Adverse Effect Level
Log Kow	Partition coefficient n-octanol/water (Log Kow)
Log Pow	Partition coefficient n-octanol/water (Log Pow)
MAK	maximum workplace concentration
NOAEC	No-Observed Adverse Effect Concentration
NOAEL	No-Observed Adverse Effect Level
NOEC	No-Observed Effect Concentration
N.O.S.	Not Otherwise Specified
OECD	Organisation for Economic Co-operation and Development
OEL	Occupational Exposure Limit

CP 572

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)


Abbreviations and acronyms	
OSHA	Occupational Safety Health Administration
PBT	Persistent Bioaccumulative Toxic
PNEC	Predicted No-Effect Concentration
PPE	Personal protection equipment
RID	Regulations concerning the International Carriage of Dangerous Goods by Rail
SDS	Safety Data Sheet
STP	Sewage treatment plant
TF	Technical function
ThOD	Theoretical oxygen demand (ThOD)
TLM	Median Tolerance Limit
TWA	Time Weighted Average
VOC	Volatile Organic Compounds
vPvB	Very Persistent and Very Bioaccumulative
UFI	Unique Formula Identifier

NFPA health hazard

NFPA fire hazard

NFPA reactivity

0 - Materials that, under emergency conditions, would offer no hazard beyond that of ordinary combustible materials.
 0 - Materials that will not burn under typical fire conditions, including intrinsically noncombustible materials such as concrete, stone, and sand.
 0 - Material that in themselves are normally stable, even under fire conditions.



Hazard Rating

Health

Flammability

Physical

0 Minimal Hazard - No significant risk to health
 0 Minimal Hazard - Materials that will not burn
 0 Minimal Hazard - Materials that are normally stable, even under fire conditions, and will NOT react with water, polymerize, decompose, condense, or self-react. Non-Explosives.
 B - Safety glasses, Gloves

Personal protection

Indication of changes:			
Section	Changed item	Change	Comments
		Modified	29 CFR § 1910.1200, Hazard Communication Standard (HCS)

SDS_US_Hilti

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.