

FS-ONE MAX / CFS-FIL

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

Revision date: 10/28/2025

Issue date: 10/28/2025

Supersedes: 10/30/2024

Version: 2.0

SECTION 1: Identification

1.1. Identification

Product form	Mixture
Trade name	FS-ONE MAX / CFS-FIL
Product code	BU Fire Protection



1.2. Other means of identification

No additional information available

1.3. Recommended use of the chemical and restrictions on use

Use of the substance/mixture	Firestop intumescent sealant
Recommended use	Adhesives, sealants

1.4. Supplier's details

Supplier

Hilti, Inc.
Legacy Tower, Suite 1000
7250 Dallas Parkway
US TX 75024 Plano
USA
T +1 9724035800
1-800-879-8000 toll free, F +1 918 254 0522
us-sales@hilti.com

Department issuing data specification sheet

Hilti AG
Feldkircher Strasse 100
FL 9494 Schaan
Liechtenstein
T +423 234 2111
product.compliance-fire.protection@hilti.com

1.5. Emergency phone number

Emergency number	Emergency CONTACT (24-Hour-Number) GBK/Infotrac ID 101022 (USA domestic) 1 800 535 5053 or international (001) 352 323 3500
------------------	--

SECTION 2: Hazard(s) identification

2.1. Classification of the substance or mixture

GHS-US classification

Not classified

2.2. GHS Label elements, including precautionary statements

GHS US labelling

No labelling applicable

2.3. Hazards associated with known or reasonably anticipated uses

No additional information available

2.4. Hazards not otherwise classified

No additional information available

FS-ONE MAX / CFS-FIL

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

2.5. Unknown acute toxicity (GHS US)

Not applicable

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	GHS-US classification
Kaolin	CAS-No.: 1332-58-7	10 – 25	Not classified
fiberglass	CAS-No.: 65997-17-3	10 – 25	Not classified
Quartz (SiO ₂)	CAS-No.: 14808-60-7	2.5 – 5	Carc. 1A, H350 STOT RE 1, H372

Full text of hazard classes and H-statements : see section 16

SECTION 4: First-aid measures

4.1. Description of first aid measures

First-aid measures general	Never give anything by mouth to an unconscious person. If you feel unwell, seek medical advice (show the label where possible).
First-aid measures after inhalation	Get medical advice/attention if you feel unwell. Allow affected person to breathe fresh air. Allow the victim to rest.
First-aid measures after skin contact	Wash skin with plenty of water. If skin irritation occurs: Get medical advice/attention. Remove affected clothing and wash all exposed skin area with mild soap and water, followed by warm water rinse.
First-aid measures after eye contact	Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention. Rinse immediately with plenty of water. Obtain medical attention if pain, blinking or redness persists.
First-aid measures after ingestion	Get medical advice/attention if you feel unwell. Rinse mouth. Do NOT induce vomiting. Obtain emergency medical attention.

4.2. Most important symptoms and effects (acute and delayed)

Potential adverse human health effects and symptoms	Based on available data, the classification criteria are not met.
Symptoms/effects	Not expected to present a significant hazard under anticipated conditions of normal use.

4.3. Immediate medical attention and special treatment, if necessary

No additional information available

SECTION 5: Fire-fighting measures

5.1. Suitable (and unsuitable) extinguishing media

Suitable extinguishing media	Water spray. Dry powder. Foam. Carbon dioxide. Sand.
Unsuitable extinguishing media	Do not use a heavy water stream.

5.2. Specific hazards arising from the chemical

Hazardous decomposition products in case of fire	Carbon dioxide. Carbon monoxide.
--	----------------------------------

FS-ONE MAX / CFS-FIL

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

5.3. Special protective equipment and precautions for fire-fighters

Firefighting instructions	Use water spray or fog for cooling exposed containers. Exercise caution when fighting any chemical fire. Prevent fire fighting water from entering the environment.
Protection during firefighting	Self-contained breathing apparatus. Complete protective clothing. Do not enter fire area without proper protective equipment, including respiratory protection.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

For non-emergency personnel

Emergency procedures	Evacuate unnecessary personnel.
----------------------	---------------------------------

For emergency responders

Protective equipment	For further information refer to section 8: "Exposure controls/personal protection". Equip cleanup crew with proper protection.
Emergency procedures	Ventilate area.
Environmental precautions	Prevent entry to sewers and public waters. Notify authorities if liquid enters sewers or public waters.

6.2. Methods and materials for containment and cleaning up

Methods for cleaning up	Mechanically recover the product. On land, sweep or shovel into suitable containers. Minimise generation of dust. Store away from other materials.
-------------------------	--

For further information refer to section 13, See Section 8, Exposure controls and personal protection

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling	Wear personal protective equipment. Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work. Provide good ventilation in process area to prevent formation of vapour.
Hygiene measures	Wash contaminated clothing before reuse. Do not eat, drink or smoke when using this product. Always wash hands after handling the product.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions	Keep cool. Store in a dry place. Keep only in the original container in a cool, well ventilated place away from : Keep container closed when not in use.
Incompatible products	Strong bases. Strong acids.
Incompatible materials	Sources of ignition. Direct sunlight.
Storage temperature	41 – 77 °F

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

FS-ONE MAX / CFS-FIL

No additional information available

FS-ONE MAX / CFS-FIL

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

Quartz (SiO ₂) (14808-60-7)	
No additional information available	
USA - ACGIH - Occupational Exposure Limits	
Local name	Silica, crystalline, quartz
ACGIH® TLV® TWA	0.025 mg/m ³ (R - Respirable particulate matter)
Remark (ACGIH®)	TLV® Basis: Pulm fibrosis; lung cancer. Notations: A2 (Suspected Human Carcinogen)
Regulatory reference	ACGIH 2025
USA - OSHA - Occupational Exposure Limits	
Local name	Silica, crystalline quartz, respirable dust
Remark (OSHA)	(3) See Table Z-3.
Regulatory reference (US-OSHA)	OSHA Annotated Table Z-3 Mineral Dusts
fiberglass (65997-17-3)	
No additional information available	
USA - ACGIH - Occupational Exposure Limits	
ACGIH® TLV® TWA	1 fibers/cm ³ (Respirable fibers: length > 5 µm; aspect ratio ≥ 3:1, as determined by the membrane filter method at 400-450X magnification (4-mm objective), using phase-contrast illumination) 1 fibers/cm ³ (Respirable fibers: length > 5 µm; aspect ratio ≥ 3:1, as determined by the membrane filter method at 400-450X magnification (4-mm objective), using phase-contrast illumination) 5 mg/m ³ (Inhalable fraction)
Kaolin (1332-58-7)	
No additional information available	
USA - ACGIH - Occupational Exposure Limits	
Local name	Kaolin
ACGIH® TLV® TWA	2 mg/m ³ (Respirable fraction. The value is for particulate matter containing no asbestos and < 1% crystalline silica)
Remark (ACGIH®)	TLV® Basis: Pneumoconiosis. Notations: A4 (Not classifiable as a Human Carcinogen)
Regulatory reference	ACGIH 2025
USA - OSHA - Occupational Exposure Limits	
Local name	Kaolin
OSHA PEL TWA	15 mg/m ³ (Total dust) 5 mg/m ³ (Respirable fraction)
Regulatory reference (US-OSHA)	OSHA Annotated Table Z-1

Additional information The product has a pasty consistency. Exposure limit values for respirable dusts are not relevant for this product.

8.2. Appropriate engineering controls

No additional information available

FS-ONE MAX / CFS-FIL

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

8.3. Individual protection measures/Personal protective equipment

Personal protective equipment:

Protective clothing. Safety glasses. Gloves. Avoid all unnecessary exposure.

Hand protection:				
Wear suitable gloves tested to EN374. Suitable for short-term work or as a splash guard: Nitrile rubber gloves (> 0.1 mm). In case of permanent product contact:				
Type	Material	Permeation	Thickness (mm)	Penetration
Disposable gloves	Nitrile rubber (NBR)	6 (> 480 minutes)	>0,4	
Eye protection:				
Chemical goggles or safety glasses				
Skin and body protection:				
Wear suitable protective clothing				
Respiratory protection:				
When used in accordance with the instructions for use, no dust formation is expected. In case of dust formation use respirator with filter: P2				

Personal protective equipment symbol(s):



Other information:

Do not eat, drink or smoke during use.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	Solid
Appearance	Pasty.
Colour	red
Odour	characteristic
Odour threshold	Not determined
pH	≈ 7.85
Melting point	Not applicable
Freezing point	No data available
Boiling point	No data available
Flash point	Not applicable
Relative evaporation rate (butylacetate=1)	No data available
Flammability (solid, gas)	Not applicable. Non flammable.
Vapour pressure	No data available
Relative vapour density at 20°C	No data available
Relative density	No data available
Density	≈ 1.35 g/cm ³
Molecular mass	Not determined
Solubility	No data available
Partition coefficient n-octanol/water (Log Pow)	No data available
Auto-ignition temperature	No data available

FS-ONE MAX / CFS-FIL

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

Decomposition temperature	No data available
Viscosity, kinematic	No data available
Viscosity, dynamic	No data available
Explosive limits	No data available
Explosive properties	No data available
Oxidising properties	No data available

9.2. Other information

VOC content	< 1 g/l ASTM D 2369 – 20, SCAQMD 1168 / All Other Architectural Sealants (Ilimit 50g/L)
-------------	---

SECTION 10: Stability and reactivity

10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

10.2. Chemical stability

Stable under normal conditions. Not established.

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use. Not established.

10.4. Conditions to avoid

None under recommended storage and handling conditions (see section 7). Direct sunlight. Extremely high or low temperatures.

10.5. Incompatible materials

Strong acids. Strong bases.

10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced. fume. Carbon monoxide. Carbon dioxide.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity (oral)	Not classified
Acute toxicity (dermal)	Not classified
Acute toxicity (inhalation)	Not classified
Skin corrosion/irritation	Not classified pH: ≈ 7.85
Serious eye damage/irritation	Not classified pH: ≈ 7.85
Respiratory or skin sensitisation	Not classified
Germ cell mutagenicity	Not classified
Carcinogenicity	Not classified

Quartz (SiO ₂) (14808-60-7)	
IARC group	1 - Carcinogenic to humans
National Toxicology Program (NTP) Status	Known Human Carcinogens

Reproductive toxicity	Not classified
STOT-single exposure	Not classified
STOT-repeated exposure	Not classified

FS-ONE MAX / CFS-FIL

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

Quartz (SiO ₂) (14808-60-7)	
STOT-repeated exposure	Causes damage to organs through prolonged or repeated exposure.
Aspiration hazard	Not classified
Viscosity, kinematic	No data available
Potential adverse human health effects and symptoms	Based on available data, the classification criteria are not met.
Symptoms/effects	Not expected to present a significant hazard under anticipated conditions of normal use.

SECTION 12: Ecological information

12.1. Toxicity

Ecology - general	The product is not considered harmful to aquatic organisms nor to cause long-term adverse effects in the environment.
-------------------	---

12.2. Persistence and degradability

FS-ONE MAX / CFS-FIL	
Persistence and degradability	Not established.
Quartz (SiO ₂) (14808-60-7)	
Not rapidly degradable	
Persistence and degradability	Biodegradability: not applicable.
Chemical oxygen demand (COD)	Not applicable (inorganic)
ThOD	Not applicable (inorganic)
fiberglass (65997-17-3)	
Not rapidly degradable	
Persistence and degradability	Biodegradability: not applicable.
Chemical oxygen demand (COD)	Not applicable
ThOD	Not applicable
BOD (% of ThOD)	Not applicable
Kaolin (1332-58-7)	
Persistence and degradability	Biodegradability: not applicable.
Chemical oxygen demand (COD)	Not applicable (inorganic)
ThOD	Not applicable (inorganic)

12.3. Bioaccumulative potential

FS-ONE MAX / CFS-FIL	
Bioaccumulative potential	Not established.
Quartz (SiO ₂) (14808-60-7)	
Bioaccumulative potential	No bioaccumulation data available.

FS-ONE MAX / CFS-FIL

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

fiberglass (65997-17-3)	
Bioaccumulative potential	No bioaccumulation data available.

Kaolin (1332-58-7)	
Bioaccumulative potential	No bioaccumulation data available.

12.4. Mobility in soil

Quartz (SiO ₂) (14808-60-7)	
Surface tension	No data available in the literature
Ecology - soil	Low potential for mobility in soil.

fiberglass (65997-17-3)	
Ecology - soil	No (test)data on mobility of the substance available.

Kaolin (1332-58-7)	
Ecology - soil	No (test)data on mobility of the substance available.

12.5. Other adverse effects

Other information Avoid release to the environment.

SECTION 13: Disposal considerations

13.1. Disposal methods

Waste treatment methods	Dispose in a safe manner in accordance with local/national regulations.
Product/Packaging disposal recommendations	Dispose in a safe manner in accordance with local/national regulations.
Ecological waste information	Avoid release to the environment.

SECTION 14: Transport information

In accordance with DOT / TDG / IMDG / IATA

DOT	TDG	IMDG	IATA
14.1. UN number			
Not regulated for transport			
14.2. Proper Shipping Name			
Not applicable	Not applicable	Not applicable	Not applicable
14.3. Transport hazard class(es)			
Not applicable	Not applicable	Not applicable	Not applicable
14.4. Packing group			
Not applicable	Not applicable	Not applicable	Not applicable
14.5. Environmental hazards			
Dangerous for the environment: No	Dangerous for the environment: No	Dangerous for the environment: No Marine pollutant: No	Dangerous for the environment: No
No supplementary information available			

FS-ONE MAX / CFS-FIL

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

14.6. Special precautions for user

DOT

No data available

TDG

No data available

IMDG

No data available

IATA

No data available

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. US Federal regulations

All components of this product are present and listed as Active on the United States Environmental Protection Agency Toxic Substances Control Act (TSCA) inventory

15.2. International regulations

No additional information available

15.3. US State regulations

California Proposition 65 - This product does not contain any substances known to the state of California to cause cancer, developmental and/or reproductive harm

SECTION 16: Other information

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

Revision date

10/28/2025

Data sources

REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006.

Other information

None.

Full text of hazard classes and H-statements

H350	May cause cancer.
H372	Causes damage to organs through prolonged or repeated exposure

Abbreviations and acronyms

CAS-No.	Chemical Abstract Service number
ADN	European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways
ADR	European Agreement concerning the International Carriage of Dangerous Goods by Road
ATE	Acute Toxicity Estimate

FS-ONE MAX / CFS-FIL

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

Abbreviations and acronyms	
BCF	Bioconcentration factor
BLV	Biological limit value
BOD	Biochemical oxygen demand (BOD)
CLP	Classification Labelling Packaging Regulation; Regulation (EC) No 1272/2008
DMEL	Derived Minimal Effect level
DNEL	Derived-No Effect Level
EC-No.	European Community number
EC50	Median effective concentration
ED	Endocrine disruptor
EN	European Standard
IARC	International Agency for Research on Cancer
IATA	International Air Transport Association
IMDG	International Maritime Dangerous Goods
IOELV	Indicative Occupational Exposure Limit Value
LC50	Median lethal concentration
LD50	Median lethal dose
LOAEL	Lowest Observed Adverse Effect Level
N.O.S.	Not Otherwise Specified
NOAEC	No-Observed Adverse Effect Concentration
NOAEL	No-Observed Adverse Effect Level
NOEC	No-Observed Effect Concentration
vPvB	Very Persistent and Very Bioaccumulative
WGK	Water Hazard Class
VOC	Volatile Organic Compounds
SDS	Safety Data Sheet
RID	Regulations concerning the International Carriage of Dangerous Goods by Rail
REACH	Registration, Evaluation, Authorisation and Restriction of Chemicals Regulation (EC) No 1907/2006
PNEC	Predicted No-Effect Concentration
PBT	Persistent Bioaccumulative Toxic
OEL	Occupational Exposure Limit
OECD	Organisation for Economic Co-operation and Development
COD	Chemical oxygen demand (COD)
ThOD	Theoretical oxygen demand (ThOD)

FS-ONE MAX / CFS-FIL

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

Abbreviations and acronyms	
TRGS	Technical Rules for Hazardous Substances
TLM	Median Tolerance Limit
STP	Sewage treatment plant
ACGIH	American Conference of Government Industrial Hygienists
CSA	Chemical safety assessment
EWC	European waste catalogue
Log Kow	Partition coefficient n-octanol/water (Log Kow)
Log Pow	Partition coefficient n-octanol/water (Log Pow)
MAK	maximum workplace concentration
OSHA	Occupational Safety Health Administration
PPE	Personal protection equipment
TF	Technical function
TWA	Time Weighted Average
UFI	Unique Formula Identifier

NFPA health hazard


NFPA fire hazard

NFPA reactivity

0 - Materials that, under emergency conditions, would offer no hazard beyond that of ordinary combustible materials.

1 - Materials that must be preheated before ignition can occur.

0 - Material that in themselves are normally stable, even under fire conditions.



Hazard Rating

Health

Flammability

Physical

0 Minimal Hazard - No significant risk to health

0 Minimal Hazard - Materials that will not burn

0 Minimal Hazard - Materials that are normally stable, even under fire conditions, and will NOT react with water, polymerize, decompose, condense, or self-react. Non-Explosives.

Personal protection

B - Safety glasses, Gloves

Indication of changes:			
Section	Changed item	Change	Comments
			29 CFR § 1910.1200, Hazard Communication Standard (HCS)

SDS_US_Hilti

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.