




Classified by  
Underwriters Laboratories, Inc.  
to UL 1479 and CAN/ULC-S115

# System No. C-AJ-8180

F Rating — 2 Hr  
T Rating — 0 Hr

CAJ 8180



**SECTION A-A**

1. Floor or Wall Assembly — Min 4-1/2 in.(144 mm) thick reinforced lightweight or normal weight (100-150 pcf) (1600 -2400 kg/m3) concrete floor or min 6-1/2 in. (165 mm) reinforced lightweight or normal weight concrete wall. Wall may also be constructed of any UL Classified Concrete Blocks\*. Max area of square, rectangular or circular opening is 192 sq in.(1239 cm2) with max dimension of 24 in. (610 mm)

See Concrete Blocks (CAZT) category in the Fire Resistance Directory for names of manufacturers.

2. Through-Penetrant — One or more pipes or tubes to be installed within the opening. The total number of through-penetrants is dependent on the size of the opening and types and sizes of the penetrants. Any combination of the penetrants described below may be used provided that the following parameters relative to the annular spaces and the spacings between the pipes are maintained. The separation between cable bundle, tubes and insulated tubes shall be a min 1/2 in.(13 mm) to max 3-1/8 in. (79 mm) The annular space between penetrants and the periphery of opening shall be a min 1/4 in.(6 mm) to max 5 in. (127 mm) Pipes or tubes to be rigidly supported on both sides of floor or wall assembly. The following types and sizes of metallic pipes or tubes may be used.

- A. Copper Tubing — Nom 3 in. (76 mm) diam (or smaller) Tyle L (or heavier) copper tube.
- B. Copper Pipe — Nom 3 in. (76 mm) diam (or smaller) Regular (or heavier) copper pipe.
- C. Steel Pipe — Nom 3 in. (76 mm) diam (or smaller) Schedule 10 (or heavier) steel pipe.
- D. Iron Pipe — Nom 3 in. (76 mm) diam (or smaller) cast or ductile iron pipe.
- E. Conduit — Nom 3 in. (76 mm) diam (or smaller) electric metallic tubing (EMT) or steel conduit.
- F. Flexible Steel Conduit+ — Nom 1 in. (25 mm) diameter (or smaller) flexible steel conduit.

See Flexible Metal Conduit (DXUZ) category in the Electrical Construction Material Directory for names of manufacturers.

3. Tube Insulation-Plastics+++ — Nom 3/4 in. (19 mm) thick (or thinner) acrylonitrile butadiene/polyvinyl chloride (AB/PVC) flexible foam furnished in the foam of tubing.

See P lastics+++ (QMFZ2) category in the Plastics Recognized Component Directory for names of manufacturers. Any Recognized Component tube insulation material meeting the above specifications and having a UL 94 Flammability Classification of 94-5VA may be used.



**Hilti Firestop Systems**

Reproduced by HILTI, Inc. Courtesy of  
Underwriters Laboratories, Inc.  
September 15, 2006



Classified by  
Underwriters Laboratories, Inc.  
to UL 1479 and CAN/ULC-S115

## System No. C-AJ-8180

F Rating — 2 Hr

T Rating — 0 Hr

CAJ 8180

4. Cables — Max 2 in. (51 mm) diam tight bundle of cables installed within the opening and rigidly supported on both sides of floor or wall assembly. The space between the cables and periphery of the opening shall range from min 2 in. (51 mm) to max 4 in. (102 mm) Any combination of the following types and sizes of metallic conductor of fiber optic cable may be used:
- A. Max 500 kcmil single copper conductor power cable with thermoplastic insulation and polyvinyl chloride (PVC) jacket.
  - B. Max 300 pair No. 24 AWG copper conductor telecommunication cables with PVC insulation and jacket material.
  - C. Max 7/C copper conductor No. 12 AWG multiconductor power and control cables with PVC or cross-linked polyethylene (XLPE) insulation and PVC jacket.
  - D. Multiple fiber optical communication cables jacketed with PVC and having a max outside diam of 1/2 in. (13 mm)
  - E. Max 3/C copper conductor No. 12 AWG with bare aluminum ground, PVC insulated steel Metal-Clad cable.
5. Firestop System — The firestop system shall consist of the following:
- A. Packing Material — Min 2-1/2 in. (64 mm) thickness of min 4 pcf (64 kg/m<sup>3</sup>) mineral wool batt insulation firmly packed into opening as a permanent form. Packing material to be recessed from top surface of floor or both surfaces of wall to accommodate the required thickness of fill material.
  - B. Fill Void or Cavity Materials\* - Sealant — Min 2 in. (51 mm) thickness of fill material applied within the annulus, flush with top surface of floor or with both surfaces of wall.  
HILTI CONSTRUCTION CHEMICALS, DIV OF  
HILTI INC — CP 620 Fire Foam

+++Bearing the UL Recognized Component Marking

\*Bearing the UL Classification Mark

+Bearing the UL Listing Mark



**Hilti Firestop Systems**

Reproduced by HILTI, Inc. Courtesy of  
Underwriters Laboratories, Inc.  
September 15, 2006