

# Synthetic diamond impregnated segments

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Revision date: 4/10/2025

Issue date: 4/10/2025

Version: 1.0

### SECTION 1: Identification

#### 1.1. Identification

Product form	Article
Trade name	Synthetic diamond impregnated segments
Product code	BU Diamond
Other means of identification	Polishing discs SPX

#### 1.2. Recommended use and restrictions on use

Recommended use	Grinding materials
Restrictions on use	For professional use only

#### 1.3. Supplier

##### Supplier

Hilti, Inc.  
Legacy Tower, Suite 1000  
7250 Dallas Parkway  
US TX 75024 Plano  
USA  
T +1 9724035800  
1-800-879-8000 toll free, F +1 918 254 0522  
[us-sales@hilti.com](mailto:us-sales@hilti.com)

##### Department issuing data specification sheet

Hilti AG  
Feldkircherstraße 100  
FL 9494 Schaan  
Liechtenstein  
T +423 234 2111  
[product.compliance-power.tools@hilti.com](mailto:product.compliance-power.tools@hilti.com)

#### 1.4. Emergency telephone number

Emergency number	Emergency CONTACT (24-Hour-Number) GBK/Infotrac ID 101022 (USA domestic) 1 800 535 5053 or international (001) 352 323 3500
------------------	--

### SECTION 2: Hazard(s) identification

#### 2.1. Classification of the substance or mixture

##### GHS-US classification

Not classified

#### 2.2. GHS Label elements, including precautionary statements

#### 2.3. Other hazards which do not result in classification

No additional information available

#### 2.4. Unknown acute toxicity (GHS US)

Not applicable

### SECTION 3: Composition/information on ingredients

#### 3.1. Substances

Not applicable

# Synthetic diamond impregnated segments

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

### 3.2. Mixtures

Name	Common Name (Synonyms)	Product identifier	%	GHS-US classification
phenol/formaldehyde, resins	phenol condensation products / phenol, polymer with formaldehyde / phenolic resin	CAS-No.: 9003-35-4	30 – 60	Skin Irrit. 2, H315 Eye Irrit. 2, H319
silicon carbide	silicon carbide (SiC) / silicon monocarbide	CAS-No.: 409-21-2	10 – 30	Carc. 1B, H350
Aluminium oxide		CAS-No.: 1344-28-1	10 – 30	Not classified
polyimino(1-oxo-1,6-hexanediyl)	(poly)amide PA 6 / 6-aminohexanoic acid homopolymer / nylon-6	CAS-No.: 25038-54-4	5 – 10	Not classified

Full text of hazard classes and H-statements : see section 16

## SECTION 4: First-aid measures

### 4.1. Description of first aid measures

First-aid measures after inhalation	Remove person to fresh air and keep comfortable for breathing. When symptoms occur: go into open air and ventilate suspected area.
First-aid measures after skin contact	Gently wash with plenty of soap and water. If skin irritation or rash occurs: Get medical advice/attention.
First-aid measures after eye contact	Rinse eyes with water as a precaution. If eye irritation persists: Get medical advice/attention.
First-aid measures after ingestion	Rinse mouth.

### 4.2. Most important symptoms and effects (acute and delayed)

Potential adverse human health effects and symptoms	Irritation: may cause irritation to the respiratory system.
Symptoms/effects after inhalation	May cause respiratory irritation.
Symptoms/effects after eye contact	May cause severe irritation.

### 4.3. Immediate medical attention and special treatment, if necessary

Treat symptomatically.

## SECTION 5: Fire-fighting measures

### 5.1. Suitable (and unsuitable) extinguishing media

Suitable extinguishing media	Use extinguishing agent suitable for surrounding fire. Water. Sand. Foam. Carbon dioxide.
Unsuitable extinguishing media	Do not use a heavy water stream.

### 5.2. Specific hazards arising from the chemical

Fire hazard	Not flammable.
-------------	----------------

# Synthetic diamond impregnated segments

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

### 5.3. Special protective equipment and precautions for fire-fighters

Protection during firefighting

Do not enter fire area without proper protective equipment, including respiratory protection.

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

#### 6.1.1. For non-emergency personnel

No additional information available

#### 6.1.2. For emergency responders

No additional information available

### 6.2. Environmental precautions

No additional information available

### 6.3. Methods and material for containment and cleaning up

Methods for cleaning up

Shovel into suitable and closed container for disposal.

### 6.4. Reference to other sections

For further information refer to section 8: "Exposure controls/personal protection". For further information refer to section 13.

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Additional hazards when processed

Normal use of this product shall imply use in accordance with the instructions on the packaging and in line with the expectations of a professional user.

Precautions for safe handling

The product should not be used for purposes other than those shown above without first referring to the supplier and obtaining written handling instructions.

Hygiene measures

Do not eat, drink or smoke when using this product. Always wash hands after handling the product. Wash contaminated clothing before reuse.

### 7.2. Conditions for safe storage, including any incompatibilities

Storage conditions

Store in a dry place.

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

Synthetic diamond impregnated segments	
No additional information available	
phenol/formaldehyde, resins (9003-35-4)	
No additional information available	
silicon carbide (409-21-2)	
USA - ACGIH - Occupational Exposure Limits	
Local name	Silicon carbide
ACGIH OEL TWA	10 mg/m <sup>3</sup> (Non fibrous. E - The value is for particulate matter containing no asbestos and < 1 % crystalline silica, I - Inhalable particulate matter) 3 mg/m <sup>3</sup> (Non fibrous. E - The value is for particulate matter containing no asbestos and < 1 % crystalline silica, R - Respirable particulate matter)

# Synthetic diamond impregnated segments

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

silicon carbide (409-21-2)	
	0.1 fibers/cm <sup>3</sup> (Fibrous (including whiskers). F - Respirable fibers)
Remark (ACGIH)	Non fibrous = TLV® Basis: Pulm dam Fibrous (including whiskers) = TLV® Basis: Lung fibrosis; cancer. Notations: A2 (Suspected Human Carcinogen)
Regulatory reference	ACGIH 2025
USA - OSHA - Occupational Exposure Limits	
Local name	Silicon carbide
OSHA PEL TWA	15 mg/m <sup>3</sup> (Total dust) 5 mg/m <sup>3</sup> (Respirable fraction)
Regulatory reference (US-OSHA)	OSHA Annotated Table Z-1
Aluminium oxide (1344-28-1)	
USA - OSHA - Occupational Exposure Limits	
Local name	alpha-Alumina
OSHA PEL TWA	15 mg/m <sup>3</sup> (Total dust) 5 mg/m <sup>3</sup> (Respirable fraction)
Regulatory reference (US-OSHA)	OSHA Annotated Table Z-1
polyimino(1-oxo-1,6-hexanediyl) (25038-54-4)	
USA - ACGIH - Occupational Exposure Limits	
ACGIH OEL TWA	3 mg/m <sup>3</sup> (Respirable fraction)

### 8.2. Appropriate engineering controls

Appropriate engineering controls

Ensure good ventilation of the work station. Use dust removal system, vacuum cleaner, air cleaner; cooling water cleaner (Hilti WMS system).

### 8.3. Individual protection measures/Personal protective equipment

#### Personal protective equipment:

Dust formation: dust mask. In case of dust production: protective goggles. Gloves. Protective clothing.

Materials for protective clothing:				
Condition		Material		
		Flame retardant protective clothing		
Hand protection:				
Wear leather gloves.				
Type	Material	Permeation	Thickness (mm)	Penetration
	leather gloves			
Eye protection:				
Safety glasses				

# Synthetic diamond impregnated segments

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Type	Field of application	Characteristics
Safety glasses	Dust	
<b>Skin and body protection:</b>		
Wear suitable protective clothing		
<b>Respiratory protection:</b>		
Where exposure through inhalation may occur from use, respiratory protection equipment is recommended		
Device	Filter type	Condition
		Dust protection

### Personal protective equipment symbol(s):



### Other information:

Hazardous dust of the workpiece material may be generated during grinding / drilling and / or sanding operations. National regulations for dust exposure limit values have to be taken into consideration as part of the job hazard assessment.

Most of the dust generated during grinding is from the base material being ground and the potential hazard from this exposure must be evaluated. This dust may present a fire or dust explosion hazard and may present a serious health hazard.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

Physical state	Solid
Colour	Various colours
Odour	odourless
Odour threshold	No data available
pH	No data available
Melting point	No data available
Freezing point	No data available
Boiling point	No data available
Flash point	No data available
Relative evaporation rate (butylacetate=1)	No data available
Flammability (solid, gas)	No data available
Vapour pressure	No data available
Relative vapour density at 20°C	No data available
Relative density	No data available
Solubility	insoluble in water.
Partition coefficient n-octanol/water (Log Pow)	No data available
Auto-ignition temperature	No data available
Decomposition temperature	No data available
Viscosity, kinematic	No data available
Viscosity, dynamic	No data available
Explosive limits	No data available
Explosive properties	No data available
Oxidising properties	No data available

# Synthetic diamond impregnated segments

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

### 9.2. Other information

No additional information available

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport. Product is not explosive.

### 10.2. Chemical stability

Stable under normal conditions.

### 10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

### 10.4. Conditions to avoid

No additional information available

### 10.5. Incompatible materials

No additional information available

### 10.6. Hazardous decomposition products

No additional information available

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

Acute toxicity (oral)	Not classified
Acute toxicity (dermal)	Not classified
Acute toxicity (inhalation)	Not classified

phenol/formaldehyde, resins (9003-35-4)	
LD50 oral rat	> 5000 mg/kg
LD50 dermal rat	> 2000 mg/kg
silicon carbide (409-21-2)	
LD50 oral rat	> 2000 mg/kg
LD50 dermal rat	> 2000 mg/kg
Aluminium oxide (1344-28-1)	
LD50 oral rat	> 15900 mg/kg
LC50 Inhalation - Rat	7.6 mg/l
LC50 Inhalation - Rat (Dust/Mist)	> 2.3 mg/l/4h (OECD 403 method)
polyimino(1-oxo-1,6-hexanediyl) (25038-54-4)	
LD50 oral rat	> 5000 mg/kg (Rat, Oral)

Skin corrosion/irritation	Not classified
Serious eye damage/irritation	Not classified
Respiratory or skin sensitisation	Not classified
Germ cell mutagenicity	Not classified
Carcinogenicity	Not classified

# Synthetic diamond impregnated segments

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

silicon carbide (409-21-2)	
IARC group	2A - Probably carcinogenic to humans
polyimino(1-oxo-1,6-hexanediyl) (25038-54-4)	
IARC group	3 - Not classifiable
Reproductive toxicity	Not classified
STOT-single exposure	Not classified
STOT-repeated exposure	Not classified
Aspiration hazard	Not classified
Viscosity, kinematic	No data available
Likely routes of exposure	Inhalation.
Potential adverse human health effects and symptoms	Irritation: may cause irritation to the respiratory system.
Symptoms/effects after inhalation	May cause respiratory irritation.
Symptoms/effects after eye contact	May cause severe irritation.

## SECTION 12: Ecological information

### 12.1. Toxicity

Ecology - general The product is not considered harmful to aquatic organisms nor to cause long-term adverse effects in the environment.

silicon carbide (409-21-2)	
ErC50 algae	> 100 mg/l (OECD 201: Alga, Growth Inhibition Test, 48 h, Desmodesmus subspicatus, Static system, Fresh water, Experimental value, GLP)
NOEC chronic crustacea	≥ 100 mg/l (22d;Daphnia magna; OECD Guideline 211)

### 12.2. Persistence and degradability

phenol/formaldehyde, resins (9003-35-4)	
Persistence and degradability	Biodegradability in water: no data available.
silicon carbide (409-21-2)	
Persistence and degradability	Biodegradability: not applicable.
Chemical oxygen demand (COD)	Not applicable (inorganic)
ThOD	Not applicable (inorganic)
Aluminium oxide (1344-28-1)	
Not rapidly degradable	
Persistence and degradability	Not applicable.
polyimino(1-oxo-1,6-hexanediyl) (25038-54-4)	
Persistence and degradability	Not readily biodegradable in water.

### 12.3. Bioaccumulative potential

phenol/formaldehyde, resins (9003-35-4)	
Bioaccumulative potential	No bioaccumulation data available.

# Synthetic diamond impregnated segments

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

silicon carbide (409-21-2)	
Bioaccumulative potential	Not bioaccumulative.
Aluminium oxide (1344-28-1)	
Bioaccumulative potential	Not applicable.
polyimino(1-oxo-1,6-hexanediyl) (25038-54-4)	
Bioaccumulative potential	No bioaccumulation data available.

### 12.4. Mobility in soil

silicon carbide (409-21-2)	
Surface tension	No data available in the literature
Ecology - soil	Low potential for adsorption in soil.

### 12.5. Other adverse effects

Other information Do not allow the product, as is, to spread into the environment.

## SECTION 13: Disposal considerations

### 13.1. Disposal methods

Regional waste regulation Disposal must be done according to official regulations.  
 Product/Packaging disposal recommendations Dispose in a safe manner in accordance with local/national regulations. Avoid release to the environment.  
 Ecological information Avoid release to the environment. Hazardous waste due to toxicity.

## SECTION 14: Transport information

In accordance with DOT / TDG / IMDG / IATA

DOT	TDG	IMDG	IATA
14.1. UN number			
Not regulated for transport			
14.2. Proper Shipping Name			
Not regulated	Not regulated	Not regulated	Not regulated
14.3. Transport hazard class(es)			
Not regulated	Not regulated	Not regulated	Not regulated
14.4. Packing group			
Not regulated	Not regulated	Not regulated	Not regulated
14.5. Environmental hazards			
Not regulated	Not regulated	Not regulated	Not regulated
No supplementary information available			

### 14.6. Special precautions for user

DOT  
Not regulated



# Synthetic diamond impregnated segments

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

### TDG

Not regulated

### IMDG

Not regulated

### IATA

Not regulated

### 14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable

## SECTION 15: Regulatory information

### 15.1. US Federal regulations

All components of this product are present and listed as Active on the United States Environmental Protection Agency Toxic Substances Control Act (TSCA) inventory

Chemical(s) subject to the reporting requirements of Section 313 or Title III of the Superfund Amendments and Reauthorization Act (SARA) of 1986 and 40 CFR Part 372.

Aluminium oxide	CAS-No. 1344-28-1	10 – 30%
-----------------	-------------------	----------

### 15.2. International regulations

#### silicon carbide (409-21-2)

Listed on IARC (International Agency for Research on Cancer)

### 15.3. US State regulations

California Proposition 65 - This product does not contain any substances known to the state of California to cause cancer, developmental and/or reproductive harm

## SECTION 16: Other information

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Revision date 04/10/2025

### Full text of H-statements

H315	Causes skin irritation.
------	-------------------------

H319	Causes serious eye irritation.
------	--------------------------------

H350	May cause cancer.
------	-------------------

### Abbreviations and acronyms

CAS-No.	Chemical Abstract Service number
---------	----------------------------------

ADN	European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways
-----	---

ADR	European Agreement concerning the International Carriage of Dangerous Goods by Road
-----	---

ATE	Acute Toxicity Estimate
-----	-------------------------

# Synthetic diamond impregnated segments

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Abbreviations and acronyms	
CLP	Classification Labelling Packaging Regulation; Regulation (EC) No 1272/2008
BCF	Bioconcentration factor
BLV	Biological limit value
BOD	Biochemical oxygen demand (BOD)
COD	Chemical oxygen demand (COD)
DMEL	Derived Minimal Effect level
DNEL	Derived-No Effect Level
EC-No.	European Community number
EC50	Median effective concentration
ED	Endocrine disrupting properties
EN	European Standard
IARC	International Agency for Research on Cancer
IATA	International Air Transport Association
IMDG	International Maritime Dangerous Goods
IOELV	Indicative Occupational Exposure Limit Value
LC50	Median lethal concentration
LD50	Median lethal dose
LOAEL	Lowest Observed Adverse Effect Level
N.O.S.	Not Otherwise Specified
NOAEC	No-Observed Adverse Effect Concentration
NOAEL	No-Observed Adverse Effect Level
NOEC	No-Observed Effect Concentration
OECD	Organisation for Economic Co-operation and Development
OEL	Occupational Exposure Limit
PBT	Persistent Bioaccumulative Toxic
PNEC	Predicted No-Effect Concentration
REACH	Registration, Evaluation, Authorisation and Restriction of Chemicals Regulation (EC) No 1907/2006
RID	Regulations concerning the International Carriage of Dangerous Goods by Rail
SDS	Safety Data Sheet
TRGS	Technical Rules for Hazardous Substances
ThOD	Theoretical oxygen demand (ThOD)
TLM	Median Tolerance Limit
VOC	Volatile Organic Compounds

# Synthetic diamond impregnated segments

## Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Abbreviations and acronyms	
WGK	Water Hazard Class
vPvB	Very Persistent and Very Bioaccumulative

NFPA health hazard


1 - Materials that, under emergency conditions, can cause significant irritation.

NFPA fire hazard

0 - Materials that will not burn under typical fire conditions, including intrinsically noncombustible materials such as concrete, stone, and sand.

NFPA reactivity

0 - Material that in themselves are normally stable, even under fire conditions.



Hazard Rating

Health

1 Slight Hazard - Irritation or minor reversible injury possible

Flammability

0 Minimal Hazard - Materials that will not burn

Physical

0 Minimal Hazard - Materials that are normally stable, even under fire conditions, and will NOT react with water, polymerize, decompose, condense, or self-react. Non-Explosives.

SDS\_US\_Hilti

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.