

CP 617 / CP 619

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

Revision date: 10/27/2025

Issue date: 10/27/2025

Supersedes: 12/16/2024

Version: 5.0

SECTION 1: Identification

1.1. Identification

Product form	Mixture
Product name	CP 617 / CP 619
Product code	BU Fire Protection

1.2. Other means of identification

No additional information available

1.3. Recommended use of the chemical and restrictions on use

Use of the substance/mixture	Firestop putty pad / stick / cable disc
Recommended use	For professional users only

1.4. Supplier's details

Supplier

Hilti, Inc.
Legacy Tower, Suite 1000
7250 Dallas Parkway
US TX 75024 Plano
USA
T +1 9724035800
1-800-879-8000 toll free, F +1 918 254 0522
us-sales@hilti.com

Department issuing data specification sheet

Hilti AG
Feldkircher Strasse
FL 9494 Schaan
Liechtenstein
T +423 234 2111
product.compliance-fire.protection@hilti.com

1.5. Emergency phone number

Emergency number	Emergency CONTACT (24-Hour-Number) GBK/Infotrac ID 101022 (USA domestic) 1 800 535 5053 or international (001) 352 323 3500
------------------	--

SECTION 2: Hazard(s) identification

2.1. Classification of the substance or mixture

GHS-US classification

Not classified

2.2. GHS Label elements, including precautionary statements

GHS US labelling

No labelling applicable

2.3. Hazards associated with known or reasonably anticipated uses

No additional information available

2.4. Hazards not otherwise classified

No additional information available

2.5. Unknown acute toxicity (GHS US)

Not applicable

CP 617 / CP 619

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

This mixture does not contain any substances to be mentioned according to the criteria for section 3.2 of HCS

SECTION 4: First-aid measures

4.1. Description of first aid measures

First-aid measures general	Never give anything by mouth to an unconscious person. If you feel unwell, seek medical advice (show the label where possible).
First-aid measures after inhalation	Remove person to fresh air and keep comfortable for breathing.
First-aid measures after skin contact	Wash skin with plenty of water.
First-aid measures after eye contact	Obtain medical attention if pain, blinking or redness persists. Rinse eyes with water as a precaution.
First-aid measures after ingestion	Rinse mouth. Do NOT induce vomiting. Obtain emergency medical attention. Call a poison center or a doctor if you feel unwell.

4.2. Most important symptoms and effects (acute and delayed)

Potential adverse human health effects and symptoms	Based on available data, the classification criteria are not met.
Symptoms/effects	Not expected to present a significant hazard under anticipated conditions of normal use.
Symptoms/effects after inhalation	Dust of the product, if present, may cause respiratory irritation after excessive inhalation exposure. Although no appropriate human or animal health effects data are known to exist, this material is expected to be an inhalation hazard.
Symptoms/effects after skin contact	None under normal conditions. Dust may cause irritation in skin folds or by contact in combination with tight clothing.
Symptoms/effects after eye contact	None under normal conditions. Dust from this product may cause eye irritation.
Symptoms/effects after ingestion	None under normal conditions.

4.3. Immediate medical attention and special treatment, if necessary

Treat symptomatically.

SECTION 5: Fire-fighting measures

5.1. Suitable (and unsuitable) extinguishing media

Suitable extinguishing media	Foam. Dry powder. Carbon dioxide. Water spray. Sand.
Unsuitable extinguishing media	Do not use a heavy water stream.

5.2. Specific hazards arising from the chemical

Fire hazard	No fire hazard.
Explosion hazard	No direct explosion hazard.
Hazardous decomposition products in case of fire	Carbon dioxide. Carbon monoxide.

5.3. Special protective equipment and precautions for fire-fighters

Firefighting instructions	Use water spray or fog for cooling exposed containers. Exercise caution when fighting any chemical fire. Prevent fire fighting water from entering the environment. Do not enter fire area without proper protective equipment, including respiratory protection.
Protection during firefighting	Do not enter fire area without proper protective equipment, including respiratory protection. Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.

CP 617 / CP 619

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

General measures Notify authorities if product enters sewers or public waters. Absorb spillage to prevent material damage.

For non-emergency personnel

Protective equipment Wear recommended personal protective equipment.
Emergency procedures Ventilate spillage area. Evacuate unnecessary personnel.

For emergency responders

Protective equipment Do not attempt to take action without suitable protective equipment. Equip cleanup crew with proper protection. For further information refer to section 8: "Exposure controls/personal protection".
Emergency procedures Ventilate area. Evacuate unnecessary personnel.

Environmental precautions Avoid release to the environment. Prevent entry to sewers and public waters.

6.2. Methods and materials for containment and cleaning up

For containment Using a clean shovel, put the material in a dry container and cover without compressing it.
Methods for cleaning up Mechanically recover the product. On land, sweep or shovel into suitable containers.
Other information Dispose of materials or solid residues at an authorized site.

See Section 8, Exposure controls and personal protection, For further information refer to section 13

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Additional hazards when processed Not expected to present a significant hazard under anticipated conditions of normal use.
Precautions for safe handling Ensure good ventilation of the work station. Wear personal protective equipment. Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work.
Hygiene measures Do not eat, drink or smoke when using this product. Always wash hands after handling the product.

7.2. Conditions for safe storage, including any incompatibilities

Technical measures Keep in a cool, well-ventilated place away from heat.
Storage conditions Store at ambient temperature.
Incompatible products Strong bases. Strong acids.
Incompatible materials Sources of ignition. Direct sunlight.
Storage temperature 23 – 104 °F
Packaging materials Store always product in container of same material as original container.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

CP 617 / CP 619

No additional information available

Additional information The product has a pasty consistency. Exposure limit values for respirable dusts are not relevant for this product.

CP 617 / CP 619

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

8.2. Appropriate engineering controls

Appropriate engineering controls Ensure good ventilation of the work station.
Environmental exposure controls Avoid release to the environment.

8.3. Individual protection measures/Personal protective equipment

Personal protective equipment:

Avoid all unnecessary exposure. Protective goggles. Wear protective gloves. Protective clothing.

Hand protection:				
Wear suitable gloves tested to EN374. Suitable for short-term work or as a splash guard: Nitrile rubber gloves (> 0.1 mm). In case of permanent product contact:				
Type	Material	Permeation	Thickness (mm)	Penetration
Disposable gloves	Nitrile rubber (NBR)	6 (> 480 minutes)	>0,4	
Eye protection:				
Safety glasses				
Skin and body protection:				
Wear suitable protective clothing				
Respiratory protection:				
No respiratory protection needed under normal use conditions				

Personal protective equipment symbol(s):



Other information:

Do not eat, drink or smoke during use.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	Solid
Appearance	Pasty.
Colour	red
Odour	characteristic
Odour threshold	Not determined
pH	Not relevant
Melting point	No data available
Freezing point	Not applicable
Boiling point	No data available
Flash point	Not applicable
Relative evaporation rate (butylacetate=1)	No data available
Flammability (solid, gas)	Non flammable.
Vapour pressure	No data available
Relative vapour density at 20°C	No data available
Relative density	No data available
Density	1.6 g/cm³

CP 617 / CP 619

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

Molecular mass	Not determined
Solubility	Water: Insoluble
Partition coefficient n-octanol/water (Log Pow)	No data available
Auto-ignition temperature	Not applicable
Decomposition temperature	No data available
Viscosity, kinematic	Not applicable
Viscosity, dynamic	No data available
Explosive limits	Not applicable
Explosive properties	No data available
Oxidising properties	No data available

9.2. Other information

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

10.2. Chemical stability

Not established.

10.3. Possibility of hazardous reactions

Not established.

10.4. Conditions to avoid

Direct sunlight. Extremely high or low temperatures.

10.5. Incompatible materials

Strong acids. Strong bases.

10.6. Hazardous decomposition products

fume. Carbon monoxide. Carbon dioxide.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity (oral)	Not classified
Acute toxicity (dermal)	Not classified
Acute toxicity (inhalation)	Not classified
Skin corrosion/irritation	Not classified
	pH: Not relevant
Serious eye damage/irritation	Not classified
	pH: Not relevant
Respiratory or skin sensitisation	Not classified
Germ cell mutagenicity	Not classified
Carcinogenicity	Not classified
Reproductive toxicity	Not classified
STOT-single exposure	Not classified
STOT-repeated exposure	Not classified
Aspiration hazard	Not classified
Viscosity, kinematic	Not applicable

CP 617 / CP 619

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

Potential adverse human health effects and symptoms

Symptoms/effects

Symptoms/effects after inhalation

Symptoms/effects after skin contact

Symptoms/effects after eye contact

Symptoms/effects after ingestion

Based on available data, the classification criteria are not met.

Not expected to present a significant hazard under anticipated conditions of normal use.

Dust of the product, if present, may cause respiratory irritation after excessive inhalation exposure. Although no appropriate human or animal health effects data are known to exist, this material is expected to be an inhalation hazard.

None under normal conditions. Dust may cause irritation in skin folds or by contact in combination with tight clothing.

None under normal conditions. Dust from this product may cause eye irritation.

None under normal conditions.

SECTION 12: Ecological information

12.1. Toxicity

Ecology - general

The product is not considered harmful to aquatic organisms nor to cause long-term adverse effects in the environment.

12.2. Persistence and degradability

CP 617 / CP 619

Persistence and degradability

Not established.

12.3. Bioaccumulative potential

CP 617 / CP 619

Bioaccumulative potential

Not established.

12.4. Mobility in soil

No additional information available

12.5. Other adverse effects

Other information

Avoid release to the environment.

SECTION 13: Disposal considerations

13.1. Disposal methods

Regional waste regulation

Waste treatment methods

Sewage disposal recommendations

Product/Packaging disposal recommendations

Additional information

Ecological waste information

Disposal must be done according to official regulations.

Dispose in a safe manner in accordance with local/national regulations. Dispose of contents/container in accordance with licensed collector's sorting instructions.

Disposal must be done according to official regulations.

Dispose in a safe manner in accordance with local/national regulations. Disposal must be done according to official regulations.

Do not re-use empty containers.

Avoid release to the environment.

SECTION 14: Transport information

In accordance with DOT / TDG / IMDG / IATA

DOT	TDG	IMDG	IATA
14.1. UN number			
Not regulated for transport			

CP 617 / CP 619

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

DOT	TDG	IMDG	IATA
14.2. Proper Shipping Name			
Not regulated	Not regulated	Not regulated	Not regulated
14.3. Transport hazard class(es)			
Not regulated	Not regulated	Not regulated	Not regulated
14.4. Packing group			
Not regulated	Not regulated	Not regulated	Not regulated
14.5. Environmental hazards			
Not regulated	Not regulated	Not regulated	Not regulated
No supplementary information available			

14.6. Special precautions for user

DOT

Not regulated

TDG

Not regulated

IMDG

Not regulated

IATA

Not regulated

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. US Federal regulations

All components of this product are present and listed as Active on the United States Environmental Protection Agency Toxic Substances Control Act (TSCA) inventory

15.2. International regulations

No additional information available

15.3. US State regulations

California Proposition 65 - This product does not contain any substances known to the state of California to cause cancer, developmental and/or reproductive harm

SECTION 16: Other information

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

Revision date

10/27/2025

Data sources

REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006.

Other information

None.

CP 617 / CP 619

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

Abbreviations and acronyms	
ADN	European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways
ADR	European Agreement concerning the International Carriage of Dangerous Goods by Road
ATE	Acute Toxicity Estimate
BCF	Bioconcentration factor
BLV	Biological limit value
BOD	Biochemical oxygen demand (BOD)
COD	Chemical oxygen demand (COD)
DMEL	Derived Minimal Effect level
DNEL	Derived-No Effect Level
EC-No.	European Community number
EC50	Median effective concentration
EN	European Standard
IARC	International Agency for Research on Cancer
IATA	International Air Transport Association
IMDG	International Maritime Dangerous Goods
LC50	Median lethal concentration
LD50	Median lethal dose
LOAEL	Lowest Observed Adverse Effect Level
NOAEC	No-Observed Adverse Effect Concentration
NOAEL	No-Observed Adverse Effect Level
NOEC	No-Observed Effect Concentration
OECD	Organisation for Economic Co-operation and Development
OEL	Occupational Exposure Limit
PBT	Persistent Bioaccumulative Toxic
PNEC	Predicted No-Effect Concentration
RID	Regulations concerning the International Carriage of Dangerous Goods by Rail
SDS	Safety Data Sheet
STP	Sewage treatment plant
ThOD	Theoretical oxygen demand (ThOD)
TLM	Median Tolerance Limit
VOC	Volatile Organic Compounds
CAS-No.	Chemical Abstract Service number
N.O.S.	Not Otherwise Specified

CP 617 / CP 619

Safety Data Sheet

according to 29 CFR § 1910.1200, Hazard Communication Standard (HCS)

Abbreviations and acronyms	
vPvB	Very Persistent and Very Bioaccumulative
ED	Endocrine disruptor

NFPA health hazard	0 - Materials that, under emergency conditions, would offer no hazard beyond that of ordinary combustible materials.	
NFPA fire hazard	0 - Materials that will not burn under typical fire conditions, including intrinsically noncombustible materials such as concrete, stone, and sand.	
NFPA reactivity	0 - Material that in themselves are normally stable, even under fire conditions.	
Hazard Rating		
Health	0 Minimal Hazard - No significant risk to health	
Flammability	0 Minimal Hazard - Materials that will not burn	
Physical	0 Minimal Hazard - Materials that are normally stable, even under fire conditions, and will NOT react with water, polymerize, decompose, condense, or self-react. Non-Explosives.	
Personal protection	B - Safety glasses, Gloves	

Indication of changes:			
Section	Changed item	Change	Comments
			29 CFR § 1910.1200, Hazard Communication Standard (HCS)

SDS_US_Hilti

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.