

COMPLIANCE TESTED by berkeley analytical VOC Emission Test Certificate

Product Name: CFS-MSL Modular Sleeve

Product Sample Information				
Company:	Hilti Inc.			
Company Website:	www.hilti.com			
Product Type:	Modular Sleeve			
Date Produced:	8/15/2022			

Certificate Information				
Certificate No:	220916-01			
Certified By:	Raja S. Tannous, Laboratory Director			
Date:	September 16, 2022			

Reference Standard: California Department of Public Health CDPH/EHLB/Standard Method Version 1.2, 2017 (Emission testing method for CA Specification 01350)

Acceptance Criteria and Results Demonstrating Compliance of Product Sample to Referenced Standard:

Exposure Scenario ¹	Individual VOCs of Concern ²		Formaldehyde ³		TVOC⁴
	Criterion	Compliant?	Criterion	Compliant?	Range
School Classroom	≤½ Chronic REL	YES	≤9.0 μg/m³	YES	≤ 0.5 mg/m³
Private Office	≤½ Chronic REL	YES	≤9.0 μg/m³	YES	≤ 0.5 mg/m³

Product Coverage⁵: See attached manufacturer's letter for loading application

- 1. Exposure scenarios & product quantities for classroom & office are defined in Tables 4-2 4-5 (CDPH Std. Mtd. V1.2-2017)
- 2. Maximum allowable concentrations of individual target VOCs are specified in Table 4-1 (ibid.)
- 3. Maximum allowable formaldehyde concentration is ≤9 µg/m³, effective Jan 1, 2012; previous limit was ≤16.5 µg/m³ (ibid.)
- 4. Informative only; predicted TVOC Range in three categories, i.e., ≤0.5 mg/m³, >0.5 4.9 mg/m³, and ≥5.0 mg/m³
- 5. Informative and applicable only to tests of wet-applied products; grams of sample applied per square meter of substrate

Standards & Codes Recognizing CDPH Standard Method V1.2 (partial list)

- USGBC LEED Version 4/4.1, BD&C, ID&C, Residential BD&C Multifamily
- The WELL Building Standard, WELL v2, Feature X06
- ANSI/GBI 01-2019 Green Globes Assessment Protocol

Narrative: Hilti Inc. selected a sample representative of its CFS-MSL Modular Sleeve - 2337019 product and submitted it on 8/17/2022 for testing. Berkeley Analytical measured and evaluated the emissions of VOCs from this sample following CDPH/EHLB/Standard Method V1.2-2017. The results of the test are presented in Berkeley Analytical report, 1031-014-01A-Sep1622.

Berkeley Analytical is an independent, third-party laboratory specializing in the analysis of organic chemicals emitted by and contained in building products, finishes, furniture, and consumer products. We are an ISO/IEC 17025 accredited laboratory (IAS, <u>TL-383</u>); all standards used in performing this test are in Berkeley Analytical's scope of accreditation.

DISCLAIMER: THIS CERTIFICATE OF COMPLIANCE AFFIRMS THAT: 1) A SAMPLE OF THE LISTED PRODUCT WAS TESTED ACCORDING TO THE REFERENCED STANDARD; 2) THE MEASURED VOC EMISSIONS FROM THE SAMPLE WERE EVALUATED FOR THE DEFINED EXPOSURE SCENARIO(S); AND 3) THE RESULTS MEET THE ACCEPTANCE CRITERIA OF THE REFERENCED STANDARD(S). BERKELEY ANALYTICAL IS NOT RESPONSIBLE FOR ANY CLAIMS REGARDING A PRODUCT OR PRODUCTS ENTERED INTO COMMERCE THAT MAY BE BASED ON THIS TEST. BERKELEY ANALYTICAL PROVIDES THIS CERTIFICATE OF COMPLIANCE "AS IS" WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESSED OR IMPLIED, INCLUDING BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR ANY PURPOSE.



Berkley Analytical Mr. Alec Huang 815 Harbor Way South, suite 6 Richmond, CA 94804

RE: VOC Emission Testing; CDPH Standard Test Method V1.2; non-full spread application calculations

Below are the average number of Hilti CFS-MSL Modular Sleeves that would be used in the standard school classroom and the standard private office as defined in the CDPH Standard Method V1.2.

CLASSROOM

The dimenstions of a typical classroom are given by the CDPH Standard as 40 ft x 24 ft. It is expected that this size room would require 2 CFS-MSL Modular Sleeves.

OFFICE

The dimenstions of a typical office are given by the CDPH Standard as 12 ft x 10 ft. It is expected that this size room would require 4 CFS-MSL Modular Sleeves.

Please contact me if you have any questions

Jerry Metcalf MPH, CHMM

Sr. Manager Safety/Environmental

jerry.metcalf@hilti.com

918 872 3704