




# COMPLIANCE TESTED by berkeley analytical

## VOC Emission Test Certificate

**Product Name: FS-ONE MAX - 2101531**

Product Sample Information		Certificate Information	
Company:	Hilti Inc.	Certificate No:	200715-02
Company Website:	www.hilti.com	Certified By:	 Raja S. Tannous, Laboratory Director
Product Type:	Sealants - Firestop	Date:	July 15, 2020
Date Produced:	5/5/2020		

**Reference Standard:** California Department of Public Health CDPH/EHLB/Standard Method Version 1.2, 2017 (Emission testing method for CA Specification 01350)

### Acceptance Criteria and Results Demonstrating Compliance of Product Sample to Referenced Standard:

Exposure Scenario <sup>1</sup>	Individual VOCs of Concern <sup>2</sup>		Formaldehyde <sup>3</sup>		TVOC <sup>4</sup> Range
	Criterion	Compliant?	Criterion	Compliant?	
School Classroom	≤½ Chronic REL	YES	≤9.0 µg/m <sup>3</sup>	YES	≤0.5 mg/m <sup>3</sup>
Private Office	≤½ Chronic REL	YES	≤9.0 µg/m <sup>3</sup>	YES	≤0.5 mg/m <sup>3</sup>

Product Coverage<sup>5</sup>: 14,260 g/m<sup>2</sup>

1. Exposure scenarios & product quantities for classroom & office are defined in Tables 4-2 – 4-5 (CDPH Std. Mtd. V1.2-2017)
2. Maximum allowable concentrations of individual target VOCs are specified in Table 4-1 (*ibid.*)
3. Maximum allowable formaldehyde concentration is ≤9 µg/m<sup>3</sup>, effective Jan 1, 2012; previous limit was ≤16.5 µg/m<sup>3</sup> (*ibid.*)
4. Informative only; predicted TVOC Range in three categories, i.e., ≤0.5 mg/m<sup>3</sup>, >0.5 – 4.9 mg/m<sup>3</sup>, and ≥5.0 mg/m<sup>3</sup>
5. Informative and applicable only to tests of wet-applied products; grams of sample applied per square meter of substrate

### Standards & Codes Recognizing CDPH Standard Method V1.2 (partial list)

- IISGRC IFFD Version 4 RD&C ID&C
- The WELL Building Standard
- ANSI/GRI 01 Green Building Assessment Protocol

**Narrative:** Hilti Inc. selected a sample representative of its FS-ONE MAX - 2101531 firestop sealant product and submitted it on 6/10/2020 for testing. Berkeley Analytical measured and evaluated the emissions of VOCs from this sample following CDPH/EHLB/Standard Method V1.2-2017. The results of the test are presented in Berkeley Analytical report, 1031-007-03A-Jul1520.

**Berkeley Analytical** is an independent, third-party laboratory specializing in the analysis of organic chemicals emitted by and contained in building products, finishes, furniture, and consumer products. We are an ISO/IEC 17025 accredited laboratory (IAS, [TL-383](#)); all standards used in performing this test are in Berkeley Analytical's scope of accreditation.

**DISCLAIMER:** THIS CERTIFICATE OF COMPLIANCE AFFIRMS THAT: 1) A SAMPLE OF THE LISTED PRODUCT WAS TESTED ACCORDING TO THE REFERENCED STANDARD; 2) THE MEASURED VOC EMISSIONS FROM THE SAMPLE WERE EVALUATED FOR THE DEFINED EXPOSURE SCENARIO(S); AND 3) THE RESULTS MEET THE ACCEPTANCE CRITERIA OF THE REFERENCED STANDARD(S). BERKELEY ANALYTICAL IS NOT RESPONSIBLE FOR ANY CLAIMS REGARDING A PRODUCT OR PRODUCTS ENTERED INTO COMMERCE THAT MAY BE BASED ON THIS TEST. BERKELEY ANALYTICAL PROVIDES THIS CERTIFICATE OF COMPLIANCE "AS IS" WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESSED OR IMPLIED, INCLUDING BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR ANY PURPOSE.