




## Hilti HIT-RE 500-SD with HIT-V rod

Injection mortar system		Benefits
	Hilti HIT-RE 500-SD 330 ml foil pack  (also available as 500 ml and 1400 ml foil pack)	<ul style="list-style-type: none"> <li>- suitable for non-cracked and cracked concrete C 20/25 to C 50/60</li> <li>- high loading capacity</li> <li>- suitable for dry and water saturated concrete</li> <li>- large diameter applications</li> <li>- high corrosion resistant</li> <li>- long working time at elevated temperatures</li> <li>- odourless epoxy</li> <li>- embedment depth range: from 40 ... 160 mm for M8 to 120 ... 600 mm for M30</li> </ul>
	Static mixer	
	HIT-V rod	



Concrete



Tensile zone



Small edge distance and spacing



Variable embedment depth



Fire resistance



Corrosion resistance



High corrosion resistance



European Technical Approval



CE conformity



Hilti anchor design software

### Approvals / certificates

Description	Authority / Laboratory	No. / date of issue
European technical approval <sup>a)</sup>	DIBt, Berlin	ETA-07/0260 / 2009-01-12
ES report	ICC evaluation service	ESR 2322 / 2007-11-01
Fire test report	MFPA, Leipzig	GS-III/B-07-070 / 2008-01-18
Assessment report (fire)	warringtonfire	WF 166402 / 2007-10-26 & suppl. WF 172920 / 2008-05-27

a) All data given in this section according to ETA-07/0260, issue 2008-11-03.

## Basic loading data (for a single anchor)

All data in this section applies to

For details see Simplified design method

- Correct setting (See setting instruction)
- No edge distance and spacing influence
- Steel failure
- Base material thickness, as specified in the table
- One typical embedment depth, as specified in the table
- One anchor material, as specified in the tables
- Concrete C 20/25,  $f_{ck,cube} = 25 \text{ N/mm}^2$
- Temperate range I  
(min. base material temperature  $-40^\circ\text{C}$ , max. long term/short term base material temperature:  $+24^\circ\text{C}/40^\circ\text{C}$ )
- Installation temperature range  $+5^\circ\text{C}$  to  $+40^\circ\text{C}$

**Embedment depth <sup>a)</sup> and base material thickness for the basic loading data.**  
**Mean ultimate resistance, characteristic resistance, design resistance, recommended loads.**

Anchor size	M8	M10	M12	M16	M20	M24	M27	M30
Typical embedment depth [mm]	80	90	110	125	170	210	240	270
Base material thickness [mm]	110	120	140	165	220	270	300	340

a) The allowed range of embedment depth is shown in the setting details. The corresponding load values can be calculated according to the simplified design method.

**Mean ultimate resistance: concrete C 20/25 –  $f_{ck,cube} = 25 \text{ N/mm}^2$ , anchor HIT-V 5.8**

		Data according ETA-07/0260, issue 2009-01-12								
Anchor size		M8	M10	M12	M16	M20	M24	M27	M30	
Non cracked concrete										
Tensile $N_{Ru,m}$	HIT-V 5.8	[kN]	18,9	30,5	44,1	83,0	129,2	185,9	241,5	295,1
Shear $V_{Ru,m}$	HIT-V 5.8	[kN]	9,5	15,8	22,1	41,0	64,1	92,4	120,8	147,0
Cracked concrete										
Tensile $N_{Ru,m}$	HIT-V 5.8	[kN]	18,9	30,5	44,1	65,2	110,8	146,1	196,0	226,2
Shear $V_{Ru,m}$	HIT-V 5.8	[kN]	9,5	15,8	22,1	41,0	64,1	92,4	120,8	147,0

**Characteristic resistance: concrete C 20/25 –  $f_{ck,cube} = 25 \text{ N/mm}^2$ , anchor HIT-V 5.8**

		Data according ETA-07/0260, issue 2009-01-12								
Anchor size		M8	M10	M12	M16	M20	M24	M27	M30	
Non cracked concrete										
Tensile $N_{Rk}$	HIT-V 5.8	[kN]	18,0	29,0	42,0	70,6	111,9	153,7	187,8	224,0
Shear $V_{Rk}$	HIT-V 5.8	[kN]	9,0	15,0	21,0	39,0	61,0	88,0	115,0	140,0
Cracked concrete										
Tensile $N_{Rk}$	HIT-V 5.8	[kN]	16,1	22,6	31,1	44,0	74,8	109,6	132,3	152,7
Shear $V_{Rk}$	HIT-V 5.8	[kN]	9,0	15,0	21,0	39,0	61,0	88,0	115,0	140,0

**Design resistance: concrete C 20/25 –  $f_{ck,cube} = 25 \text{ N/mm}^2$ , anchor HIT-V 5.8**

		Data according ETA-07/0260, issue 2009-01-12								
Anchor size		M8	M10	M12	M16	M20	M24	M27	M30	
Non cracked concrete										
Tensile $N_{Rd}$	HIT-V 5.8	[kN]	12,0	19,3	28,0	33,6	53,3	73,2	89,4	106,7
Shear $V_{Rd}$	HIT-V 5.8	[kN]	7,2	12,0	16,8	31,2	48,8	70,4	92,0	112,0
Cracked concrete										
Tensile $N_{Rd}$	HIT-V 5.8	[kN]	8,9	12,6	17,3	20,9	35,6	52,2	63,0	72,7
Shear $V_{Rd}$	HIT-V 5.8	[kN]	7,2	12,0	16,8	31,2	48,8	70,4	92,0	112,0

**Recommended loads <sup>a)</sup>: concrete C 20/25 –  $f_{ck,cube} = 25 \text{ N/mm}^2$ , anchor HIT-V 5.8**

		Data according ETA-07/0260, issue 2009-01-12								
Anchor size		M8	M10	M12	M16	M20	M24	M27	M30	
Non cracked concrete										
Tensile $N_{rec}$	HIT-V 5.8	[kN]	8,6	13,8	20,0	24,0	38,1	52,3	63,9	76,2
Shear $V_{rec}$	HIT-V 5.8	[kN]	5,1	8,6	12,0	22,3	34,9	50,3	65,7	80,0
Cracked concrete										
Tensile $N_{rec}$	HIT-V 5.8	[kN]	6,4	9,0	12,3	15,0	25,4	37,3	45,0	51,9
Shear $V_{rec}$	HIT-V 5.8	[kN]	5,1	8,6	12,0	22,3	34,9	50,3	65,7	80,0

a) With overall partial safety factor for action  $\gamma = 1,4$ . The partial safety factors for action depend on the type of loading and shall be taken from national regulations.

**Service temperature range**

Hilti HIT-RE 500-SD injection mortar may be applied in the temperature ranges given below. An elevated base material temperature may lead to a reduction of the design bond resistance.

Temperature range	Base material temperature	Maximum long term base material temperature	Maximum short term base material temperature
Temperature range I	-40 °C to +40 °C	+24 °C	+40 °C
Temperature range II	-40 °C to +58 °C	+35 °C	+58 °C
Temperature range III	-40 °C to +70 °C	+43 °C	+70 °C

**Max short term base material temperature**

Short-term elevated base material temperatures are those that occur over brief intervals, e.g. as a result of diurnal cycling.

**Max long term base material temperature**

Long-term elevated base material temperatures are roughly constant over significant periods of time.

**Materials**

**Mechanical properties of HIT-V / HAS**

		Data according ETA-07/0260, issue 2009-01-12							
Anchor size		M8	M10	M12	M16	M20	M24	M27	M30
Nominal tensile strength $f_{uk}$	HIT-V 5.8	[N/mm <sup>2</sup> ]	500	500	500	500	500	500	500
	HIT-V 8.8	[N/mm <sup>2</sup> ]	800	800	800	800	800	800	800
	HIT-V-R	[N/mm <sup>2</sup> ]	700	700	700	700	700	700	500
Yield strength $f_{yk}$	HIT-V-HCR	[N/mm <sup>2</sup> ]	800	800	800	800	800	700	700
	HIT-V 5.8	[N/mm <sup>2</sup> ]	400	400	400	400	400	400	400
	HIT-V 8.8	[N/mm <sup>2</sup> ]	640	640	640	640	640	640	640
	HIT-V-R	[N/mm <sup>2</sup> ]	450	450	450	450	450	450	210
Stressed cross-section $A_s$	HIT-V	[mm <sup>2</sup> ]	36,6	58,0	84,3	157	245	353	459
	HIT-V	[mm <sup>2</sup> ]	31,2	62,3	109	277	541	935	1387
Moment of resistance W	HIT-V	[mm <sup>3</sup> ]	31,2	62,3	109	277	541	935	1387

## Material quality

Part	Material
Threaded rod HIT-V(F) 5.8	Strength class 5.8, A <sub>5</sub> > 8% ductile steel galvanized ≥ 5 µm, (F) hot dipped galvanized ≥ 45 µm,
Threaded rod HIT-V(F) 8.8	Strength class 8.8, A <sub>5</sub> > 8% ductile steel galvanized ≥ 5 µm, (F) hot dipped galvanized ≥ 45 µm,
Threaded rod HIT-V-R	Stainless steel grade A4, A <sub>5</sub> > 8% ductile strength class 70 for ≤ M24 and class 50 for M27 to M30, 1.4401; 1.4404; 1.4578; 1.4571; 1.4439; 1.4362
Threaded rod HIT-V-HCR	High corrosion resistant steel, 1.4529; 1.4565 strength ≤ M20: R <sub>m</sub> = 800 N/mm <sup>2</sup> , R <sub>p 0.2</sub> = 640 N/mm <sup>2</sup> , A <sub>5</sub> > 8% ductile M24 to M30: R <sub>m</sub> = 700 N/mm <sup>2</sup> , R <sub>p 0.2</sub> = 400 N/mm <sup>2</sup> , A <sub>5</sub> > 8% ductile
Washer ISO 7089	Steel galvanized, hot dipped galvanized
	Stainless steel, 1.4401; 1.4404; 1.4578; 1.4571; 1.4439; 1.4362 High corrosion resistant steel, 1.4529; 1.4565
Nut EN ISO 4032	Strength class 8, steel galvanized ≥ 5 µm, hot dipped galvanized ≥ 45 µm
	Strength class 70, stainless steel grade A4, 1.4401; 1.4404; 1.4578; 1.4571; 1.4439; 1.4362
	Strength class 70, high corrosion resistant steel, 1.4529; 1.4565

## Anchor dimensions

Anchor size	M8	M10	M12	M16	M20	M24	M27	M30
Anchor embedment depth [mm]	80	90	110	125	170	210	240	270
Anchor rod HIT-V, HIT-V-R, HIT-V-HCR	Anchor rods HIT-V (-R / -HCR) are available in variable length							


## Setting

### installation equipment

Anchor size	M8	M10	M12	M16	M20	M24	M27	M30
Rotary hammer	TE2 – TE16				TE40 – TE70			
Other tools	compressed air gun or blow out pump, set of cleaning brushes, dispenser							

## Setting instruction

### Dry and water-saturated concrete, hammer drilling



Brush bore hole with required steel brush HIT-RB

For detailed information on installation see instruction for use given with the package of the product.


### Curing time for general conditions

Data according ETA-07/0260, issue 2009-01-12

Temperature of the base material	Working time in which anchor can be inserted and adjusted $t_{gel}$	Curing time before anchor can be fully loaded $t_{cure}$
40 °C	12 min	4 h
30 °C to 39 °C	20 min	8 h
20 °C to 29 °C	30 min	12 h
15 °C to 19 °C	1 ½ h	24 h
10 °C to 14 °C	2 h	48 h
5 °C to 9 °C	2 ½ h	72 h

## Setting details

			Data according ETA-07/0260, issue 2009-01-12							
Anchor size			M8	M10	M12	M16	M20	M24	M27	M30
Nominal diameter of drill bit	$d_0$	[mm]	10	12	14	18	24	28	30	35
Effective anchorage and drill hole depth range <sup>a)</sup>	$h_{ef,min}$	[mm]	40	40	48	64	80	96	108	120
	$h_{ef,max}$	[mm]	160	200	240	320	400	480	540	600
Minimum base material thickness	$h_{min}$	[mm]	$h_{ef} + 30 \text{ mm}$ $\geq 100 \text{ mm}$				$h_{ef} + 2 d_0$			
Diameter of clearance hole in the fixture	$d_f$	[mm]	9	12	14	18	22	26	30	33
Minimum spacing	$s_{min}$	[mm]	40	50	60	80	100	120	135	150
Minimum edge distance	$c_{min}$	[mm]	40	50	60	80	100	120	135	150
Critical spacing for splitting failure	$s_{cr,sp}$		$2 c_{cr,sp}$							
Critical edge distance for splitting failure <sup>b)</sup>	$c_{cr,sp}$	[mm]	$1,0 \cdot h_{ef}$ for $h / h_{ef} \geq 2,0$							
			$4,6 h_{ef} - 1,8 h$ for $2,0 > h / h_{ef} > 1,3$ :							
			$2,26 h_{ef}$ for $h / h_{ef} \leq 1,3$ :							
Critical spacing for concrete cone failure	$s_{cr,N}$		$2 c_{cr,N}$							
Critical edge distance for concrete cone failure <sup>c)</sup>	$c_{cr,N}$		$1,5 h_{ef}$							
Torque moment <sup>d)</sup>	$T_{max}$	[Nm]	10	20	40	80	150	200	270	300



For spacing (edge distance) smaller than critical spacing (critical edge distance) the design loads have to be reduced.

- $h_{ef,min} \leq h_{ef} \leq h_{ef,max}$  ( $h_{ef}$ : embedment depth)
- $h$ : base material thickness ( $h \geq h_{min}$ )
- The critical edge distance for concrete cone failure depends on the embedment depth  $h_{ef}$  and the design bond resistance. The simplified formula given in this table is on the safe side.
- This is the maximum recommended torque moment to avoid splitting failure during installation for anchors with minimum spacing and/or edge distance.

### Simplified design method

Simplified version of the design method according ETAG 001, TR 029. Design resistance according data given in ETA-07/0260, issue 2008-11-03.

- Influence of concrete strength
- Influence of edge distance
- Influence of spacing
- Valid for a group of two anchors. (The method may also be applied for anchor groups with more than two anchors or more than one edge distance. The influencing factors must then be considered for each edge distance and spacing. The calculated design loads are then on the save side: They will be lower than the exact values according ETAG 001, TR 029. To avoid this, it is recommended to use the anchor design software PROFIS anchor)

The design method is based on the following simplification:

- No different loads are acting on individual anchors (no eccentricity)


The values are valid for one anchor.

For more complex fastening applications please use the anchor design software PROFIS Anchor.

### Tension loading

The design tensile resistance is the lower value of

- Steel resistance:  $N_{Rd,s}$
- Combined pull-out and concrete cone resistance:  
 $N_{Rd,p} = N_{Rd,c}^0 \cdot f_{B,p} \cdot f_{1,N} \cdot f_{2,N} \cdot f_{3,N} \cdot f_{h,p} \cdot f_{re,N}$
- Concrete cone resistance:  $N_{Rd,c} = N_{Rd,c}^0 \cdot f_B \cdot f_{1,N} \cdot f_{2,N} \cdot f_{3,N} \cdot f_{h,N} \cdot f_{re,N}$
- Concrete splitting resistance (only non-cracked concrete):  
 $N_{Rd,sp} = N_{Rd,c}^0 \cdot f_B \cdot f_{1,sp} \cdot f_{2,sp} \cdot f_{3,sp} \cdot f_{h,N} \cdot f_{re,N}$



### Basic design tensile resistance

#### Design steel resistance $N_{Rd,s}$

		Data according ETA-07/0260, issue 2009-01-12							
Anchor size		M8	M10	M12	M16	M20	M24	M27	M30
$N_{Rd,s}$	HIT-V 5.8 [kN]	12,0	19,3	28,0	52,7	82,0	118,0	153,3	187,3
	HIT-V 8.8 [kN]	19,3	30,7	44,7	84,0	130,7	188,0	244,7	299,3
	HIT-V-R [kN]	13,9	21,9	31,6	58,8	92,0	132,1	80,4	98,3
	HIT-V-HCR [kN]	19,3	30,7	44,7	84,0	130,7	117,6	152,9	187,1

## Design combined pull-out and concrete cone resistance <sup>a)</sup>

$$N_{Rd,p} = N_{Rd,p}^0 \cdot f_{B,p} \cdot f_{1,N} \cdot f_{2,N} \cdot f_{3,N} \cdot f_{h,p} \cdot f_{re,N}$$

			Data according ETA-07/0260, issue 2009-01-12							
Anchor size			M8	M10	M12	M16	M20	M24	M27	M30
Typical embedment depth $h_{ef,typ}$ [mm]			80	90	110	125	170	210	240	270
Non cracked concrete										
$N_{Rd,p}^0$	Temperature range I	[kN]	17,9	25,1	36,9	44,9	76,3	105,6	135,7	157,5
$N_{Rd,p}^0$	Temperature range II	[kN]	14,5	20,4	29,9	35,9	61,0	82,9	106,6	133,3
$N_{Rd,p}^0$	Temperature range III	[kN]	8,9	12,6	18,4	22,4	35,6	52,8	63,0	78,8
Cracked concrete										
$N_{Rd,p}^0$	Temperature range I	[kN]	8,9	12,6	17,3	20,9	35,6	52,8	63,0	72,7
$N_{Rd,p}^0$	Temperature range II	[kN]	7,3	9,4	13,8	18,0	28,0	41,5	48,5	60,6
$N_{Rd,p}^0$	Temperature range III	[kN]	4,5	5,5	8,1	10,5	15,3	22,6	29,1	36,4

### a) Additional Hilti technical data (not part of ETA-07/0260, issue 2008-11-03):

The design values for combined pull-out and concrete cone resistance may be increased by 20 % for anchor installation in dry concrete (concrete not in contact with water before/during installation and curing).

## Design concrete cone resistance <sup>a)</sup> $N_{Rd,c} = N_{Rd,c}^0 \cdot f_B \cdot f_{1,N} \cdot f_{2,N} \cdot f_{3,N} \cdot f_{h,N} \cdot f_{re,N}$

## Design splitting resistance <sup>a) b)</sup> $N_{Rd,sp} = N_{Rd,c}^0 \cdot f_B \cdot f_{1,sp} \cdot f_{2,sp} \cdot f_{3,sp} \cdot f_{h,N} \cdot f_{re,N}$

			Data according ETA-07/0260, issue 2009-01-12							
Anchor size			M8	M10	M12	M16	M20	M24	M27	M30
$N_{Rd,c}^0$	Non cracked concrete	[kN]	20,1	24,0	32,4	33,6	53,3	73,2	89,4	106,7
$N_{Rd,c}^0$	Cracked concrete	[kN]	14,3	17,1	23,1	24,0	38,0	52,2	63,7	76,1

### a) Additional Hilti technical data (not part of ETA-07/0260, issue 2008-11-03):

The design values for concrete cone and splitting resistance may be increased by 20 % for anchor installation in dry concrete (concrete not in contact with water before/during installation and curing).

b) Splitting resistance must only be considered for non-cracked concrete

## Influencing factors

### Influence of concrete strength on combined pull-out and concrete cone resistance

Concrete strength designation (ENV 206)	C 20/25	C 25/30	C 30/37	C 35/45	C 40/50	C 45/55	C 50/60
$f_{B,p} = (f_{ck,cube}/25N/mm^2)^{0,1}$ <sup>a)</sup>	1	1,02	1,04	1,06	1,07	1,08	1,09

a)  $f_{ck,cube}$  = concrete compressive strength, measured on cubes with 150 mm side length

### Influence of embedment depth on combined pull-out and concrete cone resistance

$$f_{h,p} = h_{ef}/h_{ef,typ}$$

### Influence of concrete strength on concrete cone resistance

Concrete strength designation (ENV 206)	C 20/25	C 25/30	C 30/37	C 35/45	C 40/50	C 45/55	C 50/60
$f_B = (f_{ck,cube}/25N/mm^2)^{1/2}$ <sup>a)</sup>	1	1,1	1,22	1,34	1,41	1,48	1,55

a)  $f_{ck,cube}$  = concrete compressive strength, measured on cubes with 150 mm side length



### Influence of edge distance <sup>a)</sup>

$c/c_{cr,N}$	0,1	0,2	0,3	0,4	0,5	0,6	0,7	0,8	0,9	1
$c/c_{cr,sp}$										
$f_{1,N} = 0,7 + 0,3 \cdot c/c_{cr,N}$	0,73	0,76	0,79	0,82	0,85	0,88	0,91	0,94	0,97	1
$f_{1,sp} = 0,7 + 0,3 \cdot c/c_{cr,sp}$										
$f_{2,N} = 0,5 \cdot (1 + c/c_{cr,N})$	0,55	0,60	0,65	0,70	0,75	0,80	0,85	0,90	0,95	1
$f_{2,sp} = 0,5 \cdot (1 + c/c_{cr,sp})$										

a) The edge distance shall not be smaller than the minimum edge distance  $c_{min}$  given in the table with the setting details. These influencing factors must be considered for every edge distance smaller than the critical edge distance.

### Influence of anchor spacing <sup>a)</sup>

$s/s_{cr,N}$	0,1	0,2	0,3	0,4	0,5	0,6	0,7	0,8	0,9	1
$s/s_{cr,sp}$										
$f_{3,N} = 0,5 \cdot (1 + s/s_{cr,N})$	0,55	0,60	0,65	0,70	0,75	0,80	0,85	0,90	0,95	1
$f_{3,sp} = 0,5 \cdot (1 + s/s_{cr,sp})$										

a) The anchor spacing shall not be smaller than the minimum anchor spacing  $s_{min}$  given in the table with the setting details. This influencing factor must be considered for every anchor spacing.

### Influence of embedment depth on concrete cone resistance

$$f_{h,N} = (h_{ef}/h_{ef,typ})^{1,5}$$

### Influence of reinforcement


$h_{ef}$ [mm]	40	50	60	70	80	90	$\geq 100$
$f_{re,N} = 0,5 + h_{ef}/200\text{mm} \leq 1$	0,7 <sup>a)</sup>	0,75 <sup>a)</sup>	0,8 <sup>a)</sup>	0,85 <sup>a)</sup>	0,9 <sup>a)</sup>	0,95 <sup>a)</sup>	1

a) This factor applies only for dense reinforcement. If in the area of anchorage there is reinforcement with a spacing  $\geq 150$  mm (any diameter) or with a diameter  $\leq 10$  mm and a spacing  $\geq 100$  mm, then a factor  $f_{re} = 1$  may be applied.

## Shear loading

### The design shear resistance is the lower value of

- Steel resistance:  $V_{Rd,s}$
- Concrete pryout resistance:  $V_{Rd,cp} = k \cdot \text{lower value of } N_{Rd,p} \text{ and } N_{Rd,c}$
- Concrete edge resistance:  $V_{Rd,c} = V_{Rd,c}^0 \cdot f_B \cdot f_{fB} \cdot f_h \cdot f_4 \cdot f_{hef} \cdot f_c$



## Basic design shear resistance

### Design steel resistance $V_{Rd,s}$

			Data according ETA-07/0260, issue 2009-01-12							
Anchor size			M8	M10	M12	M16	M20	M24	M27	M30
$V_{Rd,s}$	HIT-V 5.8	[kN]	7,2	12,0	16,8	31,2	48,8	70,4	92,0	112,0
	HIT-V 8.8	[kN]	12,0	18,4	27,2	50,4	78,4	112,8	147,2	179,2
	HIT-V-R	[kN]	8,3	12,8	19,2	35,3	55,1	79,5	48,3	58,8
	HIT-V-HCR	[kN]	12,0	18,4	27,2	50,4	78,4	70,9	92,0	112,0

### Design concrete pryout resistance $V_{Rd,cp} = \text{lower value}^a)$ of $k \cdot N_{Rd,p}$ and $k \cdot N_{Rd,c}$

$$k = 1 \text{ for } h_{ef} < 60 \text{ mm}$$

$$k = 2 \text{ for } h_{ef} \geq 60 \text{ mm}$$

- a)  $N_{Rd,p}$ : Design combined pull-out and concrete cone resistance  
 $N_{Rd,c}$ : Design concrete cone resistance

### Design concrete edge resistance $V_{Rd,c} = V_{Rd,c}^0 \cdot f_B \cdot f_{\beta} \cdot f_h \cdot f_d \cdot f_{hef} \cdot f_c$

Anchor size		M8	M10	M12	M16	M20	M24	M27	M30
Non-cracked concrete									
$V_{Rd,c}^0$	[kN]	5,9	8,6	11,6	18,7	27,0	36,6	44,5	53,0
Cracked concrete									
$V_{Rd,c}^0$	[kN]	4,2	6,1	8,2	13,2	19,2	25,9	31,5	37,5

## Influencing factors


### Influence of concrete strength

Concrete strength designation (ENV 206)	C 20/25	C 25/30	C 30/37	C 35/45	C 40/50	C 45/55	C 50/60
$f_B = (f_{ck,cube}/25\text{N/mm}^2)^{1/2}$ a)	1	1,1	1,22	1,34	1,41	1,48	1,55

- a)  $f_{ck,cube}$  = concrete compressive strength, measured on cubes with 150 mm side length

### Influence of angle between load applied and the direction perpendicular to the free edge

Angle $\beta$	0°	10°	20°	30°	40°	50°	60°	70°	80°	$\geq 90^\circ$
$f_{\beta}$	1	1,01	1,05	1,13	1,24	1,40	1,64	1,97	2,32	2,50



### Influence of base material thickness

$h/c$	0,15	0,3	0,45	0,6	0,75	0,9	1,05	1,2	1,35	$\geq 1,5$
$f_h = \{h/(1,5 \cdot c)\}^{1/2} \leq 1$	0,32	0,45	0,55	0,63	0,71	0,77	0,84	0,89	0,95	1,00

**Influence of anchor spacing and edge distance <sup>a)</sup> for concrete edge resistance:  $f_4$**   
 $f_4 = (c/h_{ef})^{1,5} \cdot (1 + s / [3 \cdot c]) \cdot 0,5$

c/h <sub>ef</sub>	Single anchor	Group of two anchors s/h <sub>ef</sub>														
		0,75	1,50	2,25	3,00	3,75	4,50	5,25	6,00	6,75	7,50	8,25	9,00	9,75	10,50	11,25
0,50	0,35	0,27	0,35	0,35	0,35	0,35	0,35	0,35	0,35	0,35	0,35	0,35	0,35	0,35	0,35	0,35
0,75	0,65	0,43	0,54	0,65	0,65	0,65	0,65	0,65	0,65	0,65	0,65	0,65	0,65	0,65	0,65	0,65
1,00	1,00	0,63	0,75	0,88	1,00	1,00	1,00	1,00	1,00	1,00	1,00	1,00	1,00	1,00	1,00	1,00
1,25	1,40	0,84	0,98	1,12	1,26	1,40	1,40	1,40	1,40	1,40	1,40	1,40	1,40	1,40	1,40	1,40
1,50	1,84	1,07	1,22	1,38	1,53	1,68	1,84	1,84	1,84	1,84	1,84	1,84	1,84	1,84	1,84	1,84
1,75	2,32	1,32	1,49	1,65	1,82	1,98	2,15	2,32	2,32	2,32	2,32	2,32	2,32	2,32	2,32	2,32
2,00	2,83	1,59	1,77	1,94	2,12	2,30	2,47	2,65	2,83	2,83	2,83	2,83	2,83	2,83	2,83	2,83
2,25	3,38	1,88	2,06	2,25	2,44	2,63	2,81	3,00	3,19	3,38	3,38	3,38	3,38	3,38	3,38	3,38
2,50	3,95	2,17	2,37	2,57	2,77	2,96	3,16	3,36	3,56	3,76	3,95	3,95	3,95	3,95	3,95	3,95
2,75	4,56	2,49	2,69	2,90	3,11	3,32	3,52	3,73	3,94	4,15	4,35	4,56	4,56	4,56	4,56	4,56
3,00	5,20	2,81	3,03	3,25	3,46	3,68	3,90	4,11	4,33	4,55	4,76	4,98	5,20	5,20	5,20	5,20
3,25	5,86	3,15	3,38	3,61	3,83	4,06	4,28	4,51	4,73	4,96	5,18	5,41	5,63	5,86	5,86	5,86
3,50	6,55	3,51	3,74	3,98	4,21	4,44	4,68	4,91	5,14	5,38	5,61	5,85	6,08	6,31	6,55	6,55
3,75	7,26	3,87	4,12	4,36	4,60	4,84	5,08	5,33	5,57	5,81	6,05	6,29	6,54	6,78	7,02	7,26
4,00	8,00	4,25	4,50	4,75	5,00	5,25	5,50	5,75	6,00	6,25	6,50	6,75	7,00	7,25	7,50	7,75
4,25	8,76	4,64	4,90	5,15	5,41	5,67	5,93	6,18	6,44	6,70	6,96	7,22	7,47	7,73	7,99	8,25
4,50	9,55	5,04	5,30	5,57	5,83	6,10	6,36	6,63	6,89	7,16	7,42	7,69	7,95	8,22	8,49	8,75
4,75	10,35	5,45	5,72	5,99	6,27	6,54	6,81	7,08	7,36	7,63	7,90	8,17	8,45	8,72	8,99	9,26
5,00	11,18	5,87	6,15	6,43	6,71	6,99	7,27	7,55	7,83	8,11	8,39	8,66	8,94	9,22	9,50	9,78
5,25	12,03	6,30	6,59	6,87	7,16	7,45	7,73	8,02	8,31	8,59	8,88	9,17	9,45	9,74	10,02	10,31
5,50	12,90	6,74	7,04	7,33	7,62	7,92	8,21	8,50	8,79	9,09	9,38	9,67	9,97	10,26	10,55	10,85

a) The anchor spacing and the edge distance shall not be smaller than the minimum anchor spacing  $s_{min}$  and the minimum edge distance  $c_{min}$ .

**Influence of embedment depth**

h <sub>ef</sub> /d	4	4,5	5	6	7	8	9	10	11
f <sub>nef</sub> = 0,05 · (h <sub>ef</sub> / d) <sup>1,68</sup>	0,51	0,63	0,75	1,01	1,31	1,64	2,00	2,39	2,81
h <sub>ef</sub> /d	12	13	14	15	16	17	18	19	20
f <sub>nef</sub> = 0,05 · (h <sub>ef</sub> / d) <sup>1,68</sup>	3,25	3,72	4,21	4,73	5,27	5,84	6,42	7,04	7,67

**Influence of edge distance <sup>a)</sup>**

c/d	4	6	8	10	15	20	30	40
f <sub>c</sub> = (d / c) <sup>0,19</sup>	0,77	0,71	0,67	0,65	0,60	0,57	0,52	0,50

a) The edge distance shall not be smaller than the minimum edge distance  $c_{min}$ .

**Combined tension and shear loading**

For combined tension and shear loading see section "Anchor Design".

## Precalculated values

Design resistance: concrete C 20/25 –  $f_{ck,cube} = 25 \text{ N/mm}^2$ , Temperature range I

		Data according ETA-07/0260, issue 2009-01-12							
Anchor size		M8	M10	M12	M16	M20	M24	M27	M30
Embedment depth $h_{ef,1} =$ [mm]		48	60	72	96	120	144	162	180
Base material thickness $h_{min} =$ [mm]		100	100	102	132	168	200	222	250
<b>Tensile <math>N_{Rd}</math>: single anchor, no edge effects</b>									
Non cracked concrete									
HIT-V 5.8									
HIT-V 8.8									
HIT-V-R	[kN]	9,3	13,0	17,1	22,6	31,6	41,6	49,6	58,1
HIT-V-HCR									
Cracked concrete									
HIT-V 5.8									
HIT-V 8.8									
HIT-V-R	[kN]	5,4	8,4	11,3	16,1	22,5	29,6	35,3	41,4
HIT-V-HCR									
<b>Shear <math>V_{Rd}</math>: single anchor, no edge effects, without lever arm</b>									
Non cracked concrete									
HIT-V 5.8	[kN]	7,2	12,0	16,8	31,2	48,8	70,4	92,0	112,0
HIT-V 8.8	[kN]	11,2	18,4	27,2	50,4	78,4	112,8	138,8	162,6
HIT-V-R	[kN]	8,3	12,8	19,2	35,3	55,1	79,5	48,3	58,8
HIT-V-HCR	[kN]	11,2	18,4	27,2	50,4	78,4	70,9	92,0	112,0
Cracked concrete									
HIT-V 5.8	[kN]	6,4	12,0	16,8	31,2	48,8	70,4	92,0	112,0
HIT-V 8.8	[kN]	6,4	18,4	27,1	45,0	63,1	82,9	99,0	115,9
HIT-V-R	[kN]	6,4	12,8	19,2	35,3	55,1	79,5	48,3	58,8
HIT-V-HCR	[kN]	6,4	18,4	27,1	45,0	63,1	70,9	92,0	112,0

Design resistance: concrete C 20/25 –  $f_{ck,cube} = 25 \text{ N/mm}^2$ , Temperature range I

		Data according ETA-07/0260, issue 2009-01-12							
Anchor size		M8	M10	M12	M16	M20	M24	M27	M30
Embedment depth $h_{ef,1} =$ [mm]		48	60	72	96	120	144	162	180
Base material thickness $h_{min} =$ [mm]		100	100	102	132	168	200	222	250
Edge distance $c = c_{min} =$ [mm]		40	50	60	80	100	120	135	150
<b>Tensile <math>N_{Rd}</math>: single anchor, min. edge distance (<math>c = c_{min}</math>)</b>									
Non cracked concrete									
HIT-V 5.8									
HIT-V 8.8									
HIT-V-R	[kN]	6,3	8,5	9,9	12,9	18,2	23,8	28,2	33,2
HIT-V-HCR									
Cracked concrete									
HIT-V 5.8									
HIT-V 8.8									
HIT-V-R	[kN]	3,6	5,6	7,1	9,2	12,9	16,9	20,1	23,7
HIT-V-HCR									
<b>Shear <math>V_{Rd}</math>: single anchor, min. edge distance (<math>c = c_{min}</math>), without lever arm</b>									
Non cracked concrete									
HIT-V 5.8									
HIT-V 8.8									
HIT-V-R	[kN]	3,4	4,9	6,7	10,8	15,7	21,4	26,0	31,1
HIT-V-HCR									
Cracked concrete									
HIT-V 5.8									
HIT-V 8.8									
HIT-V-R	[kN]	2,4	3,5	4,7	7,6	11,1	15,1	18,4	22,0
HIT-V-HCR									

**Design resistance: concrete C 20/25 –  $f_{ck,cube} = 25 \text{ N/mm}^2$ , Temperature range I**  
(load values are valid for single anchor)

		Data according ETA-07/0260, issue 2009-01-12							
Anchor size		M8	M10	M12	M16	M20	M24	M27	M30
Embedment depth $h_{ef,1} =$ [mm]		48	60	72	96	120	144	162	180
Base material thickness $h_{min} =$ [mm]		100	100	102	132	168	200	222	250
Spacing $s = s_{min} =$ [mm]		40	50	60	80	100	120	135	150
<b>Tensile <math>N_{Rd}</math>: double anchor, no edge effects, min. spacing (<math>s = s_{min}</math>)</b>									
Non cracked concrete									
HIT-V 5.8									
HIT-V 8.8	[kN]	6,0	8,2	10,3	13,5	19,0	24,9	29,6	34,8
HIT-V-R									
HIT-V-HCR									
Cracked concrete									
HIT-V 5.8									
HIT-V 8.8	[kN]	3,6	5,5	7,4	9,6	13,5	17,8	21,1	24,8
HIT-V-R									
HIT-V-HCR									
<b>Shear <math>V_{Rd}</math>: double anchor, no edge effects, min. spacing (<math>s = s_{min}</math>), without lever arm</b>									
Non cracked concrete									
HIT-V 5.8	[kN]	7,2	12,0	16,8	31,2	48,8	70,4	88,7	103,9
HIT-V 8.8	[kN]	7,2	18,4	26,3	40,5	56,5	74,3	88,7	103,9
HIT-V-R	[kN]	7,2	12,8	19,2	35,3	55,1	74,3	48,3	58,8
HIT-V-HCR	[kN]	7,2	18,4	26,3	40,5	56,5	70,9	88,7	103,9
Cracked concrete									
HIT-V 5.8	[kN]	4,1	12,0	16,8	28,8	40,3	53,0	63,2	74,1
HIT-V 8.8	[kN]	4,1	12,8	17,3	28,8	40,3	53,0	63,2	74,1
HIT-V-R	[kN]	4,1	12,8	17,3	28,8	40,3	53,0	48,3	58,8
HIT-V-HCR	[kN]	4,1	12,8	17,3	28,8	40,3	53,0	63,2	74,1

**Design resistance: concrete C 20/25 –  $f_{ck,cube} = 25 \text{ N/mm}^2$ , Temperature range I**

		Data according ETA-07/0260, issue 2009-01-12							
Anchor size		M8	M10	M12	M16	M20	M24	M27	M30
Embedment depth $h_{ef,typ} =$ [mm]		80	90	110	125	170	210	240	270
Base material thickness $h_{min} =$ [mm]		110	120	140	161	218	266	300	340
<b>Tensile <math>N_{Rd}</math>: single anchor, no edge effects</b>									
Non cracked concrete									
HIT-V 5.8	[kN]	12,0	19,3	28,0	33,6	53,3	73,2	89,4	106,7
HIT-V 8.8	[kN]	17,9	24,0	32,4	33,6	53,3	73,2	89,4	106,7
HIT-V-R	[kN]	13,9	21,9	31,6	33,6	53,3	73,2	80,4	98,3
HIT-V-HCR	[kN]	17,9	24,0	32,4	33,6	53,3	73,2	89,4	106,7
Cracked concrete									
HIT-V 5.8									
HIT-V 8.8	[kN]	8,9	12,6	17,3	20,9	35,6	52,2	63,0	72,7
HIT-V-R									
HIT-V-HCR									
<b>Shear <math>V_{Rd}</math>: single anchor, no edge effects, without lever arm</b>									
Non cracked concrete									
HIT-V 5.8	[kN]	7,2	12,0	16,8	31,2	48,8	70,4	92,0	112,0
HIT-V 8.8	[kN]	12,0	18,4	27,2	50,4	78,4	112,8	147,2	179,2
HIT-V-R	[kN]	8,3	12,8	19,2	35,3	55,1	79,5	48,3	58,8
HIT-V-HCR	[kN]	12,0	18,4	27,2	50,4	78,4	70,9	92,0	112,0
Cracked concrete									
HIT-V 5.8	[kN]	7,2	12,0	16,8	31,2	48,8	70,4	92,0	112,0
HIT-V 8.8	[kN]	12,0	18,4	27,2	50,4	78,4	112,8	147,2	179,2
HIT-V-R	[kN]	8,3	12,8	19,2	35,3	55,1	79,5	48,3	58,8
HIT-V-HCR	[kN]	12,0	18,4	27,2	41,9	71,2	70,9	92,0	112,0

**Design resistance: concrete C 20/25 –  $f_{ck,cube} = 25 \text{ N/mm}^2$ , Temperature range I**

		Data according ETA-07/0260, issue 2009-01-12							
Anchor size		M8	M10	M12	M16	M20	M24	M27	M30
Embedment depth $h_{ef,typ} =$ [mm]		80	90	110	125	170	210	240	270
Base material thickness $h_{min} =$ [mm]		110	120	140	161	218	266	300	340
Edge distance $c = c_{min} =$ [mm]		40	50	60	80	100	120	135	150
<b>Tensile <math>N_{Rd}</math>: single anchor, min. edge distance (<math>c = c_{min}</math>)</b>									
Non cracked concrete									
HIT-V 5.8									
HIT-V 8.8									
HIT-V-R	[kN]	9,6	11,6	15,5	16,9	26,1	35,6	43,3	51,4
HIT-V-HCR									
Cracked concrete									
HIT-V 5.8									
HIT-V 8.8									
HIT-V-R	[kN]	4,8	7,0	9,5	12,1	18,6	25,4	30,8	36,7
HIT-V-HCR									
<b>Shear <math>V_{Rd}</math>: single anchor, min. edge distance (<math>c = c_{min}</math>), without lever arm</b>									
Non cracked concrete									
HIT-V 5.8									
HIT-V 8.8									
HIT-V-R	[kN]	3,7	5,3	7,3	11,5	17,2	23,6	29,0	34,8
HIT-V-HCR									
Cracked concrete									
HIT-V 5.8									
HIT-V 8.8									
HIT-V-R	[kN]	2,6	3,8	5,2	8,1	12,2	16,7	20,5	24,7
HIT-V-HCR									



**Design resistance: concrete C 20/25 –  $f_{ck,cube} = 25 \text{ N/mm}^2$ , Temperature range I**  
(load values are valid for single anchor)

		Data according ETA-07/0260, issue 2009-01-12							
Anchor size		M8	M10	M12	M16	M20	M24	M27	M30
Embedment depth $h_{ef,typ} =$ [mm]		80	90	110	125	170	210	240	270
Base material thickness $h_{min} =$ [mm]		110	120	140	161	218	266	300	340
Spacing $s = s_{min} =$ [mm]		40	50	60	80	100	120	135	150
<b>Tensile <math>N_{Rd}</math>: double anchor, no edge effects, min. spacing (<math>s = s_{min}</math>)</b>									
Non cracked concrete									
HIT-V 5.8	[kN]								
HIT-V 8.8	[kN]	10,9	13,5	18,1	19,2	30,1	41,2	50,3	59,9
HIT-V-R	[kN]								
HIT-V-HCR	[kN]								
Cracked concrete									
HIT-V 5.8	[kN]								
HIT-V 8.8	[kN]	5,9	8,1	11,1	13,2	21,5	29,4	35,8	42,7
HIT-V-R	[kN]								
HIT-V-HCR	[kN]								
<b>Shear <math>V_{Rd}</math>: double anchor, no edge effects, min. spacing (<math>s = s_{min}</math>), without lever arm</b>									
Non cracked concrete									
HIT-V 5.8	[kN]	7,2	12,0	16,8	31,2	48,8	70,4	92,0	112,0
HIT-V 8.8	[kN]	12,0	18,4	27,2	50,4	78,4	112,8	147,2	177,0
HIT-V-R	[kN]	8,3	12,8	19,2	35,3	55,1	79,5	48,3	58,8
HIT-V-HCR	[kN]	12,0	18,4	27,2	50,4	78,4	70,9	92,0	112,0
Cracked concrete									
HIT-V 5.8	[kN]	7,2	12,0	16,8	31,2	48,8	70,4	92,0	112,0
HIT-V 8.8	[kN]	12,0	17,9	24,5	35,6	59,6	86,9	104,8	120,6
HIT-V-R	[kN]	8,3	12,8	19,2	35,3	55,1	79,5	48,3	58,8
HIT-V-HCR	[kN]	12,0	17,9	24,5	35,6	59,6	70,9	92,0	112,0

**Design resistance: concrete C 20/25 –  $f_{ck,cube} = 25 \text{ N/mm}^2$ , Temperature range I**

		Data according ETA-07/0260, issue 2009-01-12							
Anchor size		M8	M10	M12	M16	M20	M24	M27	M30
Embedment depth $h_{ef,2} =$ [mm]		96	120	144	192	240	288	324	360
Base material thickness $h_{min} =$ [mm]		126	150	174	228	288	344	384	430
<b>Tensile <math>N_{Rd}</math>: single anchor, no edge effects</b>									
Non cracked concrete									
HIT-V 5.8	[kN]	12,0	19,3	28,0	52,7	82,0	117,5	140,2	164,3
HIT-V 8.8	[kN]	19,3	30,7	44,7	64,0	89,4	117,5	140,2	164,3
HIT-V-R	[kN]	13,9	21,9	31,6	58,8	89,4	117,5	80,4	98,3
HIT-V-HCR	[kN]	19,3	30,7	44,7	64,0	89,4	117,5	140,2	164,3
Cracked concrete									
HIT-V 5.8	[kN]	10,7	16,8	22,6	32,2	50,3	72,4	85,1	96,9
HIT-V 8.8	[kN]	10,7	16,8	22,6	32,2	50,3	72,4	85,1	96,9
HIT-V-R	[kN]	10,7	16,8	22,6	32,2	50,3	72,4	80,4	96,9
HIT-V-HCR	[kN]	10,7	16,8	22,6	32,2	50,3	72,4	85,1	96,9
<b>Shear <math>V_{Rd}</math>: single anchor, no edge effects, without lever arm</b>									
Non cracked and cracked concrete									
HIT-V 5.8	[kN]	7,2	12,0	16,8	31,2	48,8	70,4	92,0	112,0
HIT-V 8.8	[kN]	12,0	18,4	27,2	50,4	78,4	112,8	147,2	179,2
HIT-V-R	[kN]	8,3	12,8	19,2	35,3	55,1	79,5	48,3	58,8
HIT-V-HCR	[kN]	12,0	18,4	27,2	50,4	78,4	70,9	92,0	112,0

**Design resistance: concrete C 20/25 –  $f_{ck,cube} = 25 \text{ N/mm}^2$ , Temperature range I**

		Data according ETA-07/0260, issue 2009-01-12							
Anchor size		M8	M10	M12	M16	M20	M24	M27	M30
Embedment depth $h_{ef,2} =$ [mm]		96	120	144	192	240	288	324	360
Base material thickness $h_{min} =$ [mm]		126	150	174	228	288	344	384	430
Edge distance $c = c_{min} =$ [mm]		40	50	60	80	100	120	135	150
<b>Tensile <math>N_{Rd}</math>: single anchor, min. edge distance (<math>c = c_{min}</math>)</b>									
Non cracked concrete									
HIT-V 5.8									
HIT-V 8.8									
HIT-V-R	[kN]	11,6	16,5	21,7	28,6	40,0	52,6	62,7	73,5
HIT-V-HCR									
Cracked concrete									
HIT-V 5.8									
HIT-V 8.8									
HIT-V-R	[kN]	5,8	9,0	12,2	17,5	27,4	37,5	44,7	52,4
HIT-V-HCR									
<b>Shear <math>V_{Rd}</math>: single anchor, min. edge distance (<math>c = c_{min}</math>), without lever arm</b>									
Non cracked concrete									
HIT-V 5.8									
HIT-V 8.8									
HIT-V-R	[kN]	3,9	5,7	7,8	12,9	18,9	25,9	31,8	38,1
HIT-V-HCR									
Cracked concrete									
HIT-V 5.8									
HIT-V 8.8									
HIT-V-R	[kN]	2,8	4,0	5,5	9,1	13,4	18,4	22,5	27,0
HIT-V-HCR									







**Design resistance: concrete C 20/25 –  $f_{ck,cube} = 25 \text{ N/mm}^2$ , Temperature range I**  
(load values are valid for single anchor)

		Data according ETA-07/0260, issue 2009-01-12							
Anchor size		M8	M10	M12	M16	M20	M24	M27	M30
Embedment depth $h_{ef,2} =$ [mm]		96	120	144	192	240	288	324	360
Base material thickness $h_{min} =$ [mm]		126	150	174	228	288	344	384	430
Spacing $s = s_{min} =$ [mm]		40	50	60	80	100	120	135	150
<b>Tensile <math>N_{Rd}</math>: double anchor, no edge effects, min. spacing (<math>s = s_{min}</math>)</b>									
Non cracked concrete									
HIT-V 5.8	[kN]	12,0	19,3	26,5	34,9	48,8	64,2	76,6	89,7
HIT-V 8.8	[kN]	13,4	20,1	26,5	34,9	48,8	64,2	76,6	89,7
HIT-V-R	[kN]	13,4	20,1	26,5	34,9	48,8	64,2	76,6	89,7
HIT-V-HCR	[kN]	13,4	20,1	26,5	34,9	48,8	64,2	76,6	89,7
Cracked concrete									
HIT-V 5.8									
HIT-V 8.8	[kN]	7,2	11,0	14,8	20,8	31,7	44,9	52,9	61,1
HIT-V-R									
HIT-V-HCR									
<b>Shear <math>V_{Rd}</math>: double anchor, no edge effects, min. spacing (<math>s = s_{min}</math>), without lever arm</b>									
Non cracked concrete									
HIT-V 5.8	[kN]	7,2	12,0	16,8	31,2	48,8	70,4	92,0	112,0
HIT-V 8.8	[kN]	12,0	18,4	27,2	50,4	78,4	112,8	147,2	179,2
HIT-V-R	[kN]	8,3	12,8	19,2	35,3	55,1	79,5	48,3	58,8
HIT-V-HCR	[kN]	12,0	18,4	27,2	50,4	78,4	70,9	92,0	112,0
Cracked concrete									
HIT-V 5.8	[kN]	7,2	12,0	16,8	31,2	48,8	70,4	92,0	112,0
HIT-V 8.8	[kN]	12,0	18,4	27,2	50,4	78,4	112,8	135,6	154,6
HIT-V-R	[kN]	8,3	12,8	19,2	35,3	55,1	79,5	48,3	58,8
HIT-V-HCR	[kN]	12,0	18,4	27,2	50,4	78,4	70,9	92,0	112,0

## Precalculated values

Recommended loads: concrete C 20/25 –  $f_{ck,cube} = 25 \text{ N/mm}^2$ , Temperature range I

		Data according ETA-07/0260, issue 2009-01-12								
Anchor size		M8	M10	M12	M16	M20	M24	M27	M30	
Embedment depth	$h_{ef,1} = [\text{mm}]$	48	60	72	96	120	144	162	180	
Base material thickness	$h_{min} = [\text{mm}]$	100	100	102	132	168	200	222	250	
<b>Tensile <math>N_{rec}</math>: single anchor, no edge effects</b>										
Non cracked concrete										
	HIT-V 5.8									
	HIT-V 8.8									
	HIT-V-R	[kN]	6,7	9,3	12,2	16,2	22,6	29,7	35,4	41,5
	HIT-V-HCR									
Cracked concrete										
	HIT-V 5.8									
	HIT-V 8.8									
	HIT-V-R	[kN]	3,8	6,0	8,1	11,5	16,1	21,2	25,2	29,6
	HIT-V-HCR									
<b>Shear <math>V_{rec}</math>: single anchor, no edge effects, without lever arm</b>										
Non cracked concrete										
	HIT-V 5.8	[kN]	5,1	8,6	12,0	22,3	34,9	50,3	65,7	80,0
	HIT-V 8.8	[kN]	8,0	13,1	19,4	36,0	56,0	80,6	99,2	116,1
	HIT-V-R	[kN]	6,0	9,2	13,7	25,2	39,4	56,8	34,5	42,0
	HIT-V-HCR	[kN]	8,0	13,1	19,4	36,0	56,0	50,6	65,7	80,0
Cracked concrete										
	HIT-V 5.8	[kN]	4,6	8,6	12,0	22,3	34,9	50,3	65,7	80,0
	HIT-V 8.8	[kN]	4,6	13,1	19,4	32,2	45,1	59,2	70,7	82,8
	HIT-V-R	[kN]	4,6	9,2	13,7	25,2	39,4	56,8	34,5	42,0
	HIT-V-HCR	[kN]	4,6	13,1	19,4	32,2	45,1	50,6	65,7	80,0

For the recommended loads an overall partial safety factor for action  $\gamma = 1,4$  is considered. The partial safety factors for action depend on the type of loading and shall be taken from national regulations.

**Recommended loads: concrete C 20/25 –  $f_{ck,cube} = 25 \text{ N/mm}^2$ , Temperature range I**

		Data according ETA-07/0260, issue 2009-01-12							
Anchor size		M8	M10	M12	M16	M20	M24	M27	M30
Embedment depth $h_{ef,1} =$ [mm]		48	60	72	96	120	144	162	180
Base material thickness $h_{min} =$ [mm]		100	100	102	132	168	200	222	250
Edge distance $c = c_{min} =$ [mm]		40	50	60	80	100	120	135	150
<b>Tensile <math>N_{rec}</math>: single anchor, min. edge distance (<math>c = c_{min}</math>)</b>									
Non cracked concrete									
HIT-V 5.8									
HIT-V 8.8	[kN]	4,5	6,1	7,1	9,2	13,0	17,0	20,1	23,7
HIT-V-R									
HIT-V-HCR									
Cracked concrete									
HIT-V 5.8									
HIT-V 8.8	[kN]	2,6	4,0	5,0	6,6	9,2	12,1	14,3	16,9
HIT-V-R									
HIT-V-HCR									
<b>Shear <math>V_{rec}</math>: single anchor, min. edge distance (<math>c = c_{min}</math>), without lever arm</b>									
Non cracked concrete									
HIT-V 5.8									
HIT-V 8.8	[kN]	2,4	3,5	4,8	7,7	11,2	15,3	18,6	22,2
HIT-V-R									
HIT-V-HCR									
Cracked concrete									
HIT-V 5.8									
HIT-V 8.8	[kN]	1,7	2,5	3,4	5,5	8,0	10,8	13,2	15,7
HIT-V-R									
HIT-V-HCR									




For the recommended loads an overall partial safety factor for action  $\gamma = 1,4$  is considered. The partial safety factors for action depend on the type of loading and shall be taken from national regulations.

**Recommended loads: concrete C 20/25 –  $f_{ck,cube} = 25 \text{ N/mm}^2$ , Temperature range I**  
(load values are valid for single anchor)

		Data according ETA-07/0260, issue 2009-01-12								
Anchor size		M8	M10	M12	M16	M20	M24	M27	M30	
Embedment depth	$h_{ef,1} =$ [mm]	48	60	72	96	120	144	162	180	
Base material thickness	$h_{min} =$ [mm]	100	100	102	132	168	200	222	250	
Spacing	$s = s_{min} =$ [mm]	40	50	60	80	100	120	135	150	
<b>Tensile <math>N_{rec}</math>: double anchor, no edge effects, min. spacing (<math>s = s_{min}</math>)</b>										
Non cracked concrete										
	HIT-V 5.8									
	HIT-V 8.8									
	HIT-V-R	[kN]	4,3	5,9	7,4	9,7	13,6	17,8	21,2	24,9
	HIT-V-HCR									
Cracked concrete										
	HIT-V 5.8									
	HIT-V 8.8									
	HIT-V-R	[kN]	2,6	3,9	5,3	6,9	9,7	12,7	15,1	17,7
	HIT-V-HCR									
<b>Shear <math>V_{rec}</math>: double anchor, no edge effects, min. spacing (<math>s = s_{min}</math>), without lever arm</b>										
Non cracked concrete										
	HIT-V 5.8	[kN]	5,1	8,6	12,0	22,3	34,9	50,3	63,4	74,2
	HIT-V 8.8	[kN]	5,1	13,1	18,8	28,9	40,4	53,1	63,4	74,2
	HIT-V-R	[kN]	5,1	9,2	13,7	25,2	39,4	53,1	34,5	42,0
	HIT-V-HCR	[kN]	5,1	13,1	18,8	28,9	40,4	50,6	63,4	74,2
Cracked concrete										
	HIT-V 5.8	[kN]	2,9	8,6	12,0	20,6	28,8	37,9	45,2	52,9
	HIT-V 8.8	[kN]	2,9	9,2	12,4	20,6	28,8	37,9	45,2	52,9
	HIT-V-R	[kN]	2,9	9,2	12,4	20,6	28,8	37,9	34,5	42,0
	HIT-V-HCR	[kN]	2,9	9,2	12,4	20,6	28,8	37,9	45,2	52,9

For the recommended loads an overall partial safety factor for action  $\gamma = 1,4$  is considered. The partial safety factors for action depend on the type of loading and shall be taken from national regulations.

**Recommended loads: concrete C 20/25 –  $f_{ck,cube} = 25 \text{ N/mm}^2$ , Temperature range I**

Anchor size		Data according ETA-07/0260, issue 2009-01-12							
		M8	M10	M12	M16	M20	M24	M27	M30
Embedment depth $h_{ef,typ} =$ [mm]		80	90	110	125	170	210	240	270
Base material thickness $h_{min} =$ [mm]		110	120	140	161	218	266	300	340
<b>Tensile <math>N_{rec}</math>: single anchor, no edge effects</b>									
Non cracked concrete									
 HIT-V 5.8	[kN]	8,6	13,8	20,0	24,0	38,1	52,3	63,9	76,2
HIT-V 8.8	[kN]	12,8	17,1	23,1	24,0	38,1	52,3	63,9	76,2
HIT-V-R	[kN]	9,9	15,7	22,5	24,0	38,1	52,3	57,4	70,2
HIT-V-HCR	[kN]	12,8	17,1	23,1	24,0	38,1	52,3	63,9	76,2
Cracked concrete									
 HIT-V 5.8									
HIT-V 8.8	[kN]	6,4	9,0	12,3	15,0	25,4	37,3	45,0	51,9
HIT-V-R	[kN]								
HIT-V-HCR	[kN]								
<b>Shear <math>V_{rec}</math>: single anchor, no edge effects, without lever arm</b>									
Non cracked concrete									
HIT-V 5.8	[kN]	5,1	8,6	12,0	22,3	34,9	50,3	65,7	80,0
HIT-V 8.8	[kN]	8,6	13,1	19,4	36,0	56,0	80,6	105,1	128,0
HIT-V-R	[kN]	6,0	9,2	13,7	25,2	39,4	56,8	34,5	42,0
HIT-V-HCR	[kN]	8,6	13,1	19,4	36,0	56,0	50,6	65,7	80,0
Cracked concrete									
 HIT-V 5.8	[kN]	5,1	8,6	12,0	22,3	34,9	50,3	65,7	80,0
HIT-V 8.8	[kN]	8,6	13,1	19,4	36,0	56,0	80,6	105,1	128,0
HIT-V-R	[kN]	6,0	9,2	13,7	25,2	39,4	56,8	34,5	42,0
HIT-V-HCR	[kN]	8,6	13,1	19,4	36,0	56,0	50,6	65,7	80,0

For the recommended loads an overall partial safety factor for action  $\gamma = 1,4$  is considered. The partial safety factors for action depend on the type of loading and shall be taken from national regulations.

**Recommended loads: concrete C 20/25 –  $f_{ck,cube} = 25 \text{ N/mm}^2$ , Temperature range I**

		Data according ETA-07/0260, issue 2009-01-12							
Anchor size		M8	M10	M12	M16	M20	M24	M27	M30
Embedment depth $h_{ef,typ} =$ [mm]		80	90	110	125	170	210	240	270
Base material thickness $h_{min} =$ [mm]		110	120	140	161	218	266	300	340
Edge distance $c = c_{min} =$ [mm]		40	50	60	80	100	120	135	150
<b>Tensile <math>N_{rec}</math>: single anchor, min. edge distance (<math>c = c_{min}</math>)</b>									
Non cracked concrete									
HIT-V 5.8									
HIT-V 8.8									
HIT-V-R	[kN]	6,8	8,3	11,1	12,1	18,7	25,4	30,9	36,7
HIT-V-HCR									
Cracked concrete									
HIT-V 5.8									
HIT-V 8.8									
HIT-V-R	[kN]	3,4	5,0	6,8	8,6	13,3	18,1	22,0	26,2
HIT-V-HCR									
<b>Shear <math>V_{rec}</math>: single anchor, min. edge distance (<math>c = c_{min}</math>), without lever arm</b>									
Non cracked concrete									
HIT-V 5.8									
HIT-V 8.8									
HIT-V-R	[kN]	2,7	3,8	5,2	8,2	12,3	16,9	20,7	24,9
HIT-V-HCR									
Cracked concrete									
HIT-V 5.8									
HIT-V 8.8									
HIT-V-R	[kN]	1,9	2,7	3,7	5,8	8,7	11,9	14,7	17,6
HIT-V-HCR									




For the recommended loads an overall partial safety factor for action  $\gamma = 1,4$  is considered. The partial safety factors for action depend on the type of loading and shall be taken from national regulations.

**Recommended loads: concrete C 20/25 –  $f_{ck,cube} = 25 \text{ N/mm}^2$ , Temperature range I**  
(load values are valid for single anchor)

		Data according ETA-07/0260, issue 2009-01-12							
Anchor size		M8	M10	M12	M16	M20	M24	M27	M30
Embedment depth $h_{ef,typ} =$ [mm]		80	90	110	125	170	210	240	270
Base material thickness $h_{min} =$ [mm]		110	120	140	161	218	266	300	340
Spacing $s = s_{min} =$ [mm]		40	50	60	80	100	120	135	150
<b>Tensile <math>N_{rec}</math>: double anchor, no edge effects, min. spacing (<math>s = s_{min}</math>)</b>									
Non cracked concrete									
HIT-V 5.8									
HIT-V 8.8	[kN]	7,8	9,6	13,0	13,7	21,5	29,4	35,9	42,8
HIT-V-R									
HIT-V-HCR									
Cracked concrete									
HIT-V 5.8									
HIT-V 8.8	[kN]	4,2	5,8	7,9	9,5	15,3	21,0	25,6	30,5
HIT-V-R									
HIT-V-HCR									
<b>Shear <math>V_{rec}</math>: double anchor, no edge effects, min. spacing (<math>s = s_{min}</math>), without lever arm</b>									
Non cracked concrete									
HIT-V 5.8	[kN]	5,1	8,6	12,0	22,3	34,9	50,3	65,7	80,0
HIT-V 8.8	[kN]	8,6	13,1	19,4	36,0	56,0	80,6	105,1	126,4
HIT-V-R	[kN]	6,0	9,2	13,7	25,2	39,4	56,8	34,5	42,0
HIT-V-HCR	[kN]	8,6	13,1	19,4	36,0	56,0	80,6	105,1	126,4
Cracked concrete									
HIT-V 5.8	[kN]	5,1	8,6	12,0	22,3	34,9	50,3	65,7	80,0
HIT-V 8.8	[kN]	8,6	12,8	17,5	25,4	42,6	62,1	74,8	86,2
HIT-V-R	[kN]	6,0	9,2	13,7	25,2	39,4	56,8	34,5	42,0
HIT-V-HCR	[kN]	8,6	12,8	17,5	25,4	42,6	62,1	74,8	86,2

For the recommended loads an overall partial safety factor for action  $\gamma = 1,4$  is considered. The partial safety factors for action depend on the type of loading and shall be taken from national regulations.

**Recommended loads: concrete C 20/25 –  $f_{ck,cube} = 25 \text{ N/mm}^2$ , Temperature range I**

Anchor size		Data according ETA-07/0260, issue 2009-01-12							
		M8	M10	M12	M16	M20	M24	M27	M30
Embedment depth $h_{ef,2} =$ [mm]		96	120	144	192	240	288	324	360
Base material thickness $h_{min} =$ [mm]		126	150	174	228	288	344	384	430
<b>Tensile <math>N_{rec}</math>: single anchor, no edge effects</b>									
Non cracked concrete									
 HIT-V 5.8	[kN]	8,6	13,8	20,0	37,6	58,6	84,0	100,2	117,3
HIT-V 8.8	[kN]	13,8	21,9	31,9	45,7	63,9	84,0	100,2	117,3
HIT-V-R	[kN]	9,9	15,7	22,5	42,0	63,9	84,0	57,4	70,2
HIT-V-HCR	[kN]	13,8	21,9	31,9	45,7	63,9	84,0	100,2	117,3
Cracked concrete									
 HIT-V 5.8	[kN]	7,7	12,0	16,2	23,0	35,9	51,7	60,8	69,2
HIT-V 8.8	[kN]	7,7	12,0	16,2	23,0	35,9	51,7	60,8	69,2
HIT-V-R	[kN]	7,7	12,0	16,2	23,0	35,9	51,7	57,4	69,2
HIT-V-HCR	[kN]	7,7	12,0	16,2	23,0	35,9	51,7	60,8	69,2
<b>Shear <math>V_{rec}</math>: single anchor, no edge effects, without lever arm</b>									
Non cracked and cracked concrete									
 HIT-V 5.8	[kN]	5,1	8,6	12,0	22,3	34,9	50,3	65,7	80,0
HIT-V 8.8	[kN]	8,6	13,1	19,4	36,0	56,0	80,6	105,1	128,0
HIT-V-R	[kN]	6,0	9,2	13,7	25,2	39,4	56,8	34,5	42,0
HIT-V-HCR	[kN]	8,6	13,1	19,4	36,0	56,0	50,6	65,7	80,0

For the recommended loads an overall partial safety factor for action  $\gamma = 1,4$  is considered. The partial safety factors for action depend on the type of loading and shall be taken from national regulations.





**Recommended loads: concrete C 20/25 –  $f_{ck,cube} = 25 \text{ N/mm}^2$ , Temperature range I**

		Data according ETA-07/0260, issue 2009-01-12							
Anchor size		M8	M10	M12	M16	M20	M24	M27	M30
Embedment depth $h_{ef,2} =$ [mm]		96	120	144	192	240	288	324	360
Base material thickness $h_{min} =$ [mm]		126	150	174	228	288	344	384	430
Edge distance $c = c_{min} =$ [mm]		40	50	60	80	100	120	135	150
<b>Tensile <math>N_{rec}</math>: single anchor, min. edge distance (<math>c = c_{min}</math>)</b>									
Non cracked concrete									
HIT-V 5.8									
HIT-V 8.8									
HIT-V-R									
HIT-V-HCR									
Cracked concrete									
HIT-V 5.8									
HIT-V 8.8									
HIT-V-R									
HIT-V-HCR									
<b>Shear <math>V_{rec}</math>: single anchor, min. edge distance (<math>c = c_{min}</math>), without lever arm</b>									
Non cracked concrete									
HIT-V 5.8									
HIT-V 8.8									
HIT-V-R									
HIT-V-HCR									
Cracked concrete									
HIT-V 5.8									
HIT-V 8.8									
HIT-V-R									
HIT-V-HCR									

For the recommended loads an overall partial safety factor for action  $\gamma = 1,4$  is considered. The partial safety factors for action depend on the type of loading and shall be taken from national regulations.

**Recommended loads: concrete C 20/25 –  $f_{ck,cube} = 25 \text{ N/mm}^2$ , Temperature range I**  
(load values are valid for single anchor)

Anchor size		Data according ETA-07/0260, issue 2009-01-12							
		M8	M10	M12	M16	M20	M24	M27	M30
Embedment depth	$h_{ef,2} =$ [mm]	96	120	144	192	240	288	324	360
Base material thickness	$h_{min} =$ [mm]	126	150	174	228	288	344	384	430
Spacing	$s = s_{min} =$ [mm]	40	50	60	80	100	120	135	150
<b>Tensile <math>N_{rec}</math>: double anchor, no edge effects, min. spacing (<math>s = s_{min}</math>)</b>									
Non cracked concrete									
	HIT-V 5.8 [kN]	8,6	13,8	18,9	25,0	34,9	45,8	54,7	64,1
	HIT-V 8.8 [kN]	9,5	14,4	18,9	25,0	34,9	45,8	54,7	64,1
	HIT-V-R [kN]	9,5	14,4	18,9	25,0	34,9	45,8	54,7	64,1
	HIT-V-HCR [kN]	9,5	14,4	18,9	25,0	34,9	45,8	54,7	64,1
Cracked concrete									
	HIT-V 5.8								
	HIT-V 8.8 [kN]	5,1	7,8	10,5	14,9	22,7	32,0	37,8	43,6
	HIT-V-R								
	HIT-V-HCR								
<b>Shear <math>V_{rec}</math>: double anchor, no edge effects, min. spacing (<math>s = s_{min}</math>), without lever arm</b>									
Non cracked concrete									
	HIT-V 5.8 [kN]	5,1	8,6	12,0	22,3	34,9	50,3	65,7	80,0
	HIT-V 8.8 [kN]	8,6	13,1	19,4	36,0	56,0	80,6	105,1	128,0
	HIT-V-R [kN]	6,0	9,2	13,7	25,2	39,4	56,8	34,5	42,0
	HIT-V-HCR [kN]	8,6	13,1	19,4	36,0	56,0	50,6	65,7	80,0
Cracked concrete									
	HIT-V 5.8 [kN]	5,1	8,6	12,0	22,3	34,9	50,3	65,7	80,0
	HIT-V 8.8 [kN]	8,6	13,1	19,4	36,0	56,0	80,6	96,9	110,4
	HIT-V-R [kN]	6,0	9,2	13,7	25,2	39,4	56,8	34,5	42,0
	HIT-V-HCR [kN]	8,6	13,1	19,4	36,0	56,0	50,6	65,7	80,0

For the recommended loads an overall partial safety factor for action  $\gamma = 1,4$  is considered. The partial safety factors for action depend on the type of loading and shall be taken from national regulations.